


**Moulded Reed Switch - Rectangular - Normally Open Contacts**  
**Part Number : PPS 24**  
**Product Data Sheet**
**PICTURE**

**DIMENSIONS**

**✓ RoHS Compliant**

 Drawings not to scale  
 All dimensions in mm nominal

**SPECIFICATION**

Contact Form / Style	Normally Open	
Switching Voltage	Max Volts AC	24
Switching Current	Max Amps	0.1
Switching Capacity (Resistive)	Max W/V/A	1.0
Switching Distance (Typical)	mm	dependant on magnet
Contact resistance	Max mOhm	200
Operating Temperature	Celsius	-25° -70°
Storage Temperature	Celsius	-25° -70°
Case Material	Polypropylene	

**Applications Include**
**Options**

- Position and limit sensing.
- Linear actuators.
- Consumer electronics activation.
- Automated production lines.

- Colour: Standard = Blue housing. Also available Black housing.
- Various AT ratings
- Please contact our technical sales team if you have a specific requirement

Rev. No.	Revision Note	Date	Signature
2	Datasheet update	02-03-12	ML


 ISO 9001:2008  
 Certificate No. FM21080

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

**Phone : +44 (0)1255 862236**
**www.assemtech.co.uk**
**Fax: +44 (0)1255 862014**

©2012 Copyright Assemtech Europe Ltd, Unit 7, Rice Bridge Industrial Estate, Thorpe - Le - Soken, Essex, CO16 0HL, ENGLAND.