

Section Links

A045 | A040 | A095 | A090 | A195 | A190 | A080 | A085 | A087 | A200 | A070 | A210 | A300 | **A315** | A089 | A125 | A105 | A205

Product Details

A315 Heavy Duty Low Profile Fixed Stud Levelling Foot - Stainless Steel Stud and Base with Inset Nitrile Rubber Pad

Materials Base - Stainless Steel Base with an Inset Nitrile Rubber Anti-Slip Pad
Stud - Stainless Steel



Part No.	Thread Size D1 (mm)	Thread Length L (mm)	Base Diameter D2 (mm)	Overall Height H (mm)	Pad Thickness (mm)	Maximum Recommended Load (kg)
A315/001	M12	75	60	90	3	1250
A315/002	M12	125	60	140	3	1250
A315/003	M12	150	60	165	3	1250
A315/004	M12	150	80	171	3	1500
A315/005	M16	150	80	171	3	2000
A315/006	M16	150	120	174	3	2000
A315/007	M20	200	120	224	3	3000
A315/008	M20	200	150	226	3	3000
A315/009	M24	200	150	226	3	4000

Dimensions are approximate

