


LEDs & INDICATORS

515 MPA Series

- Threaded body for panel thicknesses 0.5-3.5mm, panel cut-out 6.4mm diameter
- Stripped wire termination 164mm long, PVC
- LED, Filament 6-28V 30-40mA and Neons 125-240V 0.8-1mA, as standard
- Neon-replacement LED version is fitted with a resistor and operates at 240V AC. Operating life 50,000 hours
- Polycarbonate lens/body, chrome bezel, supplied with nut and shakeproof washer
- Red, green, amber, clear, blue and opal lens colour options as standard
- Maximum working temperature 105°C
- Custom wire lengths and specification to order



TYPE NO.	515	1	05 - XXXX - T / XXX
515 Series Indicator	515		
Lens Type	Trapezoid	1	
	Top Hat	2	
Stripped wire 164mm long	05		
LED pins	13		
LED, black cathode & white anode wires	LED		
LED, neon-replacement 240V 1mA	LED2		
Filament 6V 40mA, white wire	640		
Filament 12V 35mA, yellow wire	1235		
Filament 14V 40mA, yellow wire	1440		
Filament 24V 35mA, green wire	24		
Filament 28V 30mA, green wire	28		
Neon 125V 1mA, blue wire	125		
Neon 240V 0.8mA, red wire	240		
Transparent lens	T		
Lens colour Red	RED		
Lens colour Green	GRN		
Lens colour Amber	AMB		
Lens colour Clear	CLR		
Lens colour Blue	BLU		
Lens colour Opal	OPL		

Body Dimensions

