

1A Variable Output LDO Regulators - BD00IC0WHFV

| Part number | Status | Package | Unit Quantity | Minium Package Quantity | Packing Type | RoHS |
|-------------|--------|---------|---------------|-------------------------|--------------|------|
| BD00IC0WHFV | | HVSOF6 | 3000 | 3000 | | true |

Specifications:

| | |
|-------------------------|----------|
| VoltageOutPrecision | ±1.0 |
| VoltageInMax | 5.5 |
| Channel | 1 |
| OperatingTemperatureMin | -25 |
| ShutdownFunction | Yes |
| InputCapacitor | 1.0 |
| CircuitCurrent | 0.3 |
| VoltageOutMin | 0.8 |
| ProductGradeText | Standard |
| OverCurrentProtection | Yes |
| VoltageOutMax | 4.5 |
| OutputCurrent | 1.0 |
| VoltageInMin | 2.3 |
| VimpMax | 7.0 |
| ThermalShutdown | Yes |
| OutputCapacitor | 1.0 |
| OperatingTemperatureMax | 85 |

