Search Results

Evaluate
- FAQ's
- Product Bulletins
- PDFObsolete and ..
- Selection Guides
- PDFConvenience ..

Design a Solution
- Part Drawings
- PDFFork Termina..

How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'PV10-8F-E'**

Your search criteria matched only one product, shown below

PV10-8F-E

- Fork design provides for fast and easy installation, without the need to remove fastener
- Insulation support helps to prevent wire damage in bending applications
- Brazed seam protects terminal barrel from splitting during the crimp process
- Internal barrel serrations assure good wire contact and maximum tensile strength
- UL Flammability UL 94V -0, maximum insulation temperature 221°F (105°C)
- UL and CSA rated up 600 V per UL 486A/B, where applicable

‡UL and CSA approved tooling/product combinations.
Note: Wire sizes #26 – #22 AWG, are not UL Listed or CSA Certified.

Part Number	PV10-8F-E
RoHS Compliancy Status	Compliant
Part Description	Fork Terminal, vinyl insulated, funnel entry, 14– 10 AWG, #8 stud size.
Product Type	Terminals
CSA Certified	Yes
UL Listed	Yes
Length (In.)	1.04
Length (mm)	26.4
Width (In.)	0.37
Width (mm)	9.4
CE Compliant	No
Clearance	0.25
Clearance (mm)	6.4
Insulation	Vinyl
Max. Ins.	0.225
Max. Ins. (mm)	5.75
Panduit Color Code	Yellow
Plating Type	Tinned
Pricing Description	Terminal Convenience Package
Stock	0.04
Stock (mm)	1.0
Stud Size	#8
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
Tool	CT-100A‡, CT-600-A‡, CT-1550‡, CT-1551‡, CT-2500‡
Wire Range	14 – 10 AWG
Wire Range (mm²)	4.0 – 6.0
Min. Order UOM	PC
Min. Order Qty.	20
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy