

① Cable Black print
AWM STYLE 2725 80°C 30V VW-1 28AWG/1P 24AWG/2C
---c AWM I/II A 80°C 30V FT1 USB 1.1 CABLE

PE Bag Packing



1PC/PE Bag

PIN ASSIGNMENT



WSW P/N	Jacket color	Length(mm)
AK670-1	Beige	1000±30
AK670-2	Beige	2000±50
AK670-3	Beige	3000±50
AK670-5	Beige	5000±50

Electrical test:
1. 100% short, open, miss wire test
2. Conduct resistance: 2 Ohm max.
3. Insulator resistance: 5MΩ min.
4. Dielectric test: DC 300V

NO.	NAME.	Q'TY	SPECIFICATION
⑤	PE Bag	1	Clear Print black "MADE IN CHINA"+ "1PC"
④	TIE	1	White
③	Out Jacket	12g	Beige(BG002) PVC-45P
②	Cable	1	USB1.1 UL2725 28#/1P+24#/2C+AEB OD:4.7mm Beige(BG002)
①	CONN	2	USB A Male Shell:Nickel Pin:G/F Insulator color:White

RoHS compliant
Unit: mm

Scale	Free				Date	Name	Customer-No.
TOLERANCE				Drawn	24.10.2014	Amy	
				Approved	12.04.2016	Amy	ASSMANN WSW-No. AK670-x
DIM	TOL	①	Update the drawing	12.04.2016	Amy		Drawing-No. ASS 7245 CA rev01
		⓪	Drawn	24.10.2014	Amy		
Angle	TOL	Id.	Modification	Date	Name		Replace / Sheet

ASSMANN WSW components