



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

## 12-outlet Vertical Power Strip with Hardwire Input

MODEL NUMBER: **PS3612-20HW**



### Description

Tripp Lite's PS3612-20HW Power Strip offers 20 amp multi-outlet AC power distribution in a convenient 36 inch hardwire cabinet. Includes knockout panels to accept 3/4 in. conduit fittings for hardwire installation and 12 output receptacles with 2.99 inch center-to-center spacing. Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications.

INPUT/OUTPUT: Input: Hardwire access via knockout panels that accept 3/4 inch conduit fittings

Output: 12 Outlets total (2 NEMA 5-15/20R and 10 NEMA 5-15R)

ELECTRICAL: 120V AC, 50/60Hz, 20A (no circuit breaker)

FORMAT: 36 inch strip format

### Features

- Versatile all-metal 36 inch format with outlets arranged in a single row
- Knockout panels for 3/4 inch conduit fittings allow permanent hardwire installation
- Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
- 12 outlets total: 2 NEMA 5-15/20R (20A) and 10 NEMA 5-15R (15A)
- 20 amp electrical capacity
- 120VAC, 50/60Hz electrical compatibility

## Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency compatibility	50 / 60 Hz

### Highlights

- AC input hardwired via knockout on unit
- 12 outlets
- 20-amp capacity
- Ideal for applications requiring permanent installation

### Applications

- Offers multiple outlet power distribution for a variety of applications, including office, workbench, industrial, networking, telecom and more.

### Package Includes

- PS3612-20HW
- Instruction manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Output watts	2400
Outlet quantity / type	10 NEMA 5-15R & 2 NEMA 5-15/20R
Outlet spacing	2.99 in.
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V
Input connection type	Hardwire
Voltage compatibility (VAC)	120
<b>PHYSICAL</b>	
Unit Dimensions (HWD/in)	36 x 1.5 x 1.5
Unit Dimensions (HWD/cm)	91.44 x 3.8 x 3.8
Material of construction	Metal
Integrated keyhole mounting tabs	Mount through housing supports bolt down installation to a variety of flat surfaces
Receptacle Color	Almond
Style	Bench/Cabinet Mount
Outlets center to center measurement	101.60mm
<b>CERTIFICATIONS</b>	
cUL / CSA (Canada)	cUL
Approvals	UL
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PS3612-20HW](#)