THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By -TE ALL RIGHTS RESERVED.

LOC	DIST
GP	00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REV PER ECO-11-007678	11JUL2011	RG	DO



DRILL HOLE DIAMETER
10X ø.0453±.0010
AFTER PLATING
ø.043/ø.037

RECOMMENDED FOOT PRINT



4. FINISHES:
   CROWN: GOLD PLATED, .000030 MIN THICK
   OVER NICKEL PLATED, .000040 MIN THICK.
   INSERT: SILVER PLATED, .000200 MIN THICK,
   OVER NICKEL PLATED, .000040 MIN THICK.
   CONTACT: SILVER PLATED, .000200 MIN THICK,
   OVER NICKEL PLATED, .000040 MIN THICK.

3. MATERIALS:
   HOUSING: THERMOPLASTIC, GLASS REINFORCED, COLOR-BLACK
   UL94V-0 FLAMMABILITY RATED
   INSERT: ZINC ALLOY, CASTING
   CROWN: COPPER ALLOY
   CONTACT: BRASS ALLOY

2. ITEMS PROVIDED TO THIS SPECIFICATION SHALL BE IDENTIFIED ON THE CONTAINER WITH THE FOLLOWING INFORMATION: PART NUMBER & DATE CODE OF MANUFACTURE.

1. PART NUMBER CHANGES AND OR DESIGN CHANGES AFFECTING ITEM INTERCHANGEABILITY REQUIRE PRIOR TE APPROVAL AND AUTHORIZATION BY REVISION TO THIS DRAWING.

5. A FIVE POUND (5lb) FORCE IS REQUIRED TO CORRECTLY SEAT THE CONNECTOR WITH PLATED THRU HOLES LESS THAN ø.040 INCH.

6650785-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± .02
3 PLC	± .010
4 PLC	± -
ANGLES	± .5

MATERIAL: -
FINISH: -

DWN HA NGUYEN 07/22/06
CHK -
APVD STEVE FLICKINGER 07/22/06
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME: -ICCON, PIN, SIZE No.8, PARALLEL SOLDER TAIL, 10 PIN FOOT PRINT NON LOCKING STYLE, 1.500 PIN EXT.

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-6650785	-

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV B