




FEATURES:

- Connector accepts types RG/U: 59, 59A, 59B, 62, 62A, 62B, 62C, and 210.
- Connector meets interface requirements of MIL-STD-348.

MATERIALS:

Body: Brass, Tarnish Resistant Plating

Center Contact: Male: Gold Plated Brass

Female: Gold Plated Beryllium Copper

Gasket – Silicone Rubber

Dielectric: PTFE

Marking: "POMONA 5286"

RATINGS:

Operating Voltage: 500 VRMS Max.

Nominal Impedance: 75 Ohms

ORDERING INFORMATION: Model 5286

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS **90118** (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com