| IMAGE | TPI PART NUMBER | DESCRIPTION | TYPE | JAW OPENING | VOLTAGE RATING | CURRENT RATING | MATERIAL | COLOR | LENGTH | INSULATION | TERMINATION | PLATING | INSULATION MATERIAL |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| | BC24AZP | Broad Alligator clip - Zinc plated | Heavy Duty | .75" (19mm) | _ | 25 Amps | Steel | Natural | 2.84" (72.2mm) | Non-insulated | Screw or crimp | Zinc | _ |
| | BC60AC | Narrow Alligator clip - Solid Copper | Alligator | .31" (7.9mm) | _ | 10 Amps | Copper | Natural | 1.97" (50mm) | Non-insulated | Screw | _ | _ |
| | BC60AST | Narrow Alligator clip - Solid Stainless Steel | Alligator | .31" (7.9mm) | _ | 10 Amps | Stainless Steel | Natural | 1.97" (50mm) | Non-insulated | Crimp or solder | _ | _ |
| | BC60ANP | Narrow Alligator clip - Nickel plated steel | Alligator | .31" (7.9mm) | _ | 10 Amps | Steel | Natural | 1.97" (50mm) | Non-insulated | Crimp or solder | Nickel | _ |
| | BC27AC | Medium Narrow Alligator Clip - Solid Copper | Heavy Duty 3-sided jaw | .625" (16mm) | _ | 40 Amps | Copper | Natural | 2.44" (61.9mm) | Non-insulated | Screw or crimp | _ | _ |
| | BC27AZP | Medium Narrow Alligator Clip - Zinc plated | Heavy Duty 3-sided jaw | .625" (16mm) | _ | 20 Amps | Steel | Natural | 2.44" (61.9mm) | Non-insulated | Screw or crimp | Zinc | _ |
| | BC25AZP | Medium Alligator Clip - Zinc plated | Heavy Duty 3-sided jaw | .75" (19mm) | _ | 40 Amps | Steel | Natural | 3" (76.2mm) | Non-insulated | Screw or crimp | Zinc | _ |
| | BC25AC | Medium Alligator Clip - Solid Copper | Heavy Duty 3-sided jaw | .75" (19mm) | _ | 75 Amps | Copper | Natural | 3" (76.2mm) | Non-insulated | Screw or crimp | _ | _ |
| | BC6TRC | Terminal Clamp Wide red handle - Solid Copper | Pliers -type Miniature | 1.125" (28.6mm) | _ | 75 Amps | Copper | Red | 2.88" (98.4mm) | Insulated | Crimp or solder | _ | PVC |
| | BC6TBC | Terminal Clamp Wide black handle - Solid Copper | Pliers -type Miniature | 1.125" (28.6mm) | _ | 75 Amps | Copper | Black | 2.88" (98.4mm) | Insulated | Crimp or solder | _ | PVC |
| same as BC46TBCP but with red grip | BC46TRCP | Terminal Clamp Narrow red handle - Copper plated | Pliers -type Miniature | 1.125" (28.6mm) | _ | 50 Amps | Steel | Red | 2.88" (98.4mm) | Insulated | Crimp or solder | Copper | PVC |
| | 33 | Terminal Clamp Narrow black handle - Copper plated | Pliers -type Miniature | 1.125" (28.6mm) | _ | 50 Amps | Steel | Black | 2.88" (98.4mm) | Insulated | Crimp or solder | Copper | PVC |
| | BC30ANP | Narrow Alligator clip - Nickel plated steel | Alligator Miniature | .188" (4.8mm) | _ | 5 Amps | Steel | Natural | 1.1" (27.8mm) | Non-insulated | Crimp or solder | Nickel | _ |

TPI - The Value Leader