

3M™ Floor Mats 1864/1864R Properties

Property	Typical Value
Material	EVA Copolymer/Rubber
Thickness	0.125 in. (3,2 mm)
Hardness	80-85 Shore A
*Resistance	
(Surface to Ground)	9×10^2 ohms
(Surface to Surface)	6×10^2 ohms
**Resistivity	10^2 ohms-cm

*Tested per ESD Association Standard S4.1 at 72 °F, 50% RH using 3M™ Test Kit 701 for Static Control Surfaces (Megohmmeter)

**Tested per ASTM D 257