





Performance level	PL2
Capacitance	1000pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION dB
5	1 dB
10	3dB
50	12dB
100	20dB
500	34dB
1000	30dB



				Dat.	Name		D-Sub, Female, Straight 15 Poles, with turned solder bucket and hole	Ma?Mstab/ Scale 1.5:1
			Detail.	8-JUL-02	CV			
			Insp.	12/01/12	JB			
			Stand.					
36283	12/01/12	SD				All Dim. in mm Orig. Size DIN A 4	TB 09642117230	Blatt/ Page 1 / 1
31570	06/11/03	AF	HARTING EURL F-95972 Paris					
31058	8-JUL-02	CV						
Mod.	Dat.	Name						