




LOC		DIST		REVISIONS			
GP		00		DESCRIPTION	DATE	DWN	APVD
				E	REVISED PER ECO-12-020263	16NOV2012	CJV

- 1

COORDINATE DIMENSION APPLIES FROM BASIC LOCATION.
- 2

10 AND 14 POSITION SIZES CONTAIN ONLY ONE SLOT FOR SNAP-IN POLARIZER (MILITARY POLARIZATION) LOCATED AS SHOWN.
- 3

10 POSITION SIZES CONTAIN ONLY ONE SLOT FOR DUAL POLARIZATION, LOCATED AS SHOWN.
- 4

RECOMMENDED PRINTED CIRCUIT BOARD THICKNESS IS 1.57 [0.062].
- 5

DISTANCE REQUIRED BY EJECTION LATCHES IN THE OPEN POSITION.
- 6

MATERIAL HOUSING & LATCHES: GLASS FILLED NYLON OR POLYESTER, UL94V-0 RATED BLACK.
POSTS: BRASS.
- 7

POSTS:
GOLD FLASH OVER PALLADIUM-NICKEL PLATE, 0.38µm [0.000015] MIN TOTAL ON THE LOCALIZED PLATE AREA,
2.54µm [0.000100] MIN TIN PLATE ON THE SOLDER-TAILS,
1.27µm [0.000050] MIN NICKEL UNDERPLATE ON THE ENTIRE POST.
OR
0.38µm [0.000015] MIN GOLD PLATE ON THE LOCALIZED PLATE AREA,
2.54µm [0.000100] MIN TIN PLATE ON THE SOLDER-TAILS,
1.27µm [0.000050] MIN NICKEL UNDERPLATE ON THE ENTIRE POST.
- 8

DATUMS M & N TO BE ESTABLISHED BY CUSTOMER.

OBSOLETE	78.74 [3.100]	90.42 [3.560]	90.42 [3.560]	100.58 [3.960]	96.52 [3.800]	86.36 [3.400]	64	1-5499786-2
	73.66 [2.900]	85.34 [3.360]	85.34 [3.360]	95.50 [3.760]	91.44 [3.600]	81.28 [3.200]	60	1-5499786-1
	60.96 [2.400]	72.64 [2.860]	72.64 [2.860]	82.80 [3.260]	78.74 [3.100]	68.58 [2.700]	50	1-5499786-0
	48.26 [1.900]	59.94 [2.360]	59.94 [2.360]	70.10 [2.760]	66.04 [2.600]	55.88 [2.200]	40	5499786-9
	40.64 [1.600]	52.32 [2.060]	52.32 [2.060]	62.48 [2.460]	58.42 [2.300]	48.26 [1.900]	34	5499786-8
	35.56 [1.400]	47.24 [1.860]	47.24 [1.860]	57.40 [2.260]	53.34 [2.100]	43.18 [1.700]	30	5499786-7
	30.48 [1.200]	42.16 [1.660]	42.16 [1.660]	52.32 [2.060]	48.26 [1.900]	38.10 [1.500]	26	5499786-6
	27.94 [1.100]	39.62 [1.560]	39.62 [1.560]	49.78 [1.960]	45.72 [1.800]	35.56 [1.400]	24	5499786-5
	22.86 [.900]	34.54 [1.360]	34.54 [1.360]	44.70 [1.760]	40.64 [1.600]	30.48 [1.200]	20	5499786-4
	17.78 [.700]	29.46 [1.160]	29.46 [1.160]	39.62 [1.560]	35.56 [1.400]	25.40 [1.000]	16	5499786-3
	15.24 [.600]	26.92 [1.060]	26.92 [1.060]	37.08 [1.460]	33.02 [1.300]	22.86 [.900]	14	5499786-2
	10.16 [.400]	21.84 [.860]	21.84 [.860]	32.00 [1.260]	27.94 [1.100]	17.78 [.700]	10	5499786-1
	F	E	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA - 01-07-05	TE Connectivity	
		CHK S. BOLASH - 01-07-05		
DIMENSIONS: mm [INCHES]		APVD M. WALMSLEY - 01-07-05	NAME	
		PRODUCT SPEC	HEADER ASSY, UNIVERSAL, AMP-LATCH	
		APPLICATION SPEC	108-40018	
		SIZE	CAGE CODE	DRAWING NO
		WEIGHT	—	5499786
		CUSTOMER DRAWING	SCALE	4:1
		SHEET	1	OF 1
		REV	E	