REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED

NOTES: UNLESS OTHERWISE SPECIFIED

1. CONSTRUCTION
   BODY & FITTINGS: BRASS. NICKEL PLATED.
   PIN: BRASS. GOLD PLATED.
   DIELECTRIC: TEFLON.
   HOUSING: MOLDED NYLON. AVAILABLE IN BLK.
   BANANA PLUG: BRASS. NICKEL PLATED.
   HARDWARE: STAINLESS STEEL SCREW.

2. PERFORMANCE:
   MAXIMUM CURRENT: XX
   MAXIMUM VOLTAGE: 500 VRMS
   MAXIMUM TEMPERATURE: 122°F (50°C)



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS ± DECIMALS .XX ± .XXX ± ANGLES ±	CONTRACT NO.	E-Z-HOOK® DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.
			APPROVALS / DATE	
			DRAWN R.L. 1/11	DESCRIPTION
		MATERIAL SEE NOTE.	APPROVED BY	BNC FEMALE TO STD DBL BAN PLUG ADAPTER
		FINISH SEE NOTE.		SIZE A / CODE IDENT NO. 08505 / DRAWING NO. 9225 / REV.
NEXT ASSY	USED ON			
APPLICATION		DO NOT SCALE DRAWING		SCALE 1:1 / SHEET 1 OF 1

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-Z-HOOK. THE INFORMATION IS NOT TO BE REPRODUCED WITHOUT PRIOR WRITTEN PERMISSION OF E-Z-HOOK, DIV. OF TEKTEST INC.
MAXIMUM TESTED RATINGS IN A HANDS-FREE CONTROLLED ENVIRONMENT. MAXIMUM RATINGS ARE NOT TO BE USED CONCURRENTLY.