THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT – By – ALL RIGHTS RESERVED.

MATED WITH:
PASSEND ZU:

| PROJECT NR.: | LOC | DIST |
|---|---|---|
| 98-52190 | AI | – |

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|---|---|---|---|---|
| | B8 | ECR-14-010853 | 18JUL2014 | Joas | Gilch |







Kodierung A
CODING A




Kodierung B
CODING
2:1




Kodierung C
CODING
2:1




Kodierung D
CODING
2:1




Kodierung E
CODING
2:1




Kodierung F
CODING
2:1




Kodierung Z
CODING
2:1






















| | | | | | | | |
|---|---|---|---|---|---|---|---|
| 7-967640-3 | B | A | 4 | 1 | Schutzkappe/PROTECTIVE COVER | PBT-GF10 | gelb/YELLOW |
| | | | 3 | 1 | Dichtung/SEALING | MVQ-30 | natur/NATURAL |
| | | | 2 | 1 | 2.Kont.sichrg./RETAINER | PBT-GF15 | gruen/GREEN |
| | | | 1 | 1 | Buchsengeh./SOCKET HSG. | PBT-GF15 | schwarz/BLACK |
| 9-967640-1 | B | Z | 4 | 1 | Schutzkappe/PROTECTIVE COVER | PBT-GF10 | schwarz/BLACK |
| | | | 3 | 1 | Dichtung/SEALING | MVQ-30 | natur/NATURAL |
| | | | 2 | 1 | 2.Kont.sichrg./RETAINER | PBT-GF15 | gruen/GREEN |
| | | | 1 | 1 | Buchsengeh./SOCKET HSG. | PBT-GF15 | wasserblau/WATER-BLUE |
| – | – | F | 4 | 1 | Schutzkappe/PROTECTIVE COVER | PBT-GF10 | schwarz/BLACK |
| | | | 3 | 1 | Dichtung/SEALING | MVQ-30 | natur/NATURAL |
| | | | 2 | 1 | 2.Kont.sichrg./RETAINER | PBT-GF15 | gruen/GREEN |
| | | | 1 | 1 | Buchsengeh./SOCKET HSG. | PBT-GF15 | braun/BROWN |
| – | – | E | 4 | 1 | Schutzkappe/PROTECTIVE COVER | PBT-GF10 | schwarz/BLACK |
| | | | 3 | 1 | Dichtung/SEALING | MVQ-30 | natur/NATURAL |
| | | | 2 | 1 | 2.Kont.sichrg./RETAINER | PBT-GF15 | gruen/GREEN |
| | | | 1 | 1 | Buchsengeh./SOCKET HSG. | PBT-GF15 | gruen/GREEN |
| – | – | D | 4 | 1 | Schutzkappe/PROTECTIVE COVER | PBT-GF10 | schwarz/BLACK |
| | | | 3 | 1 | Dichtung/SEALING | MVQ-30 | natur/NATURAL |
| | | | 2 | 1 | 2.Kont.sichrg./RETAINER | PBT-GF15 | gruen/GREEN |
| | | | 1 | 1 | Buchsengeh./SOCKET HSG. | PBT-GF15 | gelb/YELLOW |
| 3-967640-1 | B | C | 4 | 1 | Schutzkappe/PROTECTIVE COVER | PBT-GF10 | schwarz/BLACK |
| | | | 3 | 1 | Dichtung/SEALING | MVQ-30 | natur/NATURAL |
| | | | 2 | 1 | 2.Kont.sichrg./RETAINER | PBT-GF15 | gruen/GREEN |
| | | | 1 | 1 | Buchsengeh./SOCKET HSG. | PBT-GF15 | blau/BLUE |
| 2-967640-1 | B | B | 4 | 1 | Schutzkappe/PROTECTIVE COVER | PBT-GF10 | schwarz/BLACK |
| | | | 3 | 1 | Dichtung/SEALING | MVQ-30 | natur/NATURAL |
| | | | 2 | 1 | 2.Kont.sichrg./RETAINER | PBT-GF15 | gruen/GREEN |
| | | | 1 | 1 | Buchsengeh./SOCKET HSG. | PBT-GF15 | grau/GREY |
| 1-967640-1 | B | A | 4 | 1 | Schutzkappe/PROTECTIVE COVER | PBT-GF10 | schwarz/BLACK |
| | | | 3 | 1 | Dichtung/SEALING | MVQ-30 | natur/NATURAL |
| | | | 2 | 1 | 2.Kont.sichrg./RETAINER | PBT-GF15 | gruen/GREEN |
| | | | 1 | 1 | Buchsengeh./SOCKET HSG. | PBT-GF15 | schwarz/BLACK |
| TE CONNECTIVITY BESTELL-NR. ORDER NO. | REV. | KOD. COD. | POS. | STK. QTY. | BENENNUNG DESCRIPTION | MATERIAL | OBERFLAECHE SURFACE / FARBE/COLOUR |

Bemerkungen:
NOTES:

1. Massgebend ist der deutsche Text
ONLY THE GERMAN-LANGUAGE VERSION SHALL BE BINDING

2. Passend zu Buchsenkontakt fuer Einzelleiterdichtung:
SUITABLE FOR SOCKET CONTACT FOR SINGLE WIRE SEALING:
AMP 962885 (DGB 0.2-0.5mm²), 965906 (DGB 0.75mm²)

B1 3. Passend zu Kragenanschluss siehe Zeichnung:
SUITABLE FOR SHROUDED CONNECTION SEE DRAWING:
AMP 114-18063-124
auch passend zu AMP 114-18063-14
ALSO COMPATIBLE TO AMP 114-18063-14

4. Passend fuer Leitungsquerschnitt:
bis 0.75 mm²
SUITABLE FOR WIRE SIZE RANGE:
TO 0.75 mm²

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± 2°

MATERIAL: SEE TABLE
FINISH: SEE TABLE

n. ISO 8015
n. DIN 16901 – 140

DWN 08-AUG-96 M.Trajkov
CHK 31-AUG-98 M.Schwaeger
APVD –
PRODUCT SPEC 108-18272-0
APPLICATION SPEC 114-18061
WEIGHT 3.1

TE Connectivity

NAME: MQS SOCKET HOUSING, SWS, 4POS. ASS'Y
MQS Buchsengeh., EDS, 4pol., kompl.

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A1 | 00779 | C-967640 | – |

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 | REV B8

4805 (3/11)