Medium and Heavy Duty Toggle Switches (AC/DC)



These switches have contacts with a quick-make/quick-break wiping action. The three-position switches offer a unique positive center stop feature, which assures that the lever cannot be thrown from one side through the center "Off" position without stopping. This design feature is a major factor in the widespread acceptance of these switches for motor reversing and speed control applications. Copper and bronze contacts are standard, as well as brass screw terminals.

5

Stock No.	Mfr.'s Type	Circuit	Amps		EACH		
			125 V	250 V	1-24	25-49	50-99
757-5046	7402K5*	DPST	20 A	20 A (2 Hp)	**18.91**	**16.67**	**14.56**
757-5048	7814K2†	DPDT	14 A	7 A (3/4 Hp)	**60.62**	**59.95**	**59.27**

Action: *Off-On (ball); †On-Off-On.

Jan-S-23 Heavy-Duty Toggle Switches



Single Pole



Double Pole

15 A @ 125 VAC, 20 A @ 30 VDC. 15 A @ 30 VDC for momentary action. Solder lug terminals. All are single throw except * which indicates double throw. **Weight:** 2 oz.

Single Pole

Stock No.	Mfr.'s Type	JAN No. ST-	Action (Momentary)	EACH		
				1-24	25-49	50-99
757-3421	7300K38	42A	On-None-Off	**10.69**	**9.14**	**8.57**
757-3424	7302K38	42D	On-None-On	**11.17**	**10.13**	**9.12**
757-3425	7301K38*	42E	On-Off-On	**11.85**	**10.75**	**9.68**
757-9427	7306K38*	42G	(On)-Off-(On)	**13.49**	**12.25**	**11.03**
757-9428	7305K38*	42H	On-Off-(On)	**13.49**	**12.25**	**11.03**

Double Pole

757-3521	7310K38	52K	On-None-Off	**14.27**	**12.89**	**11.66**
757-3522	7312K38*	52N	On-None-On	**15.63**	**14.24**	**12.89**
757-3523	7311K38*	52P	On-Off-On	**14.72**	**13.43**	**12.14**
757-3525	7317K38*	52R	On-None-(On)	**16.41**	**14.97**	**13.55**
757-7910	7316K38*	52S	(On)-Off-(On)	**17.22**	**15.96**	**14.21**
757-9527	7315K38*	52T	On-Off-(On)	**17.24**	**15.54**	**14.23**

*Double throw.

AC Rated Toggle Switches



Single Pole



Double Pole

Single Pole

Stock No.	Mfr.'s Type	Action	Amps @		HP @ 250 VAC	Terminals	EACH	
			125 V	250 V			1-24	25-49
757-4885	7580K4	On-Off	6	3	—	Screw	**3.36**	**2.89**
757-4888	7580K7*	On-Off	6	3	—	Solder	**3.05**	**2.56**
757-4887	7580K6†	On-Off	6	3	—	Solder	**3.05**	**2.61**
757-4001	7500K14	On-Off	15	10	3/4	Screw	**3.63**	**3.01**
757-4021	7501K13	On-Off	15	10	3/4	Solder	**2.96**	**2.52**
757-4022	7501K15	On-Off	15	10	3/4	.250 Spade	**3.22**	**2.70**
757-4201	7504K4	On-On	15	10	3/4	Screw	**4.64**	**3.86**
757-4070	7502K13	On-Off-On	15	10	3/4	Screw	**4.64**	**3.98**
757-4270	7509K5	On-Off-On	—	10	1/2	Screw	**6.38**	**5.44**

Double Pole

757-4940	7590K4	On-Off	6	3	—	Screw	**5.46**	**4.67**
757-4942	7590K6	On-Off	6	3	—	Solder	**5.61**	**4.65**
757-4500	7560K5	On-Off	15	10	3/4	Screw	**6.44**	**5.38**
757-4560	7561K4	On-Off	15	10	3/4	Solder	**5.53**	**4.62**
757-5006	7592K6	On-On	6	3	—	Solder	**5.29**	**4.41**
757-4760	7564K6	On-On	15	10	3/4	Screw	**7.46**	**6.38**
757-4805	7565K5	On-On	15	10	3/4	Solder	**6.07**	**5.20**
757-4807	7565K7	On-On	15	10	3/4	.250 Spade	**6.07**	**5.20**
757-4970	7591K4	On-Off-On	6	3	—	Screw	**6.44**	**5.51**
757-4590	7562K4	On-Off-On	15	10	3/4	Screw	**8.86**	**7.37**
757-4720	7563K4	On-Off-On	15	10	3/4	Solder	**6.07**	**5.20**

*Bushing = 0.344". †Bushing = 0.469".

AC-DC Rated Toggle Switches



Single Pole 2-Position Switches



Double Pole 2-Position Switches

Quick-make, quick-break contact with wiping action. Arc-resistant. 5/32" diameter bushing; mounting hardware included. UL and CSA listed. All have 11/32" bushing length, except * have 15/32". **Weight:** 2 oz.

Single Pole 2-Position Switches

Stock No.	Mfr.'s Type	Action	Amps @		Terminals	EACH	
			125 V	250 V		1-24	25-49
757-6302	8280K115	On-Off	—	3	Solder	**4.08**	**3.38**
757-6555	8295K107	On-Off	—	3	Screw	**5.36**	**4.58**
757-7040	8381K107	On-Off	6	3	Solder	**4.20**	**3.60**
757-7097	8396K108*	On-Off	6	3	Screw	**4.92**	**4.21**
757-7096	8396K107	On-Off	6	3	Screw	**5.84**	**4.85**

*15/32" bushing.

Double Pole 2-Position Switches

Stock No.	Mfr.'s Type	Action	Amps @		Terminals	EACH	
			125 V AC-DC	250 V DC		1-24	25-49
757-6840	8370K107*	On-Off	6	3	Solder	**7.32**	**6.27**
757-6895	8372K107*	On-Off	6	3	Screw	**8.85**	**7.72**
757-6910	8373K107*	On-On	7	3	Solder	**8.48**	**7.16**

*15/32" bushing.

MIL-S-83731 Lever Seal Switches



Single Pole



Double Pole

Lever Seal Toggle. Tinned screw terminals, except *. Solder lug. All are single throw except † which indicates double throw. **Weight:** 2 oz.

Single Pole

Stock No.	Mfr.'s Type	Gov't. MS No.	Action (Momentary)	EACH		
				1-24	25-49	50-99
757-3822	8261K22*	25098-22	On-None-Off	**26.28**	**20.22**	**19.72**
757-8701	8801K22	35058-22	On-None-Off	**12.93**	**11.54**	**10.57**
757-8680	8800K16†	35058-21	On-Off-On	**13.30**	**11.99**	**10.98**
757-8750	8810K15†	35058-23	On-None-On	**14.35**	**12.95**	**11.84**
757-8770	8812K14†	35058-27	(On)-Off-(On)	**16.05**	**14.38**	**13.10**

Double Pole

757-8845	8820K16†	35059-21	On-Off-On	**19.80**	**18.05**	**16.34**
757-8855	8822K20	35059-22	On-None-Off	**18.33**	**16.50**	**15.12**
757-8869	8824K14†	35059-23	On-None-On	**19.22**	**17.32**	**15.86**
757-8904	8834K5†	35059-27	(On)-Off-(On)	**26.38**	**23.76**	**21.76**

*Solder lug terminals. †Double throw.