




D-SUBMINIATURE CONNECTORS:

K86X Series

High Density Vertical PCB Mount and Solder Cup

K86X Series Dimensions

Dimensions in mm



Number of Contacts (Shell Size)	Dimensions (Inch/mm)					
	A	A1	B	C	D	E
15 (E)	.643	.666	.984	1.213	.090	.010
	16.33	16.92	24.99	30.81	2.29	0.25
26 (A)	.971	.994	1.312	1.541	.090	.020
	24.66	25.25	33.32	39.14	2.29	0.51
44 (B)	1.511	1.534	1.852	2.088	.090	.020
	38.38	38.96	47.04	53.04	2.29	0.51
62 (C)	2.159	2.182	2.500	2.729	.094	.023
	54.84	55.42	63.50	69.32	2.41	0.58

A = Exterior of Female Shell (S)

A1 = Interior of Male Shell (P)

2D Drawing

IGES

STEP

3D PDF

Solder Profile

CofC RoHS Compliant

CofC REACH Compliant

UL Plastic File

Certificate of Origin

Check Stock

Request a Sample

Send Us An Email

Generated Part Number

Part Number Builder

	-					
Series		Shell Type	Pin Type	Contact Option	Contact Type	Mounting Option
						Plating Option

Series

K86X - D-Subminiature Vertical Connector

Contact Shell Size

E - 15 Contacts

A - 26 Contacts

B - 44 Contacts

C - 62 Contacts

Contact Construction, Pin Type

A - Precision Formed, Solder Cup (Not Available with BR/BRJ)

D - Precision Formed, Vertical Pin (PCB Mount)

Contact Type

P - Pin Contact (Plug)

S - Socket Contact (Receptacle)

Mounting Option

Blank - Through Hole

BR - #4-40 Threaded Boardlocks

BRJ - #4-40 Threaded Boardlocks and #4-40 Jackscrews Installed

K - #4-40 Threaded Bushings

KJ - #4-40 Bushings and #4-40 Jackscrews

Plating Option

Blank - Gold Flash

30 - 30μ" Gold

Contact Kycon for Other Options