1520230 -9 Product Details

No Image Available

1520230 -9

Active

Power Toggle Switches

Not Reviewed for ELV/RoHS Compliance

Product Highlights:

- Double Pole - Single Throw Configuration (Pole -Throw)
- Toggle Length = 20.62 mm
- Toggle Style = Baton
- Bushing Length = 11.91 mm
- Termination Type = Screw -In Terminal

View all Features

Quick Links

Check Pricing & Availability
Search for Tooling
Product Feature Selector
Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- Customer Drawing (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

List all Documents

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Configuration (Pole -Throw) = Double Pole - Single Throw
- Termination Type = Screw -In Terminal

Electrical Characteristics:

- UL/CSA 250V Current Rating (Amps.) = 20
- UL/CSA 125V Horse Power Rating (hp) = 1.50
- UL/CSA 250V Horse Power Rating (hp) = 2.00

Housing Related Features:

- Toggle Length (mm [in]) = 20.62 [0.812]
- Toggle Style = Baton

Configuration Related Features:

- Bushing Length (mm [in]) = 11.91 [0.469]

Industry Standards:

- RoHS/ELV Compliance = Not reviewed for ELV/RoHS compliance
- Lead Free Solder Processes = Not reviewed for lead free solder process

Other:

- Brand = Alcoswitch

© 2007 Tyco Electronics Corporation All Rights Reserved