




LOC	DIST	P	F	REVISIONS		
				ZONE	LTR	DESCRIPTION
FT	4				G	REDRAW ON CAD
					H	OBS -1 PER EC 0020-0394-93
					J	REACTIVATE -1
						PER EC 0G1C-0002-99
						DATE
						APPD



RECOMMENDED PANEL CUTOUT

- 1 CAVITY IDENTIFICATION CHARACTERS ON FRONT AND REAR FACE.
2. RECEPTACLE WILL ACCEPT 3 TYPE XII SOCKET CONTACTS.
3 5.08µm [.000200] MIN NICKEL OVER 10.16µm [.000400] MIN COPPER.

YES	208497-2
NO	208497-1
PERIPHERAL SEAL	PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.13[.005] 3 PLC DEC ± - ANGLES ± - MATERIAL RECEPTACLE: NYLON, BLACK RCPT SHELL: ZINC PERIP SEAL: ELASTOMER, GREY PIN: CARBON STEEL FINISH RCPT SHELL: 3 PIN: NICKEL PLATED	DR 1-29-92 W.G.LENKER CHK 2-11-92 R.STONE APPD 2-12-92 K.BEAVER APPD 2-12-92 C.ROHDE PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	AMP AMP Incorporated Harrisburg, PA 17105-3608		
		NAME	RECEPTACLE ASSEMBLY, 22-3, REV SEX, CMC	
		SIZE	CAGE CODE	DRAWING NO
		C	00779	208497
		SCALE	2:1	SHEET 1 OF 1