



The CA178 cable assemblies offered by Laird are engineered for peak performance up to 6 GHz. They are tested 100% and certified to meet performance specifications. Equipment manufacturers require certified cable assemblies to minimize system losses to within known parameters and these cable assemblies meet those requirements. The manufacturing processes and raw materials are well controlled in order to provide very consistent performance from lot to lot.



FEATURES

- Consistent low loss design construction
- 100% tested and certified to meet specifications
- Various connector options available
- Flexible high temperature kink resistant cable jacket

MARKETS

- High performance wireless systems
- OEM equipment
- WiMAX

INSERTION LOSS BY FREQUENCY



PARAMETER	CA178-NFB-UFL-8	CA178-NFB-UFL-12
Insertion loss (700-5825 MHz)	-1.5 dB max	-2.5 dB max
Length	8 in (203 mm)	12 in (305 mm)
Weight	1.4 oz (40 gm)	1.5 oz (43 gm)
Connector types	N female bulkhead - UFL	N female bulkhead - UFL
N connector seal	O-ring	O-ring
Contact plating	Gold	Gold
Operating temperature	-40 to +125°C	-40 to +125°C

SYSTEM ORDERING

CA178-NFB-UFL-8	N Female Bulkhead to U.FL 8 in
CA178-NFB-UFL-12	N Female Bulkhead to U.FL
CA178-NM-UFL-8	12 in N Male to U.FL 8 in
CA178-NM-UFL-12	N Male to U.FL 12 in

Americas: +1.847 839.6907
IAS-AmericasEastSales@lairdtech.com

Europe: +44.1628.858941
IAS-EUSales@lairdtech.com

Asia: +86.21.5855.0827.127
IAS-AsiaSales@lairdtech.com

www.lairdtech.com

PART NUMBER	CONNECTOR 1	CONNECTOR 2	CABLE LENGTH (INCHES)	CABLE TYPE	MAX INSERTION LOSS (DB)
CA100-NFB-MC-12	N female bulkhead	MC-card	12	LMR100 (equivalent)	1.5
CA100-NFB-MMCX-12	N female bulkhead	MMCX	12	LMR100 (equivalent)	1.5
CA100-NFB-RASMAM-12	N female bulkhead	Right angle SMA male	12	LMR100 (equivalent)	1
CA100-NFB-RMMCX-12	N female bulkhead	Reverse polarity MMCX	12	LMR100 (equivalent)	1.5
CA100-NFB-RSMAM-12	N female bulkhead	Reverse polarity SMA male	12	LMR100 (equivalent)	1
CA100-NFB-RTNCM-12	N female bulkhead	Reverse polarity TNC male	12	LMR100 (equivalent)	1
CA100-NFB-SMAM-8	N female bulkhead	SMA male	8	LMR100 (equivalent)	0.8
CA100-NM-MC-12	N male	MC-card	12	LMR100 (equivalent)	1
CA100-NM-MMCX-12	N male	MMCX	12	LMR100 (equivalent)	1
CA100-NM-RASMAM-12	N male	Right angle SMA male	12	LMR100 (equivalent)	1
CA100-NM-RSMAM-12	N male	Reverse polarity SMA male	12	LMR100 (equivalent)	1
CA100-NM-RTNCM-12	N male	Reverse polarity TNC male	12	LMR100 (equivalent)	1
CA100-RPSMAM-RASMAM-12	Reverse polarity SMA male	Right angle SMA male	12	LMR100 (equivalent)	1
CA100-RPTNCF-NC-6	Reverse polarity TNC female bulkhead	No connector	6	LMR100 (equivalent)	0.5
CA100-RPTNCM-RASMAM-12	Reverse polarity TNC male	Right angle SMA male	12	LMR100 (equivalent)	1
CA100-TNCF-NC-6	TNC female bulkhead	No connector	6	LMR100 (equivalent)	0.5
CA178-NFB-UFL-12	N female bulkhead	U.FL	12	RG178 hi freq	2
CA178-NFB-UFL-8	N female bulkhead	U.FL	8	RG178 hi freq	1.5
CA178-NM-UFL-12	N male	U.FL	12	RG178 hi freq	2
CA178-NM-UFL-8	N male	U.FL	8	RG178 hi freq	1.5
CA178-RTNCB-MMCX-4	Reverse polarity TNC bulkhead (black)		4	RG178 hi freq	0.8
CA178-RTNCB-MMCX-6	MMCX Reverse polarity TNC bulkhead		6	RG178 hi freq	1
CA178-RTNCB-UFL-6	(black) MMCX Reverse polarity TNC		6	RG178 hi freq	1
CA400-NM-NM-48	N male bulkhead (black) U.FL	N male	48	LMR400 (equivalent)	0.8
CA58-NM-MCX-197	N male	MCX	197	RG58/u (white)	5
CA58-SMA-MCX-96	Right angle SMA male	MCX	96	RG58/u (white)	2.5
CA58-SMA-NF-96	Right angle SMA male	N female bulkhead	96	RG58/u (white)	2.5
CA58-SMA-RSMA-96	Right angle SMA male	Reverse polarity SMA male	96	RG58/u (white)	2.5
CA58-SMA-RTNC-96	Right angle SMA male	Reverse polarity TNC male	96	RG58/u (white)	2.5
CA58-SMA-SMAF-96	Right angle SMA male	SMA female bulkhead	96	RG58/u (white)	2.5

Americas: +1.847 839.6907
IAS-AmericasEastSales@lairdtech.com

Europe: +44.1628.858941
IAS-EUSales@lairdtech.com

Asia: +86.21.5855.0827.127
IAS-AsiaSales@lairdtech.com

www.lairdtech.com

ANT-DS-CA178 0115

Any information furnished by Laird Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird materials rests with the end user, since Laird and its agents cannot be aware of all potential uses. Laird makes no warranties as to the fitness, merchantability or suitability of any Laird materials or products for any specific or general uses. Laird shall not be liable for incidental or consequential damages of any kind. All Laird products are sold pursuant to the Laird Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2015 Laird Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Logo, and other marks are trademarks or registered trademarks of Laird Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird or any third party intellectual property rights.