


LOC	DIST	REVISIONS					
E	B	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B1	ECO-10-021614	200CT10	Titong Se	

NOTES

- 1 SINGLE PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2 50 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3 Au PLATING OVER Cu PLATING
- 4 Ag PLATING OVER Cu PLATING
- 5 Ni PLATING OVER Cu PLATING
6. CHARACTERISTICS
FREQUENCY RANGE: DC-11.0GHz
IMPEDANCE: 50 OHMS
WORKING VOLTAGE: 1000V MAX AT SEA LEVEL
DIELECTRIC WITHSTAND VOLTAGE: 2500V RMS MAX
TEMPERATURE RATE: -55°C TO +165°C
7. MECHANICAL CHARACTERISTICS
DURABILITY: 500 CYCLES MIN
8. FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
9. ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



				-	-	1	1	BRASS	5	△	BODY	5
				1	1	-	-	BRASS	5	△	BODY	5
				-	-	1	1	BRASS	4	△	FLANGE	4
				1	1	-	-	BRASS	4	△	FLANGE	4
				1	1	-	-	BRASS	3	△	CONTACT	3
				-	-	1	1	BRASS	3	△	CONTACT	3
				1	1	1	1	PTFE	2		INSULATOR	2
				-	-	1	1	BRASS	1	△	BODY	1
				1	1	-	-	BRASS	1	△	BODY	1
				6--1	1--1	6--0	1--0	MATERIAL			DESCRIPTION	ITEM
				△	△	△	△					
QUANTITY PER ASSY								PARTS LIST				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH

SEE TABLE

DWN J.SANDWELL 01DEC04
CHK S.PARLOW 01DEC04
APVD F.WHEELER-KING 01DEC04
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

Tyco Electronics Corporation
Bideford, UK, EX39 4HE

NAME
N TYPE ADAPTER PANEL MOUNT JACK

SIZE A3
CAGE CODE 00779
DRAWING NO C-1814407
RESTRICTED TO -

CUSTOMER DRAWING

SCALE NTS
SHEET 1 OF 1
REV B1