| LTR. | REV. | DESCRIPTION | DATE |
|---|---|---|---|
| | A | FIRST ISSUE | 2011.1.23 |












Connecting

| P1 | 568B COLOR | P2 |
|---|---|---|
| 1 | WH/ORG | 1 |
| 2 | ORG | 2 |
| 3 | WH/GRN | 3 |
| 4 | BLU | 4 |
| 5 | WH/BLU | 5 |
| 6 | GRN | 6 |
| 7 | WH/BWN | 7 |
| 8 | BWN | 8 |



SPECIFICATIONS:

1. CONDUCTOR:
   1.1 CONDUCTORS: 26AWG 7*0.155± 0.015mm
1.2 CONDUCTOR INSULATION COLOR CODING: ONE WHITE/ORANGE,ONE ORANGE,ONE WHITE/GREEN,ONE GREEN, ONE BLUE,ONE WHITE/BLUE,ONE WHITE/BROWN,ONE BROWN.
2. CABLE JACKET
2.1 PRINTING ON THE JACKET: Maxxtro Patch Cable FTP CAT.5E 26AWG ISO/IEC 11801
3. CABLE ASSEMBLY
   3.1 SEE SECTION A-A FOR DIMENSIONS
   3.2 CABLE TIE: **Assorted upon request**
   3.3 WIRING T568B COLOR
   3.4 CONTACT PLUG: RJ45 8P8CS 15u pc UL 94V-2
4. CABLE JACKET COLOR: GYEY 687#;RED 172#;BLUE 567#;YELLOW 361#;GREEN 273#;BLACK 063#;WHITE 461#;ORANGE 760#;PINK 171#;PURPLE 964#
   5. LENGTH:L± 3%mm

| ITEM No. | LENGTH | PVC COLOR | PACKING |
|---|---|---|---|
| 102011 | 600 ± 20MM | GREY 687# | BLISTER |
| 102016 | 1000 ± 20MM | GREY 687# | BLISTER |
| 102017 | 1000 ± 20MM | BLUE 567# | BLISTER |
| 102076 | 5000 ± 110MM | YELLOW 361# | BLISTER |

| REMARK | NO | CHA.NO | SIGNATURE | DATE |
|---|---|---|---|---|
| DRAWN BY | Morgan | | | |
| CHECKED BY | 宋巧 | | | |
| AUDITED BY | 缪传友 | APPROVED BY | 祁玉军 | |
| CRAFT | | DATE | 2011.1.23 | |

SIGN | REV. A | SCALE

PAGE OF

Maxxtro®

FTP CAT5e CABLE 26AWG