No.	Stock Code	Description
1	4155221	D Sub Solder Plug 9 Way
2	4155233	D Sub Solder Plug 15 Way
3	4155245	D Sub Solder Plug 25 Way
4	4155257	D Sub Solder Plug 37 Way
5	4155269	D Sub Solder Plug 50 Way

1	2	3	4

POSITIONS	A	B	C±0.5	D	E
9	16.92	24.99	30.81	8.38	12.50
15	25.25	33.32	39.14	8.38	12.50
19	30.60	38.86	44.80	8.38	12.50
23	35.90	44.30	50.30	8.38	12.50
25	38.96	47.04	53.04	8.38	12.50
37	55.42	63.50	69.32	8.38	12.50
50	52.81	61.11	66.93	11.07	15.37

HOW TO ORDER

5501-XXPA-XX-XX

- 01:GOLD PLATED
- 02:SELECTIVE GOLD
- CS:REAR RIVET
- CC:FRONT RIVET
- BLANK:STANDARD
- PA:STAMP PIN MALE
- NO. OF POSITIONS

SPECIFICATIONS:
CONTACT RESISTANCE: 30MΩ MAX. AT DC 100mA
INSULATOR RESISTANCE: 1000MΩ MIN. AT DC 500V
CURRENT RATING: 3 AMP

DIELECTRIC WITHSTANDING:
VOLTAGE: AC 1000V FOR 1 MINUTE
OPERATING TEMPERATURE: -55°C~+105°C
CONTACT: BRASS
HOUSING: PBT & 30% GLASS FIBER (UL 94V-0)
UL FILE NO:E144392











REV	DATE	FILE	BY
E			
D			
C			
B			
A	10-06-2000	5501-XXPA-XX-XX	Jerry Chen

DRAWN: Jerry Chen

CHECKED: Peter Huang

GENERAL TOLERANCE: ±0.2

UNIT: MM

SCALE:

SHEET: 1 / 1

PROJECTION:

NELTRON INDUSTRIAL CO.,LTD

DESCRIPTION: D-SUB SOLDER MALE

PART NO: 5501-XXPA-XX-XX

SIZE A4

A B C D