PRO-LITE

Product Data Specification

PRO-LITE - 50-150VA Electronic Transformer

FEATURES

- Dimmable
- Highly efficient
- EMC Approved
- Short circuit, over-load and surge protected
- Thermal cut-off
- RoHS compliant
- Ambient temperature Ta. Max: 50˚C
- Case temperature Tc. Max: 70˚C

TESTED ACCORDING TO

- EN61347-2-2:2001
- EN61347-1:2001
- EN55015:2000/A1:2001
- EN61547:1995/A1:2000
- EN61000-3-3:2000
- EN61000-3-3:1995/+A1:2001

PACKAGING WEIGHT = 10 g

PRODUCT WEIGHT = 350 g

BOX QTY = 50

PRODUCT DIMENSIONS = 225 x 55 x 43 mm

BOX DIMENSIONS = 285 x 465 x 230 mm

TECHNICAL SPECIFICATION

Product Code	Input Voltage	Input Current	Output Voltage	Usage	IP Rating
TRANS-150VA/PROL	220-240V 50Hz	0.625A	11.6V	Indoor	IP20

SELV

© Ritelite (Systems) Ltd, Meadow Park, Bourne Road, Essendine, Stamford, Lincs PE9 4LT
Tel. 01780 765600 Fax. 01780 765700 Web: www.ritelite.co.uk E-mail: sales@ritelite.co.uk

All rights reserved. All reasonable precautions are taken to ensure that advice and data are reliable. We cannot guarantee it and we cannot accept responsibility for it. Errors and execepted omissions.