

BNC Adapters

These sturdy within-series BNC adapters are available in all standard designs. Additionally, several unique constructions compliment the product group and allow adaptations for every conceivable application. All connector bodies are plated with bright nickel. Male contacts are brass, female contacts are phosphor bronze. All contacts are plated with 5 micro inches of gold.

Part Number	RoHS	Description	Fig. No.
330A505	✓	Male/ Male Inline Barrel Splice	35
332A505	✓	Female/Female Inline Splice	36
335A544	✓	Female/Female Inline Bulkhead Mount (Grounded)	37
335R544	✓	Female/Female Inline Isolated Bulkhead (Metal Outer Thread)	37
343A205F	✓	Crimp “T” Adapter for RG58 Cable	41
343A205G	✓	Crimp “T” Adapter for RG59, 62 Cables	41
343A505	✓	Female/Male/Female “T” Adapter (Yes, it runs with Netware™)	38
345A505	✓	Female/Female/Female “T” Adapter	39
351A505	✓	Female/Male Right Angle Adapter	40
383U505	✓	The Goalie™	42
383U205F	✓	The Goalie Brute™ Crimp Version for RG58 Cable	45
383U205G	✓	The Goalie Brute™ Crimp Version for RG59, 62 Cables	45
383K505*	✓	The Goalie Brute™	43
383P505*	✓	The Insulated Goalie	44
353U205F*	✓	Male/Female/Female Right Angle Double-Down™Crimp for RG58	49
353U205G*	✓	Male/Female/Female Right Angle Double-Down™ Type for RG59	49
353U505*	✓	Male/Female/Female Right Angle Double-Down™	48
393U205F*	✓	Male/Female/Female Straight Double-Down™Crimp for RG58	47
393U205G*	✓	Male/Female/Female Straight Double-Down™Crimp for RG59	47
393U505*	✓	Male/Female/Female Straight Double-Down™	46

✓RoHS compliant




Fig. 38




Fig. 39




Fig. 40




Fig. 42




Fig. 43




Fig. 44




Fig. 35




Fig. 36




Fig. 37




Fig. 41




Fig. 49




Fig. 48




Fig. 46




Fig. 45




Fig. 47