

**3F01-140****F6-1798 (1 per pack)****SNAP DISC FAN CONTROLS**

For Regulation of Fan or Blower Control

FEATURES

- Designed for quick on-job replacement.
- Easy to remember type numbers — “L” for Limit — “F” for Fan.
- Last three numbers indicate cut-out temperatures on limits and cut-in temperatures on fan controls.
- Mounting holes match standard 3/4" snap discs.
- Tab-to-screw terminal adapters furnished.

SPECIFICATIONS

Maximum ambient 350°F

ELECTRICAL RATINGS

Model	Motor Rating (Full Load)		Resistive (Non-Inductive)		Pilot Duty
	120VAC	240VAC	120/240VAC	277VAC	120/240/277VAC
3F01, 3F02	10.0A	5.0A	25.0A	21.6A	125 VA

PARTS AND ACCESSORIES

- F6-1798 Adapter plates (Order separately) — 1 per pack

FAN CONTROLS

Model Number	Fixed Temperature Settings		Switch Action	Therm-O-Disc	
	Cut-in	Cut-out		Style	Type
3F01-110	110°F (43°C)	90°F (32°C)	Close on Rise	60T12	610044
3F01-120	120°F (49°C)	110°F (43°C)	Close on Rise	60T12	610046
3F01-130	130°F (54°C)	115°F (32°C)	Close on Rise	60T12	610047
3F01-140	140°F (60°C)	120°F (32°C)	Close on Rise	60T12	610049
3F01-150	150°F (66°C)	130°F (32°C)	Close on Rise	60T12	610050
3F01-160	160°F (71°C)	140°F (32°C)	Close on Rise	60T12	610064
3F01-180	180°F (82°C)	160°F (32°C)	Close on Rise	60T12	610065
3F01-200	200°F (93°C)	180°F (32°C)	Close on Rise	60T12	610066
3F01-350	350°F (177°C)	320°F (32°C)	Close on Rise	60T12	610067