

N=Number of contacts



NOTES:

MATERIAL
1.Item ② Contact pin: Brass(CuZn)Tin plated
2.Item ① Insulator (housing):Thermoplastic (UL 94V-0),green
ELECTRICAL
1.Current Rating : 20A
2.Voltage Rating : 300V
3.Withstand Voltage : 1.6KV
ENVIRONMENTAL
1.Soldering Temperature: 250°C ±10°C/5 Sec
2.Operating Temperature: -40°C to +115°C
3.Safety approval: c us



Recommended PCB Layout

RoHS compliant

Scale	1:1						Date	Name
TOLERANCE						Drawn	19.03.2009	Dean
X.	±0.50					Approved	19.03.2009	Hellwig
X.X	±0.30							
X.XX	±0.10							
DIM	TOL							
X.°	±1°							
X.X°	±X°	①	Drawn	19.03.2009	Dean			
Angle	TOL	Id.	Modification	Date	Name			

Customer-No.

ASSMANN WSW-No.
A-TB762-OQXXCV

Drawing-No.
ASS 3419 CO

rev01

Replace

Sheet

ASSMANN WSW components

SV1387