



N = Number of contacts



NOTES

Material

1.Terminal body(contact pin): Brass(CuZn) Tin plated
2.Insulator (housing): Thermoplastic (UL94V-0)

④ Electrical cULus

1.Voltage rating: 300VAC
2.Current rating: 20A
3.Withstanding Voltage: 1.6KV
4.Operating temperature: -40°C to +115°C
5.Soldering temperature: 250°C±10°C/5 Sec
6.Safety Approval: c us

Order code:

A-TB508-OQxxCV-xx

No. of contact: 02-24Pin

Color of insulator
Blank: Green
BK: Black

P.C.B LAYOUT



RoHS compliant

Unit: mm

④ c US

File No.: E349947

Scale	1:1
TOLERANCE	
X.	±0.50
X.X	±0.30
X.XX	±0.10
DIM	TOL
X.°	±1°
X.X°	±X°
Angle	TOL

Id.	Modification	Date	Name
④	Update UL logo and notes	12.04.2022	Daniel
③	Add P/N	28.04.2021	Daniel
②	Update	09.01.2009	Amy
①	Drawn	04.05.2009	Dean

	Date	Name
Drawn	04.05.2009	Dean
Approved	12.04.2022	Daniel

ASSMANN WSW components

Customer-No.

ASSMANN WSW-No.
A-TB508-OQxxCV-xx

Drawing-No.
ASS 3502 CO

rev04

Replace

Sheet

SV1482