



# Flanged Spade Terminals

159-1630, 159-1636, 159-1638

KOBI CONN



Dimensions: In.

SPECIFICATIONS	
Type:	flanged spade
Acceptable wire size:	16~14AWG
Voltage:	600V max. @ 75°C
Current:	27A max.
Insulation:	vinyl
Material:	copper
Material thickness:	.031"
Insulation color:	blue
Stud size:	#6(159-1636), #8(159-1638), #10(159-1630)

Date Last Revised: 6-23-05

Available from Mouser Electronics  
1-800-346-6873  
[www.mouser.com](http://www.mouser.com)

KC-300736

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

159-1630 159-1638 159-1636