Search Results

Evaluate
- FAQ's
Design a Solution
- Catalog Cut Sheet
- PDF-CN3847018NU
- Part Drawings
- DXF-NET-ACCESS C
- DWG-NET-ACCESS C
- PDF-NET-ACCESS C
- Specification Sheets
- PDF-Net-Access E ..
How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor
Install & Maintain
- Installation Instructions
- PDF-Net-Access E ..

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'CN28'**

Your search criteria matched only one product, shown below

CN28

- Engineered to provide a best in class solution for Cisco Nexus 7010 switches
- Offered in both 42 RU and 45 RU heights to meet your data center's height requirement
- Cabinet ships assembled, one per pallet

Part Number	CN28
RoHS Compliancy Status	Compliant
Part Description	Net-Access™ Extended Switch Cabinet, front dual hinge door, rear perforated split doors, no side panels, #12-24 rails. Dimensions: 31.5"W x 48.9"D x 84"H (800mm x 1242mm x 2134mm) 45 RU
Material	Steel
Color	Black
Depth (In.)	48.9
Depth (mm)	1242
Height (In.)	84.0
Height (mm)	2134
Width (In.)	31.5
Width (mm)	800
No. of Rack Spaces	45
Pricing Description	Network Cabinet With Doors, 45 RU, Rails, 31.5"W x 48.9"D, Black
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy