


NUMBER C-5917628
METRIC
三角法 (3rd ANGLE PROJECTION)

PRINT DIST
単位: mm DIMENSIONS IN MM. DO NOT SCALE PRINT


AMP-J010-2C
REV. 3/93



注記:
① 材料:ハウジング;熱可塑性樹脂 (UL 94V-0) 色:黒
コンタクト:銅合金
② 表面仕上げ;
コンタクト:全面ニッケル下地めっき
接触部金めっき、脚部すずめっき
3. 本製品はフラックス上がり防止処理済み

NOTE:
① MATERIAL:HOUSING;THERMOPLASTICS (UL 94V-0) BLACK
CONTACT:COPPER ALLOY
② FINISH:CONTACT:Au AT CONTACT AREA
TIN AT TINE, OVER Ni
3. THESE PRODUCTS WERE COATED BY ANTI-FLUX MIGRATION AGENT.
④ OBSOLETE

鉛フリー
LEAD FREE



④	29	36.83	49	62.23	—	102.87	38.83	64.23	104.87	107.86	115.49	0.76µm	160	2	7
④	—	—	—	—	39	49.53	—	—	51.53	54.62	62.15	0.76µm	80	2	3
④	39	49.53	49	62.23	—	115.57	51.53	64.23	117.57	120.66	128.19	0.3µm	180	—	-8
④	29	36.83	49	62.23	—	102.87	38.83	64.23	104.87	107.86	115.49	0.3µm	160	—	-7
④	29	36.83	39	49.53	—	90.17	38.83	51.53	92.17	95.26	102.79	0.3µm	140	—	-6
④	19	24.13	39	49.53	—	77.47	26.13	51.53	79.47	82.56	90.09	0.3µm	120	—	-5
④	—	—	—	—	49	62.23	—	—	64.23	67.32	74.85	0.3µm	100	—	-4
④	—	—	—	—	39	49.53	—	—	51.53	54.62	62.15	0.3µm	80	—	-3
④	—	—	—	—	29	36.83	—	—	38.83	41.92	49.45	0.3µm	60	—	-2
④	—	—	—	—	19	24.13	—	—	26.13	29.22	36.75	0.3µm	40	—	-1
	a	A	b	B	c	C	D	E	F	G	H	THK OF GOLD	Pos.	P/N	

				TE Connectivity			
A REVISED PER ECR-12-013341 28MAR2013 K.M.E.T				AMP FH CONNECTOR RECEPTACLE (VERTICAL) FOR 8mm STACKING			
O RELEASED (FJBO-0582-04) 08JUN04 T.K.I.E				C-5917628			
LTR DESCRIPTION DATE DWN APVD				SHEET 1 OF 1			

包含電線断面積 (WIRE RANGE) mm² (AWG -)	被覆外径 (INSULATION DIA.) mmφ	名称 (NAME)
材料 (MATERIAL) ①	仕上 (FINISH) ②	一般公差 (GENERAL TOLERANCE)
CHK. I.ENOMOTO 09JUN04	APP. I.ENOMOTO 09JUN04	10以下: ±0.2 10以上 30以下: ±0.25 30以上 100以下: ±0.3 角 度: ±3°

尺度 (SCALE) NTS	REV. A	番号 (No.) C-5917628
----------------	--------	--------------------