




|     | 10             | 9                           | 8              | 7 | 6 | 5 | 4 | 3 | 2 | 1 |
|-----|----------------|-----------------------------|----------------|---|---|---|---|---|---|---|
| CKT | A              | B                           | SLOTS LOCATION |   |   |   |   |   |   |   |
| 02  | 4.93<br>.194   | 2.54±0.05<br>.100 ±.002     | NONE           |   |   |   |   |   |   |   |
| 03  | 7.47<br>.294   | 5.08 ± 0.10<br>.200 ±.004   | NONE           |   |   |   |   |   |   |   |
| 04  | 10.01<br>.394  | 7.62 ± 0.13<br>.300 ±.005   | NONE           |   |   |   |   |   |   |   |
| 05  | 12.55<br>.494  | 10.16 ± 0.13<br>.400 ±.005  | NONE           |   |   |   |   |   |   |   |
| 06  | 15.09<br>.594  | 12.70 ± 0.13<br>.500 ±.005  | 4, 5           |   |   |   |   |   |   |   |
| 07  | 17.63<br>.694  | 15.24 ± 0.13<br>.600 ±.005  | 4, 5           |   |   |   |   |   |   |   |
| 08  | 20.17<br>.794  | 17.78 ± 0.15<br>.700 ±.006  | 4, 5           |   |   |   |   |   |   |   |
| 09  | 22.71<br>.894  | 20.32 ± 0.15<br>.800 ±.006  | 4, 5           |   |   |   |   |   |   |   |
| 10  | 25.25<br>.994  | 22.86 ± 0.15<br>.900 ±.006  | 4, 5           |   |   |   |   |   |   |   |
| 11  | 27.79<br>1.094 | 25.40 ± 0.18<br>1.000 ±.007 | 4, 5<br>8, 9   |   |   |   |   |   |   |   |
| 12  | 30.33<br>1.194 | 27.94 ± 0.18<br>1.100 ±.007 | 4, 5<br>8, 9   |   |   |   |   |   |   |   |
| 13  | 32.87<br>1.294 | 30.48 ± 0.18<br>1.200 ±.007 | 4, 5<br>8, 9   |   |   |   |   |   |   |   |
| 14  | 35.41<br>1.394 | 33.02 ± 0.18<br>1.300 ±.007 | 4, 5<br>12, 13 |   |   |   |   |   |   |   |
| 15  | 37.95<br>1.494 | 35.56 ± 0.20<br>1.400 ±.008 | 4, 5<br>12, 13 |   |   |   |   |   |   |   |
| 16  | 40.49<br>1.594 | 38.10 ± 0.20<br>1.500 ±.008 | 4, 5<br>12, 13 |   |   |   |   |   |   |   |
| 17  | 43.03<br>1.694 | 40.64 ± 0.20<br>1.600 ±.008 | 4, 5<br>12, 13 |   |   |   |   |   |   |   |
| 18  | 45.57<br>1.794 | 43.18 ± 0.20<br>1.700 ±.008 | 4, 5<br>12, 13 |   |   |   |   |   |   |   |
| 19  | 48.11<br>1.894 | 45.72 ± 0.23<br>1.800 ±.009 | 4, 5<br>16, 17 |   |   |   |   |   |   |   |
| 20  | 50.65<br>1.994 | 48.26 ± 0.23<br>1.900 ±.009 | 4, 5<br>16, 17 |   |   |   |   |   |   |   |
| 21  | 53.19<br>2.094 | 50.80 ± 0.23<br>2.000 ±.009 | 4, 5<br>16, 17 |   |   |   |   |   |   |   |
| 22  | 55.73<br>2.194 | 53.34 ± 0.23<br>2.100 ±.009 | 4, 5<br>16, 17 |   |   |   |   |   |   |   |
| 23  | 58.27<br>2.294 | 55.88 ± 0.23<br>2.200 ±.009 | 4, 5<br>20, 21 |   |   |   |   |   |   |   |
| 24  | 60.81<br>2.394 | 58.42 ± 0.25<br>2.300 ±.010 | 4, 5<br>20, 21 |   |   |   |   |   |   |   |
| 25  | 63.35<br>2.494 | 60.96 ± 0.25<br>2.400 ±.010 | 4, 5<br>20, 21 |   |   |   |   |   |   |   |
| 26  | 65.89<br>2.594 | 63.50 ± 0.25<br>2.500 ±.010 | 4, 5<br>20, 21 |   |   |   |   |   |   |   |
| 27  | 68.43<br>2.694 | 66.04 ± 0.25<br>2.600 ±.010 | 4, 5<br>24, 25 |   |   |   |   |   |   |   |
| 28  | 70.97<br>2.794 | 68.58 ± 0.25<br>2.700 ±.010 | 4, 5<br>24, 25 |   |   |   |   |   |   |   |



- NOTES:
1. MATERIAL: NYLON, UL 94V-0, COLOR - WHITE.
  2. FINISH:
    - (197) = OVERALL REFLOWED MATTE TIN: 0.00152/.000060 MIN OVER 0.00127/.000050 MIN NICKEL.
    - (154) = OVERALL TIN: 0.00254/.000100 MIN OVER 0.00127/.000050 MIN NICKEL.
    - (222) = OVERALL MATTE TIN: 0.00254/.000100 MIN OVER 0.00127/.000050 MIN NICKEL.
    - (225) = SELECT GOLD: 0.00005/.000002 MIN, SELECT MATTE TIN: 0.00254/.000100, BOTH OVER 0.00127/.000050 MIN NICKEL.
    - (228) = SELECT GOLD: 0.00076/.000030 MIN, SELECT MATTE TIN: 0.00254/.000100, BOTH OVER 0.00127/.000050 MIN NICKEL.
    - (231) = SELECT GOLD: 0.00127/.000050 MIN, SELECT MATTE TIN: 0.00254/.000100, BOTH OVER 0.00127/.000050 MIN NICKEL.
    - (241) = SELECT GOLD: 0.00051/.000020 MIN, SELECT MATTE TIN: 0.00254/.000100, BOTH OVER 0.00127/.000050 MIN NICKEL.
  3. PRODUCT SPECIFICATION AND PROCESS PARAMETERS: PS-10-07.
  4. PACKAGING INFORMATION: SEE LEGEND.
  5. PARTS ARE STACKABLE END TO END ON 2.54/.100 CENTERS.
  6. CIRCUIT ONE DESIGNATION IS USED TO DEFINE VOID LOCATION. CIRCUIT ONE MAY OR MAY NOT LINE UP WITH CIRCUIT ONE ON THE MATING HOUSING.
  7. PIN PUSHOUT FORCE: 2 LBS MIN.
  8. FOR PIN DIMENSIONS, SEE APPLICABLE DRAWING.
  9. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

A-6373-N \*\*\* - \*


NO OF CKTS: \_\_\_\_\_

OPTIONS: SEE CHART

FINISH: SEE CHART

PACKAGING: BLANK = BULK PACK A = TUBE PACK

VOIDED CKT: SEE CHART



|     |     |
|-----|-----|
| 2-* | BD5 |
| 1   | BD5 |
| SHT | REV |

ADD 46999-0801

EC NO: UCP2016-4061

DRW:MKIPPER 2016/04/15

CHKD:JBELL 2016/04/15

APPR:FSM1TH 2016/05/12

DESCRIPTION

REV

QUALITY SYMBOLS

FA=0

FE=0

FB=0

| GENERAL TOLERANCES (UNLESS SPECIFIED)                |               |
|------------------------------------------------------|---------------|
|                                                      | MM/IN         |
| 4 PLACES                                             | ± --- ± ---   |
| 3 PLACES                                             | ± --- ± .010  |
| 2 PLACES                                             | ± 0.25 ± .015 |
| 1 PLACE                                              | ± 0.38 ± ---  |
| 0 PLACE                                              | ± ±           |
| ANGULAR ±1/2°                                        |               |
| DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS |               |

| DIMENSION STYLE |            |
|-----------------|------------|
| MM/IN           |            |
| DRAWN BY        | DATE       |
| SAMIEC          | 2004/03/31 |
| CHECKED BY      | DATE       |
| SAMIEC          | 2004/03/31 |
| APPROVED BY     | DATE       |
| FSMITH          | 2010/12/03 |
| MATERIAL NO.    |            |
| SEE CHART       |            |
| SIZE            | B          |

|                                                                                                                 |                      |                                                                                                                    |  |
|-----------------------------------------------------------------------------------------------------------------|----------------------|--------------------------------------------------------------------------------------------------------------------|--|
| SCALE<br>4:1                                                                                                    | DESIGN UNITS<br>INCH | THIRD ANGLE<br>PROJECTION<br> |  |
| TITLE                                                                                                           |                      |                                                                                                                    |  |
| KK 100 HEADER ASSEMBLY<br>FRICTION LOCK SOLID BODY                                                              |                      |                                                                                                                    |  |
| 3                                                                                                               |                      |                                                                                                                    |  |
| molex                                                                                                           |                      |                                                                                                                    |  |
| DOCUMENT NO.<br>SD-6373-001                                                                                     |                      | SHEET NO.<br>1 OF *                                                                                                |  |
| THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX<br>SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |                      |                                                                                                                    |  |

|                                                  |                 |                           |     |                 |                  |                                  |         |                                                    |                  |                      |     |                 |                  |                        |  |
|--------------------------------------------------|-----------------|---------------------------|-----|-----------------|------------------|----------------------------------|---------|----------------------------------------------------|------------------|----------------------|-----|-----------------|------------------|------------------------|--|
| GROUP:                                           |                 | A-6373-NA222-*            |     |                 |                  |                                  |         |                                                    |                  |                      |     |                 |                  |                        |  |
| PIN NUMBER:                                      |                 | 42663-0306 OR 2766-1(222) |     |                 |                  |                                  |         |                                                    |                  |                      |     |                 |                  |                        |  |
| PIN LENGTH: L                                    |                 | .560 / (14.22)            |     |                 |                  |                                  |         |                                                    |                  |                      |     |                 |                  |                        |  |
| MATING: M                                        |                 | .295 / (7.49)             |     |                 |                  | DIM. G                           | N/A     |                                                    |                  |                      |     |                 |                  |                        |  |
| PC TAIL: P                                       |                 | .140 / (3.56)             |     |                 |                  | DIM T                            | OVERALL |                                                    |                  |                      |     |                 |                  |                        |  |
| PACKAGING:                                       |                 | PK-6373-001 BULK          |     |                 |                  |                                  |         |                                                    |                  |                      |     |                 |                  |                        |  |
| CKT                                              | MATERIAL NUMBER | ENG NUMBER                | CKT | MATERIAL NUMBER | ENG NUMBER       | VOID CKT                         | CKT     | MATERIAL NUMBER                                    | ENG NUMBER       | VOID CKT             | CKT | MATERIAL NUMBER | ENG NUMBER       | VOID CKT               |  |
| 2                                                | 22-23-2021      | A-6373-02A222             | 9   | 22-04-5094      | A-6373-09A222-4  | 4                                | 11      | 22-04-5117                                         | A-6373-11A222-7  | 7                    | 07  | 22-04-5076      | A-6373-07A222-2  | 2                      |  |
| 3                                                | 22-23-2031      | A-6373-03A222             | 9   | 22-04-5096      | A-6373-09A222-6  | 6                                | 06      | 22-04-5063                                         | A-6373-06A222-3  | 3                    | 07  | 22-04-5077      | A-6373-07A222-6  | 6                      |  |
| 4                                                | 22-23-2041      | A-6373-04A222             | 11  | 22-04-5114      | A-6373-11A222-4  | 4                                | 10      | 22-04-5101                                         | A-6373-10A222-1  | 1                    | 06  | 22-04-5069      | A-6373-06A222-54 | 4, 5                   |  |
| 5                                                | 22-23-2051      | A-6373-05A222             | 11  | 22-04-5118      | A-6373-11A222-8  | 8                                | 10      | 22-04-5102                                         | A-6373-10A222-2  | 2                    | 25  | 22-04-5252      | A-6373-25A222-2  | 2                      |  |
| 6                                                | 22-23-2061      | A-6373-06A222             | 08  | 22-04-5083      | A-6373-08A222-3  | 3                                | 10      | 22-04-5103                                         | A-6373-10A222-3  | 3                    | 08  | 22-04-5086      | A-6373-08A222-6  | 6                      |  |
| 7                                                | 22-23-2071      | A-6373-07A222             | 08  | 22-04-5082      | A-6373-08A222-2  | 2                                | 15      | 22-04-5154                                         | A-6373-15A222-14 | 14                   | 08  | 22-04-5087      | A-6373-08A222-52 | 2,3,5,6,7              |  |
| 8                                                | 22-23-2081      | A-6373-08A222             | 10  | 22-04-5106      | A-6373-10A222-6  | 6                                | 05      | 22-04-5052                                         | A-6373-05A222-2  | 2                    | 10  | 22-04-5105      | A-6373-10A222-5  | 5                      |  |
| 9                                                | 22-23-2091      | A-6373-09A222             | 04  | 22-04-5043      | A-6373-04A222-3  | 3                                | 08      | 22-04-5084                                         | A-6373-08A222-4  | 4                    | 05  | 22-04-5057      | A-6373-05A222-52 | 2, 4                   |  |
| 10                                               | 22-23-2101      | A-6373-10A222             | 08  | 22-04-5081      | A-6373-08A222-51 | 2,4,6                            | 06      | 22-04-5064                                         | A-6373-06A222-4  | 4                    | 19  | 22-04-5198      | A-6373-19A222-8  | 8                      |  |
| 11                                               | 22-23-2111      | A-6373-11A222             | 09  | 22-04-5093      | A-6373-09A222-3  | 3                                | 03      | 22-04-5031                                         | A-6373-03A222-1  | 1                    | 11  | 22-04-5119      | A-6373-11A222-51 | 2,4,6,8,10             |  |
| 12                                               | 22-23-2121      | A-6373-12A222             | 08  | 22-04-5085      | A-6373-08A222-5  | 5                                | 05      | 22-04-5053                                         | A-6373-05A222-3  | 3                    | 12  | 22-04-5129      | A-6373-12A222-11 | 11                     |  |
| 13                                               | 22-23-2131      | A-6373-13A222             | 06  | 22-04-5065      | A-6373-06A222-5  | 5                                | 11      | 22-04-5116                                         | A-6373-11A222-6  | 6                    | 08  | 22-04-5088      | A-6373-08A222-53 | 4, 6                   |  |
| 14                                               | 22-23-2141      | A-6373-14A222             | 07  | 22-04-5072      | A-6373-07A222-52 | 2,4,6                            | 07      | 22-04-5074                                         | A-6373-07A222-4  | 4                    | 04  | 22-04-5044      | A-6373-04A222-4  | 4                      |  |
| 15                                               | 22-23-2151      | A-6373-15A222             | 06  | 22-04-5062      | A-6373-06A222-2  | 2                                | 10      | 22-04-5079                                         | A-6373-10A222-52 | 2,3,5,6,8,9          | 27  | 22-04-5277      | A-6373-27A222-51 | 3,7,9,11,14,16, 21, 23 |  |
| 16                                               | 22-23-2161      | A-6373-16A222             | 07  | 22-04-5071      | A-6373-07A222-51 | 2,3,5,6                          | 04      | 22-04-5049                                         | A-6373-04A222-51 | 2,3                  |     |                 |                  |                        |  |
| 17                                               | 22-23-2171      | A-6373-17A222             | 10  | 22-04-5100      | A-6373-10A222-10 | 10                               | 04      | 22-04-5048                                         | A-6373-04A222-52 | 2,4                  | 11  | 22-04-5115      | A-6373-11A222-52 | 5, 6                   |  |
| 18                                               | 22-23-2181      | A-6373-18A222             | 10  | 22-04-5109      | A-6373-10A222-9  | 9                                | 04      | 22-04-5041                                         | A-6373-04A222-1  | 1                    | 24  | 22-23-3245      | A-6373-24A222-23 | 23                     |  |
| 19                                               | 22-23-2191      | A-6373-19A222             | 10  | 22-04-5108      | A-6373-10A222-8  | 8                                | 03      | 22-04-5032                                         | A-6373-03A222-2  | 2                    | 11  | 22-23-3115      | A-6373-11A222-10 | 10                     |  |
| 20                                               | 22-23-2201      | A-6373-20A222             | 05  | 22-04-5054      | A-6373-05A222-4  | 4                                | 13      | 22-04-5139                                         | A-6373-13A222-9  | 9                    | 15  | 22-23-3155      | A-6373-15A222-15 | 15                     |  |
| 21                                               | 22-23-2211      | A-6373-21A222             | 03  | 22-04-5033      | A-6373-03A222-3  | 3                                | 12      | 22-04-5126                                         | A-6373-12A222-6  | 6                    | 08  | 22-04-5089      | A-6373-08A222-54 | 2, 5                   |  |
| 22                                               | 22-23-2221      | A-6373-22A222             | 07  | 22-04-5075      | A-6373-07A222-5  | 5                                | 13      | 22-04-5131                                         | A-6373-13A222-51 | 2,3,5,6,8,9,11,12    | 06  | 22-23-2069      | A-6373-06A222-55 | 2,3,4,5                |  |
| 23                                               | 22-23-2231      | A-6373-23A222             | 07  | 22-04-5073      | A-6373-07A222-3  | 3                                | 06      | 22-04-5066                                         | A-6373-06A222-52 | 3,5                  | 07  | 22-23-2079      | A-6373-07A222-53 | 2,3,4,5,6              |  |
| 24                                               | 22-23-2241      | A-6373-24A222             | 14  | 22-04-5149      | A-6373-14A222-9  | 9                                | 05      | 22-04-5056                                         | A-6373-05A222-51 | 1,3,5                | 13  | 22-23-1137      | A-6373-13A222-53 | 3,6,10,12              |  |
| 25                                               | 22-23-2251      | A-6373-25A222             | 15  | 22-04-5152      | A-6373-15A222-2  | 2                                | 06      | 22-04-5067                                         | A-6373-06A222-53 | 1, 5                 | 10  | 22-23-1107      | A-6373-10A222-53 | 4,7                    |  |
| 26                                               | 22-23-2261      | A-6373-26A222             | 11  | 50-29-1594      | A-6373-11A222-53 | 2,3,4,5,7,8,9,10                 | 06      | 22-04-5068                                         | A-6373-06A222-6  | 6                    | 18  | 22-23-1187      | A-6373-18A222-5  | 5                      |  |
| 27                                               | 22-23-2271      | A-6373-27A222             |     |                 |                  |                                  | 02      | 22-04-5021                                         | A-6373-02A222-1  | 1                    | 18  | 22-23-1188      | A-6373-18A222-7  | 7                      |  |
| 28                                               | 22-23-2281      | A-6373-28A222             | 13  | 22-04-5132      | A-6373-13A222-52 | 8, 9                             | 04      | 22-04-5042                                         | A-6373-04A222-2  | 2                    | 12  | 50-29-0096      | A-6373-12A222-8  | 8                      |  |
|                                                  |                 |                           |     |                 |                  |                                  |         |                                                    |                  |                      |     |                 |                  |                        |  |
| REV:                                             |                 | ECR/ECN INFORMATION:      |     |                 |                  | TITLE:                           |         | KK 100 HEADER ASSEMBLY<br>FRICTION LOCK SOLID BODY |                  |                      |     |                 |                  | SHEET No.              |  |
| BD5                                              |                 | EC No.: UCP2016-4061      |     |                 |                  |                                  |         |                                                    |                  |                      |     |                 |                  | - 2 -                  |  |
|                                                  |                 | DATE: 5/16/2016           |     |                 |                  |                                  |         |                                                    |                  |                      |     |                 |                  |                        |  |
| DOCUMENT NUMBER:<br>SD - 6373 - 001              |                 |                           |     |                 |                  | CREATED / REVISED BY:<br>MKIPPER |         |                                                    |                  | CHECKED BY:<br>JBELL |     |                 |                  | APPROVED BY:<br>FSMITH |  |
| TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC |                 |                           |     |                 |                  |                                  |         |                                                    |                  |                      |     |                 |                  |                        |  |

|               |                 |                  |        |                 |            |          |
|---------------|-----------------|------------------|--------|-----------------|------------|----------|
| GROUP:        |                 | A-6373-NC197-*   |        |                 |            |          |
| PIN NUMBER:   |                 | 42663-0242       |        |                 |            |          |
| PIN LENGTH: L |                 | .530 / (13.46)   |        |                 |            |          |
| MATING: M     |                 | .260 / (6.60)    | DIM. G |                 | N/A        |          |
| PC TAIL: P    |                 | .145 / (3.68)    | DIM T  |                 | OVERALL    |          |
| PACKAGING:    |                 | PK-6373-001 BULK |        |                 |            |          |
| CKTS          | MATERIAL NUMBER | ENG NUMBER       | CKTS   | MATERIAL NUMBER | ENG NUMBER | VOID CKT |
| 2             | 22-23-2023      | A-6373-02C197    |        |                 |            |          |
| 3             | 22-23-2033      | A-6373-03C197    |        |                 |            |          |
| 4             | 22-23-2043      | A-6373-04C197    |        |                 |            |          |
| 5             | 22-23-2053      | A-6373-05C197    |        |                 |            |          |
| 6             | 22-23-2063      | A-6373-06C197    |        |                 |            |          |
| 7             | 22-23-2073      | A-6373-07C197    |        |                 |            |          |
| 8             | 22-23-2083      | A-6373-08C197    |        |                 |            |          |
| 9             | 22-23-2093      | A-6373-09C197    |        |                 |            |          |
| 10            | 22-23-2103      | A-6373-10C197    |        |                 |            |          |
| 11            | 22-23-2113      | A-6373-11C197    |        |                 |            |          |
| 12            | 22-23-2123      | A-6373-12C197    |        |                 |            |          |
| 13            | 22-23-2133      | A-6373-13C197    |        |                 |            |          |
| 14            | 22-23-2143      | A-6373-14C197    |        |                 |            |          |
| 15            | 22-23-2153      | A-6373-15C197    |        |                 |            |          |
| 16            | 22-23-2163      | A-6373-16C197    |        |                 |            |          |
| 17            | 22-23-2173      | A-6373-17C197    |        |                 |            |          |
| 18            | 22-23-2183      | A-6373-18C197    |        |                 |            |          |
| 19            | 22-23-2193      | A-6373-19C197    |        |                 |            |          |
| 20            | 22-23-2203      | A-6373-20C197    |        |                 |            |          |
| 21            | 22-23-2213      | A-6373-21C197    |        |                 |            |          |
| 22            | 22-23-2223      | A-6373-22C197    |        |                 |            |          |
| 23            | 22-23-2233      | A-6373-23C197    |        |                 |            |          |
| 24            | 22-23-2243      | A-6373-24C197    |        |                 |            |          |
| 25            | 22-23-2253      | A-6373-25C197    |        |                 |            |          |
| 26            | 22-23-2263      | A-6373-26C197    |        |                 |            |          |
| 27            | 22-23-2273      | A-6373-27C197    |        |                 |            |          |
| 28            | 22-23-2283      | A-6373-28C197    |        |                 |            |          |

|               |                    |                  |        |                    |               |             |
|---------------|--------------------|------------------|--------|--------------------|---------------|-------------|
| GROUP:        |                    | A-6373-NV228-*   |        |                    |               |             |
| PIN NUMBER:   |                    | 42663-0243       |        |                    |               |             |
| PIN LENGTH: L |                    | .530 / (13.46)   |        |                    |               |             |
| MATING: M     |                    | .295 / (7.49)    | DIM. G |                    | .140 / (3.56) |             |
| PC TAIL: P    |                    | .110 / (2.79)    | DIM T  |                    | .135 / (3.43) |             |
| PACKAGING:    |                    | PK-6373-001 BULK |        |                    |               |             |
| CKTS          | MATERIAL<br>NUMBER | ENG<br>NUMBER    | CKTS   | MATERIAL<br>NUMBER | ENG<br>NUMBER | VOID<br>CKT |
| 2             | 22-15-3029         | A-6373-02V228    |        |                    |               |             |
| 3             | 22-15-3039         | A-6373-03V228    |        |                    |               |             |
| 4             | 22-15-3049         | A-6373-04V228    |        |                    |               |             |
| 5             | 22-15-3059         | A-6373-05V228    |        |                    |               |             |
| 6             | 22-15-3069         | A-6373-06V228    |        |                    |               |             |
| 7             | 22-15-3079         | A-6373-07V228    |        |                    |               |             |
| 8             | 22-15-3089         | A-6373-08V228    |        |                    |               |             |
| 9             | 22-15-3099         | A-6373-09V228    |        |                    |               |             |
| 10            | 22-15-3109         | A-6373-10V228    |        |                    |               |             |
| 11            | 22-15-3119         | A-6373-11V228    |        |                    |               |             |
| 12            | 22-15-3129         | A-6373-12V228    |        |                    |               |             |
| 13            | 22-15-3139         | A-6373-13V228    |        |                    |               |             |
| 14            | 22-15-3149         | A-6373-14V228    |        |                    |               |             |
| 15            | 22-15-3159         | A-6373-15V228    |        |                    |               |             |
| 16            | 22-15-3169         | A-6373-16V228    |        |                    |               |             |
| 17            | 22-15-3179         | A-6373-17V228    |        |                    |               |             |
| 18            | 22-15-3189         | A-6373-18V228    |        |                    |               |             |
| 19            | 22-15-3199         | A-6373-19V228    |        |                    |               |             |
| 20            | 22-15-3209         | A-6373-20V228    |        |                    |               |             |
| 21            | 22-15-3219         | A-6373-21V228    |        |                    |               |             |
| 22            | 22-15-3229         | A-6373-22V228    |        |                    |               |             |
| 23            | 22-15-3239         | A-6373-23V228    |        |                    |               |             |
| 24            | 22-15-3249         | A-6373-24V228    |        |                    |               |             |
| 25            | 22-15-3259         | A-6373-25V228    |        |                    |               |             |
| 26            | 22-15-3269         | A-6373-26V228    |        |                    |               |             |
| 27            | 22-15-3279         | A-6373-27V228    |        |                    |               |             |
| 28            | 22-15-3289         | A-6373-28V228    |        |                    |               |             |

|                        |                             |                                 |               |
|------------------------|-----------------------------|---------------------------------|---------------|
| REV:                   | ECR/ECN INFORMATION:        | TITLE:                          | SHEET No.     |
| <b>BD5</b>             | EC No.: <b>UCP2016-4061</b> | <b>KK 100 HEADER ASSEMBLY</b>   | <b>- 3 -</b>  |
|                        | DATE: <b>5/16/2016</b>      | <b>FRICTION LOCK SOLID BODY</b> |               |
| DOCUMENT NUMBER:       | CREATED / REVISED BY:       | CHECKED BY:                     | APPROVED BY:  |
| <b>SD - 6373 - 001</b> | <b>MKIPPER</b>              | <b>JBELL</b>                    | <b>FSMITH</b> |

|               |                    |                  |        |                    |               |             |
|---------------|--------------------|------------------|--------|--------------------|---------------|-------------|
| GROUP:        |                    | A-6373-NE197-*   |        |                    |               |             |
| PIN NUMBER:   |                    | 42663-0682       |        |                    |               |             |
| PIN LENGTH: L |                    | .750 / (19.05)   |        |                    |               |             |
| MATING: M     |                    | .260 / (6.60)    | DIM. G |                    | N/A           |             |
| PC TAIL: P    |                    | .365 / (9.27)    | DIM T  |                    | OVERALL       |             |
| PACKAGING:    |                    | PK-6373-001 BULK |        |                    |               |             |
| CKTS          | MATERIAL<br>NUMBER | ENG<br>NUMBER    | CKTS   | MATERIAL<br>NUMBER | ENG<br>NUMBER | VOID<br>CKT |
| 2             | 22-23-2025         | A-6373-02E197    |        |                    |               |             |
| 3             |                    | A-6373-03E197    |        |                    |               |             |
| 4             |                    | A-6373-04E197    |        |                    |               |             |
| 5             | 22-23-2055         | A-6373-05E197    |        |                    |               |             |
| 6             | 22-23-2065         | A-6373-06E197    |        |                    |               |             |
| 7             |                    | A-6373-07E197    |        |                    |               |             |
| 8             |                    | A-6373-08E197    |        |                    |               |             |
| 9             |                    | A-6373-09E197    |        |                    |               |             |
| 10            | 22-23-2105         | A-6373-10E197    |        |                    |               |             |
| 11            |                    | A-6373-11E197    |        |                    |               |             |
| 12            |                    | A-6373-12E197    |        |                    |               |             |
| 13            |                    | A-6373-13E197    |        |                    |               |             |
| 14            |                    | A-6373-14E197    |        |                    |               |             |
| 15            | 22-23-2155         | A-6373-15E197    |        |                    |               |             |
| 16            |                    | A-6373-16E197    |        |                    |               |             |
| 17            |                    | A-6373-17E197    |        |                    |               |             |
| 18            |                    | A-6373-18E197    |        |                    |               |             |
| 19            |                    | A-6373-19E197    |        |                    |               |             |
| 20            |                    | A-6373-20E197    |        |                    |               |             |
| 21            |                    | A-6373-21E197    |        |                    |               |             |
| 22            |                    | A-6373-22E197    |        |                    |               |             |
| 23            |                    | A-6373-23E197    |        |                    |               |             |
| 24            |                    | A-6373-24E197    |        |                    |               |             |
| 25            |                    | A-6373-25E197    |        |                    |               |             |
| 26            |                    | A-6373-26E197    |        |                    |               |             |
| 27            |                    | A-6373-27E197    |        |                    |               |             |
| 28            |                    | A-6373-28E197    |        |                    |               |             |

|               |                 |                  |        |                 |               |          |
|---------------|-----------------|------------------|--------|-----------------|---------------|----------|
| GROUP:        |                 | A-6373-NY241-*   |        |                 |               |          |
| PIN NUMBER:   |                 | 42663-0443       |        |                 |               |          |
| PIN LENGTH: L |                 | .630 / (16.00)   |        |                 |               |          |
| MATING: M     |                 | .318 / (8.08)    | DIM. G |                 | .140 / (3.56) |          |
| PC TAIL: P    |                 | .187 / (4.75)    | DIM T  |                 | .135 / (3.43) |          |
| PACKAGING:    |                 | PK-6373-001 BULK |        |                 |               |          |
| CKTS          | MATERIAL NUMBER | ENG NUMBER       | CKTS   | MATERIAL NUMBER | ENG NUMBER    | VOID CKT |
| 2             | 22-11-2026      | A-6373-02Y241    |        |                 |               |          |
| 3             | 22-11-2036      | A-6373-03Y241    |        |                 |               |          |
| 4             | 22-11-2046      | A-6373-04Y241    |        |                 |               |          |
| 5             | 22-11-2056      | A-6373-05Y241    |        |                 |               |          |
| 6             | 22-11-2066      | A-6373-06Y241    |        |                 |               |          |
| 7             | 22-11-2076      | A-6373-07Y241    |        |                 |               |          |
| 8             | 22-11-2086      | A-6373-08Y241    |        |                 |               |          |
| 9             | 22-11-2096      | A-6373-09Y241    |        |                 |               |          |
| 10            | 22-11-2106      | A-6373-10Y241    |        |                 |               |          |
| 11            | 22-11-2116      | A-6373-11Y241    |        |                 |               |          |
| 12            | 22-11-2126      | A-6373-12Y241    |        |                 |               |          |
| 13            | 22-11-2136      | A-6373-13Y241    |        |                 |               |          |
| 14            | 22-11-2146      | A-6373-14Y241    |        |                 |               |          |
| 15            | 22-11-2156      | A-6373-15Y241    |        |                 |               |          |
| 16            | 22-11-2166      | A-6373-16Y241    |        |                 |               |          |
| 17            | 22-11-2176      | A-6373-17Y241    |        |                 |               |          |
| 18            | 22-11-2186      | A-6373-18Y241    |        |                 |               |          |
| 19            | 22-11-2196      | A-6373-19Y241    |        |                 |               |          |
| 20            | 22-11-2206      | A-6373-20Y241    |        |                 |               |          |
| 21            | 22-11-2216      | A-6373-21Y241    |        |                 |               |          |
| 22            | 22-11-2226      | A-6373-22Y241    |        |                 |               |          |
| 23            | 22-11-2236      | A-6373-23Y241    |        |                 |               |          |
| 24            | 22-11-2246      | A-6373-24Y241    |        |                 |               |          |
| 25            | 22-11-2256      | A-6373-25Y241    |        |                 |               |          |
| 26            | 22-11-2266      | A-6373-26Y241    |        |                 |               |          |
| 27            | 22-11-2276      | A-6373-27Y241    |        |                 |               |          |
| 28            | 22-11-2286      | A-6373-28Y241    |        |                 |               |          |

|                        |                             |                                                            |              |
|------------------------|-----------------------------|------------------------------------------------------------|--------------|
| REV:                   | ECR/ECN INFORMATION:        | TITLE:                                                     | SHEET No.    |
| <b>BD5</b>             | EC No.: <b>UCP2016-4061</b> | <b>KK 100 HEADER ASSEMBLY<br/>FRICTION LOCK SOLID BODY</b> | <b>- 4 -</b> |
|                        | DATE: <b>5/16/2016</b>      |                                                            |              |
| DOCUMENT NUMBER:       |                             | CREATED / REVISED BY:                                      | CHECKED BY:  |
| <b>SD - 6373 - 001</b> |                             | <b>MKIPPER</b>                                             | <b>JBELL</b> |
|                        |                             | APPROVED BY:                                               |              |
|                        |                             | <b>FSMITH</b>                                              |              |



|               |                 |                  |        |                 |            |          |
|---------------|-----------------|------------------|--------|-----------------|------------|----------|
| GROUP:        |                 | A-6373-NAB197-*  |        |                 |            |          |
| PIN NUMBER:   |                 | 42663-0582       |        |                 |            |          |
| PIN LENGTH: L |                 | .700 / (17.78)   |        |                 |            |          |
| MATING: M     |                 | .286 / (7.26)    | DIM. G |                 | N/A        |          |
| PC TAIL: P    |                 | .289 / (7.34)    | DIM T  |                 | OVERALL    |          |
| PACKAGING:    |                 | PK-6373-001 BULK |        |                 |            |          |
| CKTS          | MATERIAL NUMBER | ENG NUMBER       | CKTS   | MATERIAL NUMBER | ENG NUMBER | VOID CKT |
| 2             |                 | A-6373-02AB197   |        |                 |            |          |
| 3             | 50-29-0052      | A-6373-03AB197   |        |                 |            |          |
| 4             | 50-29-0053      | A-6373-04AB197   |        |                 |            |          |
| 5             |                 | A-6373-05AB197   |        |                 |            |          |
| 6             |                 | A-6373-06AB197   |        |                 |            |          |
| 7             |                 | A-6373-07AB197   |        |                 |            |          |
| 8             | 50-29-0057      | A-6373-08AB197   |        |                 |            |          |
| 9             |                 | A-6373-09AB197   |        |                 |            |          |
| 10            | 50-29-0058      | A-6373-10AB197   |        |                 |            |          |
| 11            |                 | A-6373-11AB197   |        |                 |            |          |
| 12            |                 | A-6373-12AB197   |        |                 |            |          |
| 13            |                 | A-6373-13AB197   |        |                 |            |          |
| 14            |                 | A-6373-14AB197   |        |                 |            |          |
| 15            |                 | A-6373-15AB197   |        |                 |            |          |
| 16            |                 | A-6373-16AB197   |        |                 |            |          |
| 17            |                 | A-6373-17AB197   |        |                 |            |          |
| 18            |                 | A-6373-18AB197   |        |                 |            |          |
| 19            |                 | A-6373-19AB197   |        |                 |            |          |
| 20            |                 | A-6373-20AB197   |        |                 |            |          |
| 21            |                 | A-6373-21AB197   |        |                 |            |          |
| 22            |                 | A-6373-22AB197   |        |                 |            |          |
| 23            |                 | A-6373-23AB197   |        |                 |            |          |
| 24            |                 | A-6373-24AB197   |        |                 |            |          |
| 25            |                 | A-6373-25AB197   |        |                 |            |          |
| 26            |                 | A-6373-26AB197   |        |                 |            |          |
| 27            |                 | A-6373-27AB197   |        |                 |            |          |
| 28            |                 | A-6373-28AB197   |        |                 |            |          |

|               |                    |                  |        |                    |               |             |
|---------------|--------------------|------------------|--------|--------------------|---------------|-------------|
| GROUP:        |                    | A-6373-NA231-*   |        |                    |               |             |
| PIN NUMBER:   |                    | 42663-0307       |        |                    |               |             |
| PIN LENGTH: L |                    | .560 / (14.22)   |        |                    |               |             |
| MATING: M     |                    | .295 / (7.49)    | DIM. G |                    | .140 / (3.56) |             |
| PC TAIL: P    |                    | .140 / (3.56)    | DIM T  |                    | .135 / (3.43) |             |
| PACKAGING:    |                    | PK-6373-001 BULK |        |                    |               |             |
| CKTS          | MATERIAL<br>NUMBER | ENG<br>NUMBER    | CKTS   | MATERIAL<br>NUMBER | ENG<br>NUMBER | VOID<br>CKT |
| 2             | 22-04-5022         | A-6373-02A231    |        |                    |               |             |
| 3             | 46999-0800         | A-6373-03A231    |        |                    |               |             |
| 4             | 46999-0801         | A-6373-04A231    |        |                    |               |             |
| 5             |                    | A-6373-05A231    |        |                    |               |             |
| 6             |                    | A-6373-06A231    |        |                    |               |             |
| 7             |                    | A-6373-07A231    |        |                    |               |             |
| 8             |                    | A-6373-08A231    |        |                    |               |             |
| 9             |                    | A-6373-09A231    |        |                    |               |             |
| 10            |                    | A-6373-10A231    |        |                    |               |             |
| 11            |                    | A-6373-11A231    |        |                    |               |             |
| 12            |                    | A-6373-12A231    |        |                    |               |             |
| 13            |                    | A-6373-13A231    |        |                    |               |             |
| 14            |                    | A-6373-14A231    |        |                    |               |             |
| 15            |                    | A-6373-15A231    |        |                    |               |             |
| 16            |                    | A-6373-16A231    |        |                    |               |             |
| 17            |                    | A-6373-17A231    |        |                    |               |             |
| 18            |                    | A-6373-18A231    |        |                    |               |             |
| 19            |                    | A-6373-19A231    |        |                    |               |             |
| 20            |                    | A-6373-20A231    |        |                    |               |             |
| 21            |                    | A-6373-21A231    |        |                    |               |             |
| 22            |                    | A-6373-22A231    |        |                    |               |             |
| 23            |                    | A-6373-23A231    |        |                    |               |             |
| 24            |                    | A-6373-24A231    |        |                    |               |             |
| 25            |                    | A-6373-25A231    |        |                    |               |             |
| 26            |                    | A-6373-26A231    |        |                    |               |             |
| 27            |                    | A-6373-27A231    |        |                    |               |             |
| 28            |                    | A-6373-28A231    |        |                    |               |             |

|                                            |                                                       |                                                                      |                             |
|--------------------------------------------|-------------------------------------------------------|----------------------------------------------------------------------|-----------------------------|
| REV:<br><b>BD5</b>                         | ECR/ECN INFORMATION:                                  | TITLE:<br><b>KK 100 HEADER ASSEMBLY<br/>FRICTION LOCK SOLID BODY</b> | SHEET No.<br><b>- 6 -</b>   |
|                                            | EC No.: <b>UCP2016-4061</b><br>DATE: <b>5/16/2016</b> |                                                                      |                             |
| DOCUMENT NUMBER:<br><b>SD - 6373 - 001</b> |                                                       | CREATED / REVISED BY:<br><b>MKIPPER</b>                              | CHECKED BY:<br><b>JBELL</b> |
|                                            |                                                       | APPROVED BY:<br><b>FSMITH</b>                                        |                             |

|               |                 |                  |        |                 |               |          |
|---------------|-----------------|------------------|--------|-----------------|---------------|----------|
| GROUP:        |                 | A-6373-NAH241-*  |        |                 |               |          |
| PIN NUMBER:   |                 | 42663-0305       |        |                 |               |          |
| PIN LENGTH: L |                 | .560 / (14.22)   |        |                 |               |          |
| MATING: M     |                 | .260 / (6.60)    | DIM. G |                 | .140 / (3.56) |          |
| PC TAIL: P    |                 | .175 / (4.45)    | DIM T  |                 | .135 / (3.43) |          |
| PACKAGING:    |                 | PK-6373-001 BULK |        |                 |               |          |
| CKTS          | MATERIAL NUMBER | ENG NUMBER       | CK TS  | MATERIAL NUMBER | ENG NUMBER    | VOID CKT |
| 2             | 22-23-6024      | A-6373-02AH241   |        |                 |               |          |
| 3             | 22-23-6034      | A-6373-03AH241   |        |                 |               |          |
| 4             | 22-23-6044      | A-6373-04AH241   |        |                 |               |          |
| 5             | 22-23-6054      | A-6373-05AH241   |        |                 |               |          |
| 6             | 22-23-6064      | A-6373-06AH241   |        |                 |               |          |
| 7             | 22-23-6074      | A-6373-07AH241   |        |                 |               |          |
| 8             | 22-23-6084      | A-6373-08AH241   |        |                 |               |          |
| 9             | 22-23-6094      | A-6373-09AH241   |        |                 |               |          |
| 10            | 22-23-6104      | A-6373-10AH241   |        |                 |               |          |
| 11            | 22-23-6114      | A-6373-11AH241   |        |                 |               |          |
| 12            | 22-23-6124      | A-6373-12AH241   |        |                 |               |          |
| 13            | 22-23-6134      | A-6373-13AH241   |        |                 |               |          |
| 14            | 22-23-6144      | A-6373-14AH241   |        |                 |               |          |
| 15            | 22-23-6154      | A-6373-15AH241   |        |                 |               |          |
| 16            | 22-23-6164      | A-6373-16AH241   |        |                 |               |          |
| 17            | 22-23-6174      | A-6373-17AH241   |        |                 |               |          |
| 18            | 22-23-6184      | A-6373-18AH241   |        |                 |               |          |
| 19            | 22-23-6194      | A-6373-19AH241   |        |                 |               |          |
| 20            | 22-23-6204      | A-6373-20AH241   |        |                 |               |          |
| 21            | 22-23-6214      | A-6373-21AH241   |        |                 |               |          |
| 22            | 22-23-6224      | A-6373-22AH241   |        |                 |               |          |
| 23            | 22-23-6234      | A-6373-23AH241   |        |                 |               |          |
| 24            | 22-23-6244      | A-6373-24AH241   |        |                 |               |          |
| 25            | 22-23-6254      | A-6373-25AH241   |        |                 |               |          |
| 26            | 22-23-6264      | A-6373-26AH241   |        |                 |               |          |
| 27            | 22-23-6274      | A-6373-27AH241   |        |                 |               |          |
| 28            | 22-23-6284      | A-6373-28AH241   |        |                 |               |          |

|               |                 |                  |        |                 |                 |          |
|---------------|-----------------|------------------|--------|-----------------|-----------------|----------|
| GROUP:        |                 | A-6373-NA228-*   |        |                 |                 |          |
| PIN NUMBER:   |                 | 42663-0304       |        |                 |                 |          |
| PIN LENGTH: L |                 | .560 / (14.22)   |        |                 |                 |          |
| MATING: M     |                 | .295 / (7.49)    | DIM. G |                 | .140 / (3.56)   |          |
| PC TAIL: P    |                 | .140 / (3.56)    | DIM T  |                 | .135 / (3.43)   |          |
| PACKAGING:    |                 | PK-6373-001 BULK |        |                 |                 |          |
| CKTS          | MATERIAL NUMBER | ENG NUMBER       | CKTS   | MATERIAL NUMBER | ENG NUMBER      | VOID CKT |
| 2             | 22-11-2028      | A-6373-02A228    | 09     | 22-11-2095      | A-6373-09A228-3 | 3        |
| 3             | 22-11-2038      | A-6373-03A228    | 09     | 22-11-2097      | A-6373-09A228-5 | 5        |
| 4             | 22-11-2048      | A-6373-04A228    | 05     | 22-11-2055      | A-6373-05A228-3 | 3        |
| 5             | 22-11-2058      | A-6373-05A228    | 11     | 22-11-2117      | A-6373-11A228-5 | 5        |
| 6             | 22-11-2068      | A-6373-06A228    |        |                 |                 |          |
| 7             | 22-11-2078      | A-6373-07A228    |        |                 |                 |          |
| 8             | 22-11-2088      | A-6373-08A228    |        |                 |                 |          |
| 9             | 22-11-2098      | A-6373-09A228    |        |                 |                 |          |
| 10            | 22-11-2108      | A-6373-10A228    |        |                 |                 |          |
| 11            | 22-11-2118      | A-6373-11A228    |        |                 |                 |          |
| 12            | 22-11-2128      | A-6373-12A228    |        |                 |                 |          |
| 13            | 22-11-2138      | A-6373-13A228    |        |                 |                 |          |
| 14            | 22-11-2148      | A-6373-14A228    |        |                 |                 |          |
| 15            |                 | A-6373-15A228    |        |                 |                 |          |
| 16            |                 | A-6373-16A228    |        |                 |                 |          |
| 17            | 22-11-2178      | A-6373-17A228    |        |                 |                 |          |
| 18            | 46999-0605      | A-6373-18A228    |        |                 |                 |          |
| 19            |                 | A-6373-19A228    |        |                 |                 |          |
| 20            |                 | A-6373-20A228    |        |                 |                 |          |
| 21            |                 | A-6373-21A228    |        |                 |                 |          |
| 22            | 22-11-2228      | A-6373-22A228    |        |                 |                 |          |
| 23            |                 | A-6373-23A228    |        |                 |                 |          |
| 24            |                 | A-6373-24A228    |        |                 |                 |          |
| 25            |                 | A-6373-25A228    |        |                 |                 |          |
| 26            |                 | A-6373-26A228    |        |                 |                 |          |
| 27            |                 | A-6373-27A228    |        |                 |                 |          |
| 28            |                 | A-6373-28A228    |        |                 |                 |          |

|                                                   |                             |  |                                                                                 |                                      |  |  |
|---------------------------------------------------|-----------------------------|--|---------------------------------------------------------------------------------|--------------------------------------|--|--|
| REV:<br><br><b>BD5</b>                            | <u>ECR/ECN INFORMATION:</u> |  | <u>TITLE:</u><br><br><b>KK 100 HEADER ASSEMBLY<br/>FRICTION LOCK SOLID BODY</b> | <u>SHEET No.</u><br><br><b>- 7 -</b> |  |  |
|                                                   | EC No.: <b>UCP2016-4061</b> |  |                                                                                 |                                      |  |  |
|                                                   | DATE: <b>5/16/2016</b>      |  |                                                                                 |                                      |  |  |
| <u>DOCUMENT NUMBER:</u><br><b>SD - 6373 - 001</b> |                             |  | <u>CREATED / REVISED BY:</u><br><b>MKIPPER</b>                                  | <u>CHECKED BY:</u><br><b>JBELL</b>   |  |  |
|                                                   |                             |  | <u>APPROVED BY:</u><br><b>FSMITH</b>                                            |                                      |  |  |

|               |                 |                  |        |                 |            |          |
|---------------|-----------------|------------------|--------|-----------------|------------|----------|
| GROUP:        |                 | A-6373-NAD197-*  |        |                 |            |          |
| PIN NUMBER:   |                 | 42663-0302       |        |                 |            |          |
| PIN LENGTH: L |                 | .560 / (14.22)   |        |                 |            |          |
| MATING: M     |                 | .295 / (7.49)    | DIM. G |                 | N/A        |          |
| PC TAIL: P    |                 | .140 / (3.56)    | DIM T  |                 | OVERALL    |          |
| PACKAGING:    |                 | PK-6373-001 BULK |        |                 |            |          |
| CKTS          | MATERIAL NUMBER | ENG NUMBER       | CKTS   | MATERIAL NUMBER | ENG NUMBER | VOID CKT |
| 2             | 22-23-2028      | A-6373-02AD197   |        |                 |            |          |
| 3             | 22-23-2038      | A-6373-03AD197   |        |                 |            |          |
| 4             | 22-23-2048      | A-6373-04AD197   |        |                 |            |          |
| 5             | 22-23-2058      | A-6373-05AD197   |        |                 |            |          |
| 6             | 22-23-2068      | A-6373-06AD197   |        |                 |            |          |
| 7             | 22-23-2078      | A-6373-07AD197   |        |                 |            |          |
| 8             | 22-23-2088      | A-6373-08AD197   |        |                 |            |          |
| 9             | 22-23-2098      | A-6373-09AD197   |        |                 |            |          |
| 10            | 22-23-2108      | A-6373-10AD197   |        |                 |            |          |
| 11            | 22-23-2118      | A-6373-11AD197   |        |                 |            |          |
| 12            | 22-23-2128      | A-6373-12AD197   |        |                 |            |          |
| 13            | 22-23-2138      | A-6373-13AD197   |        |                 |            |          |
| 14            | 22-23-2148      | A-6373-14AD197   |        |                 |            |          |
| 15            | 22-23-2158      | A-6373-15AD197   |        |                 |            |          |
| 16            | 22-23-2168      | A-6373-16AD197   |        |                 |            |          |
| 17            | 22-23-2178      | A-6373-17AD197   |        |                 |            |          |
| 18            | 22-23-2188      | A-6373-18AD197   |        |                 |            |          |
| 19            | 22-23-2198      | A-6373-19AD197   |        |                 |            |          |
| 20            | 22-23-2208      | A-6373-20AD197   |        |                 |            |          |
| 21            | 22-23-2218      | A-6373-21AD197   |        |                 |            |          |
| 22            | 22-23-2228      | A-6373-22AD197   |        |                 |            |          |
| 23            | 22-23-2238      | A-6373-23AD197   |        |                 |            |          |
| 24            | 22-23-2248      | A-6373-24AD197   |        |                 |            |          |
| 25            | 22-23-2258      | A-6373-25AD197   |        |                 |            |          |
| 26            | 22-23-2268      | A-6373-26AD197   |        |                 |            |          |
| 27            | 22-23-2278      | A-6373-27AD197   |        |                 |            |          |
| 28            | 22-23-2288      | A-6373-28AD197   |        |                 |            |          |

|               |                 |            |      |                 |            |          |
|---------------|-----------------|------------|------|-----------------|------------|----------|
| GROUP:        |                 |            |      |                 |            |          |
| PIN NUMBER:   |                 |            |      |                 |            |          |
| PIN LENGTH: L |                 |            |      |                 |            |          |
| MATING: M     |                 |            |      |                 |            |          |
| PC TAIL: P    |                 |            |      |                 |            |          |
| PACKAGING:    |                 |            |      |                 |            |          |
| CKTS          | MATERIAL NUMBER | ENG NUMBER | CKTS | MATERIAL NUMBER | ENG NUMBER | VOID CKT |
| 2             |                 |            |      |                 |            |          |
| 3             |                 |            |      |                 |            |          |
| 4             |                 |            |      |                 |            |          |
| 5             |                 |            |      |                 |            |          |
| 6             |                 |            |      |                 |            |          |
| 7             |                 |            |      |                 |            |          |
| 8             |                 |            |      |                 |            |          |
| 9             |                 |            |      |                 |            |          |
| 10            |                 |            |      |                 |            |          |
| 11            |                 |            |      |                 |            |          |
| 12            |                 |            |      |                 |            |          |
| 13            |                 |            |      |                 |            |          |
| 14            |                 |            |      |                 |            |          |
| 15            |                 |            |      |                 |            |          |
| 16            |                 |            |      |                 |            |          |
| 17            |                 |            |      |                 |            |          |
| 18            |                 |            |      |                 |            |          |
| 19            |                 |            |      |                 |            |          |
| 20            |                 |            |      |                 |            |          |
| 21            |                 |            |      |                 |            |          |
| 22            |                 |            |      |                 |            |          |
| 23            |                 |            |      |                 |            |          |
| 24            |                 |            |      |                 |            |          |
| 25            |                 |            |      |                 |            |          |
| 26            |                 |            |      |                 |            |          |
| 27            |                 |            |      |                 |            |          |
| 28            |                 |            |      |                 |            |          |

|                        |                             |                                                            |              |
|------------------------|-----------------------------|------------------------------------------------------------|--------------|
| REV:                   | ECR/ECN INFORMATION:        | TITLE:                                                     | SHEET No.    |
| <b>BD5</b>             | EC No.: <b>UCP2016-4061</b> | <b>KK 100 HEADER ASSEMBLY<br/>FRICTION LOCK SOLID BODY</b> | <b>- 8 -</b> |
|                        | DATE: <b>5/16/2016</b>      |                                                            |              |
| DOCUMENT NUMBER:       |                             | CREATED / REVISED BY:                                      | CHECKED BY:  |
| <b>SD - 6373 - 001</b> |                             | <b>MKIPPER</b>                                             | <b>JBELL</b> |
|                        |                             | APPROVED BY:                                               |              |
|                        |                             | <b>FSMITH</b>                                              |              |



|              |                    |                  |        |                    |                 |             |
|--------------|--------------------|------------------|--------|--------------------|-----------------|-------------|
| GROUP:       |                    | A-6373-NA197-*   |        |                    |                 |             |
| PIN NUMBER:  |                    | 42663-0302       |        |                    |                 |             |
| PIN LENGTH L |                    | .560 / (14.22)   |        |                    |                 |             |
| MATING: M    |                    | .295 / (7.49)    | DIM. G |                    | N/A             |             |
| PC TAIL: P   |                    | .140 / (3.56)    | DIM T  |                    | OVERALL         |             |
| PACKAGING:   |                    | PK-6373-001 BULK |        |                    |                 |             |
| CKTS         | MATERIAL<br>NUMBER | ENG<br>NUMBER    | CKTS   | MATERIAL<br>NUMBER | ENG<br>NUMBER   | VOID<br>CKT |
| 2            | 22-23-2027         | A-6373-02A197    | 5      | 22-04-6053         | A-6373-05A197-3 | 3           |
| 3            | 22-23-2037         | A-6373-03A197    |        |                    |                 |             |
| 4            | 22-23-2047         | A-6373-04A197    |        |                    |                 |             |
| 5            | 22-23-2057         | A-6373-05A197    |        |                    |                 |             |
| 6            | 22-23-2067         | A-6373-06A197    |        |                    |                 |             |
| 7            | 22-23-2077         | A-6373-07A197    |        |                    |                 |             |
| 8            | 22-23-2087         | A-6373-08A197    |        |                    |                 |             |
| 9            | 22-23-2097         | A-6373-09A197    |        |                    |                 |             |
| 10           | 22-23-2107         | A-6373-10A197    |        |                    |                 |             |
| 11           | 22-23-2117         | A-6373-11A197    |        |                    |                 |             |
| 12           | 22-23-2127         | A-6373-12A197    |        |                    |                 |             |
| 13           | 22-23-2137         | A-6373-13A197    |        |                    |                 |             |
| 14           | 22-23-2147         | A-6373-14A197    |        |                    |                 |             |
| 15           | 22-23-2157         | A-6373-15A197    |        |                    |                 |             |
| 16           | 22-23-2167         | A-6373-16A197    |        |                    |                 |             |
| 17           | 22-23-2177         | A-6373-17A197    |        |                    |                 |             |
| 18           | 22-23-2187         | A-6373-18A197    |        |                    |                 |             |
| 19           | 22-23-2197         | A-6373-19A197    |        |                    |                 |             |
| 20           | 22-23-2207         | A-6373-20A197    |        |                    |                 |             |
| 21           | 22-23-2217         | A-6373-21A197    |        |                    |                 |             |
| 22           | 22-23-2227         | A-6373-22A197    |        |                    |                 |             |
| 23           | 22-23-2237         | A-6373-23A197    |        |                    |                 |             |
| 24           | 22-23-2247         | A-6373-24A197    |        |                    |                 |             |
| 25           | 22-23-2257         | A-6373-25A197    |        |                    |                 |             |
| 26           | 22-23-2267         | A-6373-26A197    |        |                    |                 |             |
| 27           | 22-23-2277         | A-6373-27A197    |        |                    |                 |             |
| 28           | 22-23-2287         | A-6373-28A197    |        |                    |                 |             |

|               |                 |                        |        |                 |                  |          |
|---------------|-----------------|------------------------|--------|-----------------|------------------|----------|
| GROUP:        |                 | A-6373-NA197A-*        |        |                 |                  |          |
| PIN NUMBER:   |                 | 42663-0302             |        |                 |                  |          |
| PIN LENGTH: L |                 | .560 / (14.22)         |        |                 |                  |          |
| MATING: M     |                 | .295 / (7.49)          | DIM. G |                 | N/A              |          |
| PC TAIL: P    |                 | .140 / (3.56)          | DIM T  |                 | OVERALL          |          |
| PACKAGING:    |                 | PK-44743-001 TUBE PACK |        |                 |                  |          |
| CKTS          | MATERIAL NUMBER | ENG NUMBER             | CK TS  | MATERIAL NUMBER | ENG NUMBER       | VOID CKT |
| 2             | 22-23-6021      | A-6373-02A197A         | 10     | 22-23-6106      | A-6373-10A197A-2 | 2        |
| 3             | 22-23-6031      | A-6373-03A197A         |        |                 |                  |          |
| 4             | 22-23-6041      | A-6373-04A197A         |        |                 |                  |          |
| 5             | 22-23-6051      | A-6373-05A197A         |        |                 |                  |          |
| 6             | 22-23-6061      | A-6373-06A197A         |        |                 |                  |          |
| 7             | 22-23-6071      | A-6373-07A197A         |        |                 |                  |          |
| 8             | 22-23-6081      | A-6373-08A197A         |        |                 |                  |          |
| 9             | 22-23-6091      | A-6373-09A197A         |        |                 |                  |          |
| 10            | 22-23-6101      | A-6373-10A197A         |        |                 |                  |          |
| 11            | 22-23-6111      | A-6373-11A197A         |        |                 |                  |          |
| 12            | 22-23-6121      | A-6373-12A197A         |        |                 |                  |          |
| 13            | 22-23-6131      | A-6373-13A197A         |        |                 |                  |          |
| 14            | 22-23-6141      | A-6373-14A197A         |        |                 |                  |          |
| 15            | 22-23-6151      | A-6373-15A197A         |        |                 |                  |          |
| 16            | 22-23-6161      | A-6373-16A197A         |        |                 |                  |          |
| 17            | 22-23-6171      | A-6373-17A197A         |        |                 |                  |          |
| 18            | 22-23-6181      | A-6373-18A197A         |        |                 |                  |          |
| 19            | 22-23-6191      | A-6373-19A197A         |        |                 |                  |          |
| 20            | 22-23-6201      | A-6373-20A197A         |        |                 |                  |          |
| 21            | 22-23-6211      | A-6373-21A197A         |        |                 |                  |          |
| 22            | 22-23-6221      | A-6373-22A197A         |        |                 |                  |          |
| 23            | 22-23-6231      | A-6373-23A197A         |        |                 |                  |          |
| 24            | 22-23-6241      | A-6373-24A197A         |        |                 |                  |          |
| 25            | 22-23-6251      | A-6373-25A197A         |        |                 |                  |          |
| 26            | 22-23-6261      | A-6373-26A197A         |        |                 |                  |          |
| 27            | 22-23-6271      | A-6373-27A197A         |        |                 |                  |          |
| 28            | 22-23-6281      | A-6373-28A197A         |        |                 |                  |          |

|                        |                             |                                                            |              |
|------------------------|-----------------------------|------------------------------------------------------------|--------------|
| REV:                   | ECR/ECN INFORMATION:        | TITLE:                                                     | SHEET No.    |
| <b>BD5</b>             | EC No.: <b>UCP2016-4061</b> | <b>KK 100 HEADER ASSEMBLY<br/>FRICTION LOCK SOLID BODY</b> | <b>- 9 -</b> |
|                        | DATE: <b>5/16/2016</b>      |                                                            |              |
| DOCUMENT NUMBER:       |                             | CREATED / REVISED BY:                                      | CHECKED BY:  |
| <b>SD - 6373 - 001</b> |                             | <b>MKIPPER</b>                                             | <b>JBELL</b> |
|                        |                             | APPROVED BY:                                               |              |
|                        |                             | <b>FSMITH</b>                                              |              |

|               |                 |                  |        |                 |            |          |
|---------------|-----------------|------------------|--------|-----------------|------------|----------|
| GROUP:        |                 | A-6373-NAF197-*  |        |                 |            |          |
| PIN NUMBER:   |                 | 42663-0182       |        |                 |            |          |
| PIN LENGTH: L |                 | .500 / (12.70)   |        |                 |            |          |
| MATING : M    |                 | .260 / (6.60)    | DIM. G |                 | N/A        |          |
| PC TAIL: P    |                 | .115 / (2.92)    | DIM T  |                 | OVERALL    |          |
| PACKAGING:    |                 | PK-6373-001 BULK |        |                 |            |          |
| CKTS          | MATERIAL NUMBER | ENG NUMBER       | CKTS   | MATERIAL NUMBER | ENG NUMBER | VOID CKT |
| 2             | 22-23-2020      | A-6373-02AF197   |        |                 |            |          |
| 3             | 22-23-2030      | A-6373-03AF197   |        |                 |            |          |
| 4             | 22-23-2040      | A-6373-04AF197   |        |                 |            |          |
| 5             | 22-23-2050      | A-6373-05AF197   |        |                 |            |          |
| 6             | 22-23-2060      | A-6373-06AF197   |        |                 |            |          |
| 7             | 22-23-2070      | A-6373-07AF197   |        |                 |            |          |
| 8             | 22-23-2080      | A-6373-08AF197   |        |                 |            |          |
| 9             | 22-23-2090      | A-6373-09AF197   |        |                 |            |          |
| 10            | 22-23-2100      | A-6373-10AF197   |        |                 |            |          |
| 11            | 22-23-2110      | A-6373-11AF197   |        |                 |            |          |
| 12            | 22-23-2120      | A-6373-12AF197   |        |                 |            |          |
| 13            | 22-23-2130      | A-6373-13AF197   |        |                 |            |          |
| 14            | 22-23-2140      | A-6373-14AF197   |        |                 |            |          |
| 15            | 22-23-2150      | A-6373-15AF197   |        |                 |            |          |
| 16            | 22-23-2160      | A-6373-16AF197   |        |                 |            |          |
| 17            | 22-23-2170      | A-6373-17AF197   |        |                 |            |          |
| 18            | 22-23-2180      | A-6373-18AF197   |        |                 |            |          |
| 19            | 22-23-2190      | A-6373-19AF197   |        |                 |            |          |
| 20            | 22-23-2200      | A-6373-20AF197   |        |                 |            |          |
| 21            | 22-23-2210      | A-6373-21AF197   |        |                 |            |          |
| 22            | 22-23-2220      | A-6373-22AF197   |        |                 |            |          |
| 23            | 22-23-2230      | A-6373-23AF197   |        |                 |            |          |
| 24            | 22-23-2240      | A-6373-24AF197   |        |                 |            |          |
| 25            | 22-23-2250      | A-6373-25AF197   |        |                 |            |          |
| 26            | 22-23-2260      | A-6373-26AF197   |        |                 |            |          |
| 27            | 22-23-2270      | A-6373-27AF197   |        |                 |            |          |
| 28            | 22-23-2280      | A-6373-28AF197   |        |                 |            |          |

|               |                 |                  |        |                 |            |          |
|---------------|-----------------|------------------|--------|-----------------|------------|----------|
| GROUP:        |                 | A-6373-NAG197-*  |        |                 |            |          |
| PIN NUMBER:   |                 | 42663-0182       |        |                 |            |          |
| PIN LENGTH: L |                 | .500 / (12.70)   |        |                 |            |          |
| MATING: M     |                 | .301 / (7.65)    | DIM. G |                 | N/A        |          |
| PC TAIL: P    |                 | .074 / (1.88)    | DIM T  |                 | OVERALL    |          |
| PACKAGING:    |                 | PK-6373-001 BULK |        |                 |            |          |
| CKTS          | MATERIAL NUMBER | ENG NUMBER       | CKTS   | MATERIAL NUMBER | ENG NUMBER | VOID CKT |
| 2             | 22-23-2022      | A-6373-02AG197   |        |                 |            |          |
| 3             | 22-23-2032      | A-6373-03AG197   |        |                 |            |          |
| 4             | 22-23-2042      | A-6373-04AG197   |        |                 |            |          |
| 5             | 22-23-2052      | A-6373-05AG197   |        |                 |            |          |
| 6             | 22-23-2062      | A-6373-06AG197   |        |                 |            |          |
| 7             | 22-23-2072      | A-6373-07AG197   |        |                 |            |          |
| 8             | 22-23-2082      | A-6373-08AG197   |        |                 |            |          |
| 9             | 22-23-2092      | A-6373-09AG197   |        |                 |            |          |
| 10            | 22-23-2102      | A-6373-10AG197   |        |                 |            |          |
| 11            | 22-23-2112      | A-6373-11AG197   |        |                 |            |          |
| 12            | 22-23-2122      | A-6373-12AG197   |        |                 |            |          |
| 13            | 22-23-2132      | A-6373-13AG197   |        |                 |            |          |
| 14            | 22-23-2142      | A-6373-14AG197   |        |                 |            |          |
| 15            | 22-23-2152      | A-6373-15AG197   |        |                 |            |          |
| 16            | 22-23-2162      | A-6373-16AG197   |        |                 |            |          |
| 17            | 22-23-2172      | A-6373-17AG197   |        |                 |            |          |
| 18            | 22-23-2182      | A-6373-18AG197   |        |                 |            |          |
| 19            | 22-23-2192      | A-6373-19AG197   |        |                 |            |          |
| 20            | 22-23-2202      | A-6373-20AG197   |        |                 |            |          |
| 21            | 22-23-2212      | A-6373-21AG197   |        |                 |            |          |
| 22            | 22-23-2222      | A-6373-22AG197   |        |                 |            |          |
| 23            | 22-23-2232      | A-6373-23AG197   |        |                 |            |          |
| 24            | 22-23-2242      | A-6373-24AG197   |        |                 |            |          |
| 25            | 22-23-2252      | A-6373-25AG197   |        |                 |            |          |
| 26            | 22-23-2262      | A-6373-26AG197   |        |                 |            |          |
| 27            | 22-23-2272      | A-6373-27AG197   |        |                 |            |          |
| 28            | 22-23-2282      | A-6373-28AG197   |        |                 |            |          |

|                        |                             |                                                            |               |
|------------------------|-----------------------------|------------------------------------------------------------|---------------|
| REV:                   | ECR/ECN INFORMATION:        | TITLE:                                                     | SHEET No.     |
| <b>BD5</b>             | EC No.: <b>UCP2016-4061</b> | <b>KK 100 HEADER ASSEMBLY<br/>FRICTION LOCK SOLID BODY</b> | <b>- 10 -</b> |
|                        | DATE: <b>5/16/2016</b>      |                                                            |               |
| DOCUMENT NUMBER:       |                             | CREATED / REVISED BY:                                      | CHECKED BY:   |
| <b>SD - 6373 - 001</b> |                             | <b>MKIPPER</b>                                             | <b>JBELL</b>  |
|                        |                             | APPROVED BY:                                               |               |
|                        |                             | <b>FSMITH</b>                                              |               |

|               |                    |                  |        |                    |               |             |
|---------------|--------------------|------------------|--------|--------------------|---------------|-------------|
| GROUP:        |                    | A-6373-NAH197-*  |        |                    |               |             |
| PIN NUMBER:   |                    | 42663-0302       |        |                    |               |             |
| PIN LENGTH: L |                    | .560 / (14.22)   |        |                    |               |             |
| MATING: M     |                    | .260 / (6.60)    | DIM. G |                    | N/A           |             |
| PC TAIL: P    |                    | .175 / (4.45)    | DIM T  |                    | OVERALL       |             |
| PACKAGING:    |                    | PK-6373-001 BULK |        |                    |               |             |
| CKTS          | MATERIAL<br>NUMBER | ENG<br>NUMBER    | CKTS   | MATERIAL<br>NUMBER | ENG<br>NUMBER | VOID<br>CKT |
| 2             | 22-23-3020         | A-6373-02AH197   |        |                    |               |             |
| 3             | 22-23-3030         | A-6373-03AH197   |        |                    |               |             |
| 4             | 22-23-3040         | A-6373-04AH197   |        |                    |               |             |
| 5             | 22-23-3050         | A-6373-05AH197   |        |                    |               |             |
| 6             | 22-23-3060         | A-6373-06AH197   |        |                    |               |             |
| 7             | 22-23-3070         | A-6373-07AH197   |        |                    |               |             |
| 8             | 22-23-3080         | A-6373-08AH197   |        |                    |               |             |
| 9             | 22-23-3090         | A-6373-09AH197   |        |                    |               |             |
| 10            | 22-23-3100         | A-6373-10AH197   |        |                    |               |             |
| 11            | 22-23-3110         | A-6373-11AH197   |        |                    |               |             |
| 12            | 22-23-3120         | A-6373-12AH197   |        |                    |               |             |
| 13            | 22-23-3130         | A-6373-13AH197   |        |                    |               |             |
| 14            | 22-23-3140         | A-6373-14AH197   |        |                    |               |             |
| 15            | 22-23-3150         | A-6373-15AH197   |        |                    |               |             |
| 16            | 22-23-3160         | A-6373-16AH197   |        |                    |               |             |
| 17            | 22-23-3170         | A-6373-17AH197   |        |                    |               |             |
| 18            | 22-23-3180         | A-6373-18AH197   |        |                    |               |             |
| 19            | 22-23-3190         | A-6373-19AH197   |        |                    |               |             |
| 20            | 22-23-3200         | A-6373-20AH197   |        |                    |               |             |
| 21            | 22-23-3210         | A-6373-21AH197   |        |                    |               |             |
| 22            | 22-23-3220         | A-6373-22AH197   |        |                    |               |             |
| 23            | 22-23-3230         | A-6373-23AH197   |        |                    |               |             |
| 24            | 22-23-3240         | A-6373-24AH197   |        |                    |               |             |
| 25            | 22-23-3250         | A-6373-25AH197   |        |                    |               |             |
| 26            | 22-23-3260         | A-6373-26AH197   |        |                    |               |             |
| 27            | 22-23-3270         | A-6373-27AH197   |        |                    |               |             |
| 28            | 22-23-3280         | A-6373-28AH197   |        |                    |               |             |

|               |                 |                  |        |                 |                  |          |
|---------------|-----------------|------------------|--------|-----------------|------------------|----------|
| GROUP:        |                 | A-6373-NAJ197-*  |        |                 |                  |          |
| PIN NUMBER:   |                 | 42663-0342       |        |                 |                  |          |
| PIN LENGTH: L |                 | .580 / (14.73)   |        |                 |                  |          |
| MATING:       | M               | .300 / (7.62)    | DIM. G |                 | N/A              |          |
| PC TAIL:      | P               | .155 / (3.94)    | DIM T  |                 | OVERALL          |          |
| PACKAGING:    |                 | PK-6373-001 BULK |        |                 |                  |          |
| CKTS          | MATERIAL NUMBER | ENG NUMBER       | CKTS   | MATERIAL NUMBER | ENG NUMBER       | VOID CKT |
| 2             | 22-23-3023      | A-6373-02AJ197   | 05     | 22-04-6052      | A-6373-05AJ197-1 | 1        |
| 3             | 22-23-3033      | A-6373-03AJ197   | 06     | 22-04-6062      | A-6373-06AJ197-2 | 2        |
| 4             | 22-23-3043      | A-6373-04AJ197   |        |                 |                  |          |
| 5             | 22-23-3053      | A-6373-05AJ197   |        |                 |                  |          |
| 6             | 22-23-3063      | A-6373-06AJ197   |        |                 |                  |          |
| 7             |                 | A-6373-07AJ197   |        |                 |                  |          |
| 8             | 22-23-3083      | A-6373-08AJ197   |        |                 |                  |          |
| 9             | 22-23-3093      | A-6373-09AJ197   |        |                 |                  |          |
| 10            | 22-23-3103      | A-6373-10AJ197   |        |                 |                  |          |
| 11            |                 | A-6373-11AJ197   |        |                 |                  |          |
| 12            |                 | A-6373-12AJ197   |        |                 |                  |          |
| 13            |                 | A-6373-13AJ197   |        |                 |                  |          |
| 14            |                 | A-6373-14AJ197   |        |                 |                  |          |
| 15            | 22-23-3153      | A-6373-15AJ197   |        |                 |                  |          |
| 16            | 22-23-3163      | A-6373-16AJ197   |        |                 |                  |          |
| 17            |                 | A-6373-17AJ197   |        |                 |                  |          |
| 18            |                 | A-6373-18AJ197   |        |                 |                  |          |
| 19            |                 | A-6373-19AJ197   |        |                 |                  |          |
| 20            | 22-23-3203      | A-6373-20AJ197   |        |                 |                  |          |
| 21            |                 | A-6373-21AJ197   |        |                 |                  |          |
| 22            |                 | A-6373-22AJ197   |        |                 |                  |          |
| 23            |                 | A-6373-23AJ197   |        |                 |                  |          |
| 24            |                 | A-6373-24AJ197   |        |                 |                  |          |
| 25            |                 | A-6373-25AJ197   |        |                 |                  |          |
| 26            |                 | A-6373-26AJ197   |        |                 |                  |          |
| 27            |                 | A-6373-27AJ197   |        |                 |                  |          |
| 28            |                 | A-6373-28AJ197   |        |                 |                  |          |

|                                                   |                                                                                                            |                                                                                 |                                        |                                          |  |
|---------------------------------------------------|------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------|----------------------------------------|------------------------------------------|--|
| REV:<br><br><b>BD5</b>                            | <u>ECR/ECN INFORMATION:</u><br><br><u>EC No.:</u> <b>UCP2016-4061</b><br><br><u>DATE:</u> <b>5/16/2016</b> | <u>TITLE:</u><br><br><b>KK 100 HEADER ASSEMBLY<br/>FRICTION LOCK SOLID BODY</b> | <u>SHEET No.</u><br><br><b>- 11 -</b>  |                                          |  |
| <u>DOCUMENT NUMBER:</u><br><b>SD - 6373 - 001</b> |                                                                                                            | <u>CREATED / REVISED BY:</u><br><br><b>MKIPPER</b>                              | <u>CHECKED BY:</u><br><br><b>JBELL</b> | <u>APPROVED BY:</u><br><br><b>FSMITH</b> |  |
| TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC  |                                                                                                            |                                                                                 |                                        |                                          |  |

|               |                    |                        |        |                    |               |             |
|---------------|--------------------|------------------------|--------|--------------------|---------------|-------------|
| GROUP:        |                    | A-6373-NA241A-*        |        |                    |               |             |
| PIN NUMBER:   |                    | 42663-0305             |        |                    |               |             |
| PIN LENGTH: L |                    | .560 / (14.22)         |        |                    |               |             |
| MATING: M     |                    | .295 / (7.49)          | DIM. G |                    | .140 / (3.56) |             |
| PC TAIL: P    |                    | .140 / (3.56)          | DIM T  |                    | .135 / (3.43) |             |
| PACKAGING:    |                    | PK-44743-001 TUBE PACK |        |                    |               |             |
| CKTS          | MATERIAL<br>NUMBER | ENG<br>NUMBER          | CKTS   | MATERIAL<br>NUMBER | ENG<br>NUMBER | VOID<br>CKT |
| 2             |                    |                        |        |                    |               |             |
| 3             | 22-23-1035         | A-6373-03A241A         |        |                    |               |             |
| 4             | 22-23-1045         | A-6373-04A241A         |        |                    |               |             |
| 5             | 22-23-1055         | A-6373-05A241A         |        |                    |               |             |
| 6             | 22-23-1065         | A-6373-06A241A         |        |                    |               |             |
| 7             | 22-23-1075         | A-6373-07A241A         |        |                    |               |             |
| 8             | 22-23-1085         | A-6373-08A241A         |        |                    |               |             |
| 9             | 22-23-1095         | A-6373-09A241A         |        |                    |               |             |
| 10            | 22-23-1105         | A-6373-10A241A         |        |                    |               |             |
| 11            | 22-23-1115         | A-6373-11A241A         |        |                    |               |             |
| 12            | 22-23-1125         | A-6373-12A241A         |        |                    |               |             |
| 13            | 22-23-1135         | A-6373-13A241A         |        |                    |               |             |
| 14            | 22-23-1145         | A-6373-14A241A         |        |                    |               |             |
| 15            | 22-23-1155         | A-6373-15A241A         |        |                    |               |             |
| 16            | 22-23-1165         | A-6373-16A241A         |        |                    |               |             |
| 17            | 22-23-1175         | A-6373-17A241A         |        |                    |               |             |
| 18            | 22-23-1185         | A-6373-18A241A         |        |                    |               |             |
| 19            | 22-23-1195         | A-6373-19A241A         |        |                    |               |             |
| 20            | 22-23-1205         | A-6373-20A241A         |        |                    |               |             |
| 21            | 22-23-1211         | A-6373-21A241A         |        |                    |               |             |
| 22            | 22-23-1222         | A-6373-22A241A         |        |                    |               |             |
| 23            | 22-23-1233         | A-6373-23A241A         |        |                    |               |             |
| 24            | 22-23-1244         | A-6373-24A241A         |        |                    |               |             |
| 25            | 22-23-1255         | A-6373-25A241A         |        |                    |               |             |
| 26            | 22-23-1266         | A-6373-26A241A         |        |                    |               |             |
| 27            | 22-23-1277         | A-6373-27A241A         |        |                    |               |             |
| 28            | 22-23-1288         | A-6373-28A241A         |        |                    |               |             |

|               |                    |                  |          |                    |                  |             |
|---------------|--------------------|------------------|----------|--------------------|------------------|-------------|
| GROUP:        |                    | A-6373-NAL197-*  |          |                    |                  |             |
| PIN NUMBER:   |                    | 42663-1182       |          |                    |                  |             |
| PIN LENGTH: L |                    | 1.000 / (25.40)  |          |                    |                  |             |
| MATING: M     |                    | .295 / (7.49)    | DIM. G   |                    | N/A              |             |
| PC TAIL: P    |                    | .580 / (14.73)   | DIM T    |                    | OVERALL          |             |
| PACKAGING:    |                    | PK-6373-001 BULK |          |                    |                  |             |
| CKTS          | MATERIAL<br>NUMBER | ENG<br>NUMBER    | CK<br>TS | MATERIAL<br>NUMBER | ENG<br>NUMBER    | VOID<br>CKT |
| 2             |                    |                  | 06       | 22-04-6066         | A-6373-06AL197-2 | 2           |
| 3             | 22-23-6032         | A-6373-03AL197   | 06       | 22-04-6067         | A-6373-06AL197-3 | 3           |
| 4             | 22-23-6042         | A-6373-04AL197   |          |                    |                  |             |
| 5             | 22-23-6052         | A-6373-05AL197   |          |                    |                  |             |
| 6             | 22-23-6062         | A-6373-06AL197   |          |                    |                  |             |
| 7             | 22-23-6072         | A-6373-07AL197   |          |                    |                  |             |
| 8             | 22-23-6082         | A-6373-08AL197   |          |                    |                  |             |
| 9             | 22-23-6092         | A-6373-09AL197   |          |                    |                  |             |
| 10            | 22-23-6102         | A-6373-10AL197   |          |                    |                  |             |
| 11            | 22-23-6112         | A-6373-11AL197   |          |                    |                  |             |
| 12            | 22-23-6122         | A-6373-12AL197   |          |                    |                  |             |
| 13            | 22-23-6132         | A-6373-13AL197   |          |                    |                  |             |
| 14            | 22-23-6142         | A-6373-14AL197   |          |                    |                  |             |
| 15            | 22-23-6152         | A-6373-15AL197   |          |                    |                  |             |
| 16            | 22-23-6162         | A-6373-16AL197   |          |                    |                  |             |
| 17            | 22-23-6172         | A-6373-17AL197   |          |                    |                  |             |
| 18            | 22-23-6182         | A-6373-18AL197   |          |                    |                  |             |
| 19            | 22-23-6192         | A-6373-19AL197   |          |                    |                  |             |
| 20            | 22-23-6202         | A-6373-20AL197   |          |                    |                  |             |
| 21            | 22-23-6212         | A-6373-21AL197   |          |                    |                  |             |
| 22            | 22-23-6222         | A-6373-22AL197   |          |                    |                  |             |
| 23            | 22-23-6232         | A-6373-23AL197   |          |                    |                  |             |
| 24            | 22-23-6242         | A-6373-24AL197   |          |                    |                  |             |
| 25            | 22-23-6252         | A-6373-25AL197   |          |                    |                  |             |
| 26            | 22-23-6262         | A-6373-26AL197   |          |                    |                  |             |
| 27            | 22-23-6272         | A-6373-27AL197   |          |                    |                  |             |
| 28            | 22-23-6282         | A-6373-28AL197   |          |                    |                  |             |

|                        |                      |                                                            |               |               |
|------------------------|----------------------|------------------------------------------------------------|---------------|---------------|
| REV:                   | ECR/ECN INFORMATION: | TITLE:                                                     | SHEET No.     |               |
| <b>BD5</b>             | EC No.: UCP2016-4061 | <b>KK 100 HEADER ASSEMBLY<br/>FRICTION LOCK SOLID BODY</b> | <b>- 12 -</b> |               |
|                        | DATE: 5/16/2016      |                                                            |               |               |
| DOCUMENT NUMBER:       |                      | CREATED / REVISED BY:                                      | CHECKED BY:   | APPROVED BY:  |
| <b>SD - 6373 - 001</b> |                      | <b>MKIPPER</b>                                             | <b>JBELL</b>  | <b>FSMITH</b> |

|               |                 |                  |        |                 |            |          |
|---------------|-----------------|------------------|--------|-----------------|------------|----------|
| GROUP:        |                 | A-6373-NAM197-*  |        |                 |            |          |
| PIN NUMBER:   |                 | 42663-0222       |        |                 |            |          |
| PIN LENGTH: L |                 | .520 / (13.21)   |        |                 |            |          |
| MATING: M     |                 | .305 / (7.75)    | DIM. G |                 | N/A        |          |
| PC TAIL: P    |                 | .090 / (2.29)    | DIM T  |                 | OVERALL    |          |
| PACKAGING:    |                 | PK-6373-001 BULK |        |                 |            |          |
| CKTS          | MATERIAL NUMBER | ENG NUMBER       | CKTS   | MATERIAL NUMBER | ENG NUMBER | VOID CKT |
| 2             | 22-23-6023      | A-6373-02AM197   |        |                 |            |          |
| 3             | 22-23-6033      | A-6373-03AM197   |        |                 |            |          |
| 4             | 22-23-6043      | A-6373-04AM197   |        |                 |            |          |
| 5             | 22-23-6053      | A-6373-05AM197   |        |                 |            |          |
| 6             | 22-23-6063      | A-6373-06AM197   |        |                 |            |          |
| 7             | 22-23-6073      | A-6373-07AM197   |        |                 |            |          |
| 8             | 22-23-6083      | A-6373-08AM197   |        |                 |            |          |
| 9             | 22-23-6093      | A-6373-09AM197   |        |                 |            |          |
| 10            | 22-23-6103      | A-6373-10AM197   |        |                 |            |          |
| 11            | 22-23-6113      | A-6373-11AM197   |        |                 |            |          |
| 12            | 22-23-6123      | A-6373-12AM197   |        |                 |            |          |
| 13            | 22-23-6133      | A-6373-13AM197   |        |                 |            |          |
| 14            | 22-23-6143      | A-6373-14AM197   |        |                 |            |          |
| 15            | 22-23-6153      | A-6373-15AM197   |        |                 |            |          |
| 16            | 22-23-6163      | A-6373-16AM197   |        |                 |            |          |
| 17            | 22-23-6173      | A-6373-17AM197   |        |                 |            |          |
| 18            | 22-23-6183      | A-6373-18AM197   |        |                 |            |          |
| 19            | 22-23-6193      | A-6373-19AM197   |        |                 |            |          |
| 20            | 22-23-6203      | A-6373-20AM197   |        |                 |            |          |
| 21            | 22-23-6213      | A-6373-21AM197   |        |                 |            |          |
| 22            | 22-23-6223      | A-6373-22AM197   |        |                 |            |          |
| 23            | 22-23-6233      | A-6373-23AM197   |        |                 |            |          |
| 24            | 22-23-6243      | A-6373-24AM197   |        |                 |            |          |
| 25            | 22-23-6253      | A-6373-25AM197   |        |                 |            |          |
| 26            | 22-23-6263      | A-6373-26AM197   |        |                 |            |          |
| 27            | 22-23-6273      | A-6373-27AM197   |        |                 |            |          |
| 28            | 22-23-6283      | A-6373-28AM197   |        |                 |            |          |

|               |                 |                  |        |                 |               |          |
|---------------|-----------------|------------------|--------|-----------------|---------------|----------|
| GROUP:        |                 | A-6373-NAM241-*  |        |                 |               |          |
| PIN NUMBER:   |                 | 42663-0223       |        |                 |               |          |
| PIN LENGTH: L |                 | .520 / (13.21)   |        |                 |               |          |
| MATING: M     |                 | .305 / (7.75)    | DIM. G |                 | .140 / (3.56) |          |
| PC TAIL: P    |                 | .090 / (2.29)    | DIM T  |                 | .135 / (3.43) |          |
| PACKAGING:    |                 | PK-6373-001 BULK |        |                 |               |          |
| CKTS          | MATERIAL NUMBER | ENG NUMBER       | CKTS   | MATERIAL NUMBER | ENG NUMBER    | VOID CKT |
| 2             | 22-23-6025      | A-6373-02AM241   |        |                 |               |          |
| 3             | 22-23-6035      | A-6373-03AM241   |        |                 |               |          |
| 4             | 22-23-6045      | A-6373-04AM241   |        |                 |               |          |
| 5             | 22-23-6055      | A-6373-05AM241   |        |                 |               |          |
| 6             | 22-23-6065      | A-6373-06AM241   |        |                 |               |          |
| 7             | 22-23-6075      | A-6373-07AM241   |        |                 |               |          |
| 8             | 22-23-6085      | A-6373-08AM241   |        |                 |               |          |
| 9             | 22-23-6095      | A-6373-09AM241   |        |                 |               |          |
| 10            | 22-23-6105      | A-6373-10AM241   |        |                 |               |          |
| 11            | 22-23-6115      | A-6373-11AM241   |        |                 |               |          |
| 12            | 22-23-6125      | A-6373-12AM241   |        |                 |               |          |
| 13            | 22-23-6135      | A-6373-13AM241   |        |                 |               |          |
| 14            | 22-23-6145      | A-6373-14AM241   |        |                 |               |          |
| 15            | 22-23-6155      | A-6373-15AM241   |        |                 |               |          |
| 16            | 22-23-6165      | A-6373-16AM241   |        |                 |               |          |
| 17            | 22-23-6175      | A-6373-17AM241   |        |                 |               |          |
| 18            | 22-23-6185      | A-6373-18AM241   |        |                 |               |          |
| 19            | 22-23-6195      | A-6373-19AM241   |        |                 |               |          |
| 20            | 22-23-6205      | A-6373-20AM241   |        |                 |               |          |
| 21            | 22-23-6215      | A-6373-21AM241   |        |                 |               |          |
| 22            | 22-23-6225      | A-6373-22AM241   |        |                 |               |          |
| 23            | 22-23-6235      | A-6373-23AM241   |        |                 |               |          |
| 24            | 22-23-6245      | A-6373-24AM241   |        |                 |               |          |
| 25            | 22-23-6255      | A-6373-25AM241   |        |                 |               |          |
| 26            | 22-23-6265      | A-6373-26AM241   |        |                 |               |          |
| 27            | 22-23-6275      | A-6373-27AM241   |        |                 |               |          |
| 28            | 22-23-6285      | A-6373-28AM241   |        |                 |               |          |

|                                                   |                                                                                                            |                                                                                 |                                        |                                          |                                       |
|---------------------------------------------------|------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------|----------------------------------------|------------------------------------------|---------------------------------------|
| REV:<br><br><b>BD5</b>                            | <u>ECR/ECN INFORMATION:</u><br><br><u>EC No.:</u> <b>UCP2016-4061</b><br><br><u>DATE:</u> <b>5/16/2016</b> | <u>TITLE:</u><br><br><b>KK 100 HEADER ASSEMBLY<br/>FRICTION LOCK SOLID BODY</b> |                                        |                                          | <u>SHEET No.</u><br><br><b>- 13 -</b> |
| <u>DOCUMENT NUMBER:</u><br><b>SD - 6373 - 001</b> |                                                                                                            | <u>CREATED / REVISED BY:</u><br><br><b>MKIPPER</b>                              | <u>CHECKED BY:</u><br><br><b>JBELL</b> | <u>APPROVED BY:</u><br><br><b>FSMITH</b> |                                       |

|               |                    |                  |        |                    |               |             |
|---------------|--------------------|------------------|--------|--------------------|---------------|-------------|
| GROUP:        |                    | A-6373-NAN241-*  |        |                    |               |             |
| PIN NUMBER:   |                    | 42663-0443       |        |                    |               |             |
| PIN LENGTH: L |                    | .630 / (16.00)   |        |                    |               |             |
| MATING: M     |                    | .300 / (7.62)    | DIM. G |                    | .140 / (3.56) |             |
| PC TAIL: P    |                    | .205 / (5.21)    | DIM T  |                    | .135 / (3.43) |             |
| PACKAGING:    |                    | PK-6373-001 BULK |        |                    |               |             |
| CKTS          | MATERIAL<br>NUMBER | ENG<br>NUMBER    | CKTS   | MATERIAL<br>NUMBER | ENG<br>NUMBER | VOID<br>CKT |
| 2             |                    | A-6373-02AN241   |        |                    |               |             |
| 3             |                    | A-6373-03AN241   |        |                    |               |             |
| 4             | 22-23-6047         | A-6373-04AN241   |        |                    |               |             |
| 5             |                    | A-6373-05AN241   |        |                    |               |             |
| 6             |                    | A-6373-06AN241   |        |                    |               |             |
| 7             |                    | A-6373-07AN241   |        |                    |               |             |
| 8             |                    | A-6373-08AN241   |        |                    |               |             |
| 9             |                    | A-6373-09AN241   |        |                    |               |             |
| 10            |                    | A-6373-10AN241   |        |                    |               |             |
| 11            |                    | A-6373-11AN241   |        |                    |               |             |
| 12            |                    | A-6373-12AN241   |        |                    |               |             |
| 13            |                    | A-6373-13AN241   |        |                    |               |             |
| 14            |                    | A-6373-14AN241   |        |                    |               |             |
| 15            |                    | A-6373-15AN241   |        |                    |               |             |
| 16            |                    | A-6373-16AN241   |        |                    |               |             |
| 17            |                    | A-6373-17AN241   |        |                    |               |             |
| 18            |                    | A-6373-18AN241   |        |                    |               |             |
| 19            |                    | A-6373-19AN241   |        |                    |               |             |
| 20            |                    | A-6373-20AN241   |        |                    |               |             |
| 21            |                    | A-6373-21AN241   |        |                    |               |             |
| 22            |                    | A-6373-22AN241   |        |                    |               |             |
| 23            |                    | A-6373-23AN241   |        |                    |               |             |
| 24            |                    | A-6373-24AN241   |        |                    |               |             |
| 25            |                    | A-6373-25AN241   |        |                    |               |             |
| 26            |                    | A-6373-26AN241   |        |                    |               |             |
| 27            |                    | A-6373-27AN241   |        |                    |               |             |
| 28            |                    | A-6373-28AN241   |        |                    |               |             |

|               |                    |                  |        |                    |               |             |
|---------------|--------------------|------------------|--------|--------------------|---------------|-------------|
| GROUP:        |                    | A-6373-NAB241-*  |        |                    |               |             |
| PIN NUMBER:   |                    | 42663-0583       |        |                    |               |             |
| PIN LENGTH: L |                    | .700 / (17.78)   |        |                    |               |             |
| MATING: M     |                    | .286 / (7.26)    | DIM. G |                    | .200 / (5.08) |             |
| PC TAIL: P    |                    | .289 / (7.34)    | DIM T  |                    | .135 / (3.43) |             |
| PACKAGING:    |                    | PK-6373-001 BULK |        |                    |               |             |
| CKTS          | MATERIAL<br>NUMBER | ENG<br>NUMBER    | CKTS   | MATERIAL<br>NUMBER | ENG<br>NUMBER | VOID<br>CKT |
| 2             | 50-29-1746         | A-6373-02AB241   |        |                    |               |             |
| 3             |                    | A-6373-03AB241   |        |                    |               |             |
| 4             |                    | A-6373-04AB241   |        |                    |               |             |
| 5             |                    | A-6373-05AB241   |        |                    |               |             |
| 6             |                    | A-6373-06AB241   |        |                    |               |             |
| 7             |                    | A-6373-07AB241   |        |                    |               |             |
| 8             | 50-29-1741         | A-6373-08AB241   |        |                    |               |             |
| 9             |                    | A-6373-09AB241   |        |                    |               |             |
| 10            | 50-29-1742         | A-6373-10AB241   |        |                    |               |             |
| 11            |                    | A-6373-11AB241   |        |                    |               |             |
| 12            |                    | A-6373-12AB241   |        |                    |               |             |
| 13            |                    | A-6373-13AB241   |        |                    |               |             |
| 14            |                    | A-6373-14AB241   |        |                    |               |             |
| 15            |                    | A-6373-15AB241   |        |                    |               |             |
| 16            |                    | A-6373-16AB241   |        |                    |               |             |
| 17            |                    | A-6373-17AB241   |        |                    |               |             |
| 18            |                    | A-6373-18AB241   |        |                    |               |             |
| 19            |                    | A-6373-19AB241   |        |                    |               |             |
| 20            |                    | A-6373-20AB241   |        |                    |               |             |
| 21            |                    | A-6373-21AB241   |        |                    |               |             |
| 22            |                    | A-6373-22AB241   |        |                    |               |             |
| 23            |                    | A-6373-23AB241   |        |                    |               |             |
| 24            |                    | A-6373-24AB241   |        |                    |               |             |
| 25            |                    | A-6373-25AB241   |        |                    |               |             |
| 26            |                    | A-6373-26AB241   |        |                    |               |             |
| 27            |                    | A-6373-27AB241   |        |                    |               |             |
| 28            |                    | A-6373-28AB241   |        |                    |               |             |

|                                            |                                                                                           |                                                                         |                             |                               |                                |
|--------------------------------------------|-------------------------------------------------------------------------------------------|-------------------------------------------------------------------------|-----------------------------|-------------------------------|--------------------------------|
| REV:<br><br>BD5                            | <u>ECR/ECN INFORMATION:</u><br><br>EC No.:     UCP2016-4061<br><br>DATE:        5/16/2016 | <u>TITLE:</u><br><br>KK 100 HEADER ASSEMBLY<br>FRICTION LOCK SOLID BODY |                             |                               | <u>SHEET No.</u><br><br>- 14 - |
| <u>DOCUMENT NUMBER:</u><br>SD - 6373 - 001 |                                                                                           | <u>CREATED / REVISED BY:</u><br>MKIPPER                                 | <u>CHECKED BY:</u><br>JBELL | <u>APPROVED BY:</u><br>FSMITH |                                |

|               |                    |                  |        |                    |                  |             |
|---------------|--------------------|------------------|--------|--------------------|------------------|-------------|
| GROUP:        |                    | A-6373-NAN197-*  |        |                    |                  |             |
| PIN NUMBER:   |                    | 42663-0442       |        |                    |                  |             |
| PIN LENGTH: L |                    | .630 / (16.00)   |        |                    |                  |             |
| MATING: M     |                    | .300 / (7.62)    | DIM. G |                    | N/A              |             |
| PC TAIL: P    |                    | .205 / (5.21)    | DIM T  |                    | OVERALL          |             |
| PACKAGING:    |                    | PK-6373-001 BULK |        |                    |                  |             |
| CKTS          | MATERIAL<br>NUMBER | ENG<br>NUMBER    | CKTS   | MATERIAL<br>NUMBER | ENG<br>NUMBER    | VOID<br>CKT |
| 2             |                    |                  | 9      | 50-34-8527         | A-6373-09AN197-7 | 7           |
| 3             |                    |                  |        |                    |                  |             |
| 4             | 50-36-1696         | A-6373-04AN197   |        |                    |                  |             |
| 5             |                    |                  |        |                    |                  |             |
| 6             |                    |                  |        |                    |                  |             |
| 7             |                    |                  |        |                    |                  |             |
| 8             |                    |                  |        |                    |                  |             |
| 9             |                    |                  |        |                    |                  |             |
| 10            |                    |                  |        |                    |                  |             |
| 11            |                    |                  |        |                    |                  |             |
| 12            |                    |                  |        |                    |                  |             |
| 13            |                    |                  |        |                    |                  |             |
| 14            |                    |                  |        |                    |                  |             |
| 15            |                    |                  |        |                    |                  |             |
| 16            |                    |                  |        |                    |                  |             |
| 17            |                    |                  |        |                    |                  |             |
| 18            |                    |                  |        |                    |                  |             |
| 19            |                    |                  |        |                    |                  |             |
| 20            |                    |                  |        |                    |                  |             |
| 21            |                    |                  |        |                    |                  |             |
| 22            |                    |                  |        |                    |                  |             |
| 23            |                    |                  |        |                    |                  |             |
| 24            |                    |                  |        |                    |                  |             |
| 25            |                    |                  |        |                    |                  |             |
| 26            |                    |                  |        |                    |                  |             |
| 27            |                    |                  |        |                    |                  |             |
| 28            |                    |                  |        |                    |                  |             |

|               |                    |                  |        |                    |                 |             |
|---------------|--------------------|------------------|--------|--------------------|-----------------|-------------|
| GROUP:        |                    | A-6373-NA154-*   |        |                    |                 |             |
| PIN NUMBER:   |                    | 42663-0309       |        |                    |                 |             |
| PIN LENGTH: L |                    | .560 / (14.22)   |        |                    |                 |             |
| MATING: M     |                    | .295 / (7.49)    | DIM. G |                    | N/A             |             |
| PC TAIL: P    |                    | .140 / (3.56)    | DIM T  |                    | OVERALL         |             |
| PACKAGING:    |                    | PK-6373-001 BULK |        |                    |                 |             |
| CKTS          | MATERIAL<br>NUMBER | ENG<br>NUMBER    | CKTS   | MATERIAL<br>NUMBER | ENG<br>NUMBER   | VOID<br>CKT |
| 2             |                    |                  | 9      | 26-01-3183         | A-6373-09A154-7 | 7           |
| 3             |                    |                  |        |                    |                 |             |
| 4             |                    |                  |        |                    |                 |             |
| 5             |                    |                  |        |                    |                 |             |
| 6             |                    |                  |        |                    |                 |             |
| 7             |                    |                  |        |                    |                 |             |
| 8             |                    |                  |        |                    |                 |             |
| 9             |                    |                  |        |                    |                 |             |
| 10            |                    |                  |        |                    |                 |             |
| 11            |                    |                  |        |                    |                 |             |
| 12            |                    |                  |        |                    |                 |             |
| 13            |                    |                  |        |                    |                 |             |
| 14            |                    |                  |        |                    |                 |             |
| 15            |                    |                  |        |                    |                 |             |
| 16            |                    |                  |        |                    |                 |             |
| 17            |                    |                  |        |                    |                 |             |
| 18            |                    |                  |        |                    |                 |             |
| 19            |                    |                  |        |                    |                 |             |
| 20            |                    |                  |        |                    |                 |             |
| 21            |                    |                  |        |                    |                 |             |
| 22            |                    |                  |        |                    |                 |             |
| 23            |                    |                  |        |                    |                 |             |
| 24            |                    |                  |        |                    |                 |             |
| 25            |                    |                  |        |                    |                 |             |
| 26            |                    |                  |        |                    |                 |             |
| 27            |                    |                  |        |                    |                 |             |
| 28            |                    |                  |        |                    |                 |             |

|                                            |                                                                                              |                                                                         |                             |                               |                                |
|--------------------------------------------|----------------------------------------------------------------------------------------------|-------------------------------------------------------------------------|-----------------------------|-------------------------------|--------------------------------|
| REV:<br><br>BD5                            | <u>ECR/ECN INFORMATION:</u><br><br><u>EC No.:</u> UCP2016-4061<br><br><u>DATE:</u> 5/16/2016 | <u>TITLE:</u><br><br>KK 100 HEADER ASSEMBLY<br>FRICTION LOCK SOLID BODY |                             |                               | <u>SHEET No.</u><br><br>- 15 - |
| <u>DOCUMENT NUMBER:</u><br>SD - 6373 - 001 |                                                                                              | <u>CREATED / REVISED BY:</u><br>MKIPPER                                 | <u>CHECKED BY:</u><br>JBELL | <u>APPROVED BY:</u><br>FSMITH |                                |