THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST
CE	16

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECR-08-003988	05MAR08	JWD	JD



L METERS [INCHES]	PART NUMBER
15.00±0.15 [591.0±6.0]	1-6374610-5
10.00±0.15 [393.7±6.0]	1-6374610-0
0.304+0.050/-0.0 [12.0+2.0/-0.0]	6374610-7
0.64±0.03 [25.3±1.2]	6374610-6
5.00±0.08 [196.9±3.0]	6374610-5
4.00±0.08 [157.5±3.0]	6374610-4
3.00±0.05 [118.1±2.0]	6374610-3
2.00±0.05 [78.7±2.0]	6374610-2
1.00±0.05 [39.4±2.0]	6374610-1

1. MAX INSERTION LOSS:
   0.5 dB SC
   0.2 dB LC
2. 55 dB MIN RETURN LOSS
3. TRACE LABEL IS PLACED ON IT'S UNIT PACKAGE FOR ASSEMBLIES LESS THAN 1 METER LONG.
4. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF THE TYCO ELECTRONICS STANDARD 230-702

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: METERS [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL -

FINISH -

DWN	C.S.VASU	03 FEB 06
CHK	J.DUNCAN	03 FEB 06
APVD	J.DUNCAN	03 FEB 06

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

Tyco Electronics

Tyco Electronics Corporation
Harrisburg Pa, 17105-3608

NAME
CABLE ASSY, FIBER OPTIC SINGLEMODE BUFFERED FIBER, AMP SC (NG), TO LC
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-6374610	-

CUSTOMER DRAWING

SCALE	SHEET	REV
NTS	1 OF 1	B

AMP 1470-19 REV 31MAR2000