




SWCC - SERIES

Features


- Offered in 5 Heights all with overall width 600mm (23.6")
- Overall depth of 550mm (21.6") includes 100mm (3.9") deep wall mount sections and 450mm (17.7") deep hinged cabinet body
- Quick and easy wall mounting system
- Provides standard 19" rack mounting
- High quality, powder coat finish (black)
- Full-configured assembly includes:
 - Sturdy cold-rolled steel frame
 - Static load capacity of 36 kg (80lbs)
 - Ventilation slots front and side
 - Optional fans can be added into top cutouts
 - Hinged cabinets body can open 120 degrees
 - Body secured to wall mount section by lock and key
 - Wall mount section has cable access panels top and bottom
 - 2 pair of mounting rails
 - Square hole design, 20 screws and push-in nuts
 - 25mm incremental depth adjustment
 - Tempered glass door provides full view of equipment
 - Full 180 degree opening
 - Easily removed and can be hinged in either direction
 - Complete with lock and key
 - Pair of solid removable side panels



SECTION A-A



FRONT VIEW



SIDE VIEW

Part Number	Height (A)	Overall Width (B)	Overall Depth (C)
SWCC1901021BK2	384mm (15.1")6U	600mm (23.6")	550mm (21.7")
SWCC1901521BK2	517mm (20.3")9U	600mm (23.6")	550mm (21.7")
SWCC1902121BK2	650mm (25.6")12U	600mm (23.6")	550mm (21.7")
SWCC1902621BK2	784mm (30.8")15U	600mm (23.6")	550mm (21.7")
SWCC1903121BK2	917mm (36.1")18U	600mm (23.6")	550mm (21.7")



visit our website @ www.hammondmfg.com