REV.	DATE	DESCRIPTION
A	12/29/00	UPDATE PLATING TO SILVER
B	03/21/06	UPDATE DRAWING FORMAT, CHANGE PLATING TO NEXCOTE



	DESCRIPTION	MATERIAL	FINISH	QTY
8				
7				
6				
5				
4	COVER	PE	BLUE	1
3	CONTACT PIN	BRASS	NEXCOTE	1
2	INSULATOR	TEFLON	NATURAL	1
1	HOUSING/BODY	BRASS	NEXCOTE	1

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERANCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
0.5 – 8mm ± 0.20mm
8 – 30mm ± 0.40mm
30 – 120mm ± 0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
.020 – .315 = ± 0.007"
.315 – 1.180 = ± 0.015"
1.180 – 4.724 = ± 0.020"

DO NOT SCALE DRAWING

APPROVALS		DATE
DRAWN	G.R.S.	03/21/06
CHECKED		
ISSUED		
SHEET	1 OF 1	

CAD FILE C:/272/272134.DWG

Amphenol Connex

PART DESCRIPTION
7/16 MALE TO MALE ADAPTER
–

PART NO. 272134

DWG. NO. 272134.DWG | REV. B | SIZE A | SCALE NA