THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST
AF	50

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	M	REVISED PER ECR-13-005733	27AUG2013	KH	PD



1. CONTINUOUS STRIP ON REELS.
2. MATING TAB THK TO BE 0.51±0.025[.020±.001].
3. WIRE SIZE IS [#22-#18] AWG.
4. INSULATION RANGE IS 2.03-3.05 [.080-.120] DIA.

	FINISH	PART NO.
	PRE-TIN	63241-3
OBSOLETE	0.002032 [.000080] MIN TIN	63241-2
	-	63241-1

F	3.56 [.140]	3.96 [.156]	F	1.78 [.070]	0.94 [.037]	[#22]
					1.02 [.040]	[#20]
					1.14 [.045]	[#18]
TYPE	WIDTH	STRIP LENGTH ±0.38 ±[.015]	TYPE	WIDTH	±.051±.002 HEIGHT	WIRE
INSUL BARREL CRIMP		WIRE BARREL CRIMP				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± 0.38 [.015]
3 PLC	± -
4 PLC	± -
ANGLES	± -

MATERIAL: BRASS

FINISH: SEE TABLE

DWN JR RUTH	3/27/97	TE Connectivity
CHK MS FEHER	3/27/97	
APVD J GILLESPIE	3/27/97	NAME: RECEPTACLE, FASTIN-FASTON, 2.79 [.110] SERIES -
PRODUCT SPEC -		
APPLICATION SPEC 114-2065		SIZE A3 · CAGE CODE 00779 · DRAWING NO C-63241 · RESTRICTED TO -
WEIGHT -		
CUSTOMER DRAWING		SCALE 5:1 · SHEET 1 OF 1 · REV M