Search Results

Evaluate
- FAQ's
Design a Solution
- BOM Reference List
- XLS-PD Raceway
- Part Drawings
- DWG-PD Raceway
- PDF-PD Raceway
How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor
Install & Maintain
- Installation Instructions
- PDF-PAN-WAY Type ..

Home > Products Overview > Search Results >

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'PD3EI6-A'**

Your search criteria matched only one product, shown below

PD3EI6-A

Pan-Way® Type PD Surface Raceway is a single channel raceway system to route, protect and conceal power, data, voice, or video cabling.

- UL & CSA rated 600V; meets UL5A and CSA C22.2 No. 62.1-03 standards
- Textured Finish
- Tamper resistant latch design
- Raceway Base and Cover are packaged together
- FT-4 Rated for Canada

For actual product color please refer to the Surface Raceway Color Chart located in selection guides.

Part Number	PD3EI6A
RoHS Compliancy Status	Compliant
Part Description	Raceway Base and Cover packaged together. Raceway Base with pre -applied adhesive backing to speed installation.
Product Type	Power Rated Raceway
Material	PVC
Color	Electric Ivory
CSA Certified	Yes
UL Listed	Yes
Height (In.)	0.36
Length (ft.)	6
Length (In.)	72.00
Width (In.)	0.83
Adhesive Backed	Yes
CE Compliant	No
Channel Type	Single-Channel
Inside Diameter (In.)	(A = 0.14in^2)
Mounting	Adhesive
Pricing Description	PD3 Power Rated, 2-piece Single Channel Raceway with Adh. 6ft.
Product Length	6'
Product Size	3
Raceway Size	0.86" x 0.37"
Min. Order UOM	FT
Min. Order Qty.	6
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy