

Path: [Home](#) > [Enclosure Index](#) > Extruded Aluminum w/ Metal End Panels



(click to enlarge)
**Black Anodized
(Open View)**



(click to enlarge)
**Black Anodized
(Assembled View)**



(click to enlarge)
**Blue Anodized
(Assembled View)**



(click to enlarge)
**Clear Anodized
(Assembled View)**

Key Features:

- Designed to house P.C. boards or for equipment interfacing.
- Sized for standard Eurocards.
- P.C. boards mount horizontally by sliding into internal slots extruded into the enclosure body.
- Rugged body constructed from extruded aluminum with a minimum thickness of .06" (1.5 mm).
- Extruded body includes a slide removable "belly" plate - except in smaller "C" & "D" sizes (ie..1455D601, 1455D801, 1455C801 & 1455C1201 sizes)
- See  "[photo tables](#)" for more visual details.

Includes:

- Two aluminum end panels - finish matched to extruded aluminum body (or link here if you prefer our solid [plastic end panel version](#))
- Two black ABS plastic bezels (your option to install)
- Extruded aluminum body - choice of clear, black or blue anodized finish
- Self adhesive rubber feet.
- All hardware - end panel screws are #6 x 3/8" TTT - thread rolling, steel screws with a #4 flat head phillips drive. Zinc plate finish - either clear or black (black screws are used on the both the black & blue models).
- For black replacement screws (quantity 100) order part number **1455MS100BK**
- For clear replacement screws (quantity 100) order part number **1455MS100**
- NOTE:** Recommended screw torque is 5 lbf/in

Part Number	Anodized Color	PDF Reader File	AutoCAD .dwg Files (zipped)	3D Solid Model .igs & .stp files (zipped)	Units	Length	Width	Height
1455D601 1455D601BK 1455D601BU	Clear Black Blue	 209K	 172K	 206K	Inches	2.36	1.76	0.99
					mm	60	45	25
1455D801 1455D801BK 1455D801BU	Clear Black Blue	 209K	 172K	 206K	Inches	3.15	1.76	0.99
					mm	80	45	25
1455C801 1455C801BK	Clear Black	 193K	 167K	 154K	Inches	3.15	2.13	0.91
					mm	80	54	23

1455C801BU	Blue							
1455C1201	Clear				Inches	4.72	2.13	0.91
1455C1201BK	Black				mm	120	54	23
1455C1201BU	Blue	195K	167K	154K				
1455J1201	Clear				Inches	4.72	3.07	1.06
1455J1201BK	Black				mm	120	78	27
1455J1201BU	Blue	269K	159K	237K				
1455K1201	Clear				Inches	4.72	3.07	1.69
1455K1201BK	Black				mm	120	78	43
1455K1201BU	Blue	197K	174K	213K				
1455L1201	Clear				Inches	4.72	4.06	1.20
1455L1201BK	Black				mm	120	103	30.5
1455L1201BU	Blue	273K	158K	227K				
1455N1201	Clear				Inches	4.72	4.06	2.09
1455N1201BK	Black				mm	120	103	53
1455N1201BU	Blue	173K	175K	230K				
1455J1601	Clear				Inches	6.30	3.07	1.06
1455J1601BK	Black				mm	160	78	27
1455J1601BU	Blue	270K	155K	237K				
1455K1601	Clear				Inches	6.30	3.07	1.69
1455K1601BK	Black				mm	160	78	43
1455K1601BU	Blue	216K	175K	214K				
1455L1601	Clear				Inches	6.30	4.06	1.20
1455L1601BK	Black				mm	160	103	30.5
1455L1601BU	Blue	269K	162K	240K				
1455N1601	Clear				Inches	6.30	4.06	2.09
1455N1601BK	Black				mm	160	103	53
1455N1601BU	Blue	172K	173K	230K				
1455P1601	Clear				Inches	6.30	4.92	1.20
1455P1601BK	Black				mm	160	125	30.5
1455P1601BU	Blue	266K	161K	250K				
1455Q1601	Clear				Inches	6.30	4.92	2.03
1455Q1601BK	Black				mm	160	125	51.5
1455Q1601BU	Blue	271K	164K	291K				
1455R1601	Clear				Inches	6.30	6.50	1.20
1455R1601BK	Black				mm	160	165	30.5
1455R1601BU	Blue	201K	179K	264K				
1455T1601	Clear				Inches	6.30	6.50	2.03
1455T1601BK	Black				mm	160	165	51.5
1455T1601BU	Blue	151K	183K	298K				
1455L2201	Clear				Inches	8.66	4.06	1.20
1455L2201BK	Black				mm	220	103	30.5
1455L2201BU	Blue	261K	161K	240K				
1455N2201	Clear				Inches	8.66	4.06	2.09
1455N2201BK	Black				mm	220	103	53
1455N2201BU	Blue	200K	178K	230K				
1455P2201	Clear				Inches	8.66	4.92	1.20
1455P2201BK	Black				mm	220	125	30.5
1455P2201BU	Blue	261K	163K	250K				
1455Q2201	Clear				Inches	8.66	4.92	2.03
1455Q2201BK	Black				mm	220	125	51.5
1455Q2201BU	Blue	274K	164K	291K				
1455R2201	Clear				Inches	8.66	6.50	1.20

1455R2201BK 1455R2201BU	Black Blue	 204K	 178K	 264K	mm	220	165	30.5
1455T2201 1455T2201BK 1455T2201BU	Clear Black Blue	 155K	 194K	 298K	Inches	8.66	6.50	2.03
					mm	220	165	51.5



Link here to [photo tables](#) of each part number

Color Options:



(click to enlarge)



(click to enlarge)

- Choose either black anodized or clear anodized or blue anodized
- Note that aluminum front & back panels match the enclosure color

Accessories

Wallmount Options:



(click to enlarge)



(click to enlarge)

- Designed to convert these enclosures where shelf or wall mounting is required
- Flanges are .064" (1.6 mm) thick aluminum foot "L" brackets and attach to each end, replacing the aluminum end panels
- Finish available in both clear & black anodized to match enclosure
- **SOLD IN PAIRS**

Part Number	Color	 Reader File	AutoCAD .dwg Files (zipped)	3D Solid Model .igs & .stp files (zipped)	USE WITH ENCLOSURE
1455CF 1455CFBK	Clear Black	 142K	 94K	 24K	Any part above starting with 1455C
1455JF 1455JFBK	Clear Black	 174K	 83K	 25K	Any part above starting with 1455J
1455KF 1455KFBK	Clear Black	 159K	 118K	 23K	Any part above starting with 1455K
1455LF 1455LFBK	Clear Black	 159K	 118K	 23K	Any part above starting with 1455L

		160K	110K	25K	
1455NF 1455NFBK	Clear Black	 165K	 111K	 25K	Any part above starting with 1455N
1455PF 1455PFBK	Clear Black	 180K	 112K	 87K	Any part above starting with 1455P
1455QF 1455QFBK	Clear Black	 145K	 113K	 25K	Any part above starting with 1455Q
1455RF 1455RFBK	Clear Black	 143K	 111K	 25K	Any part above starting with 1455R
1455TF 1455TFBK	Clear Black	 150K	 111K	 25K	Any part above starting with 1455T

Replacement Parts & Bezel Options:



(click to enlarge)

Aluminum Clear End Plate



(click to enlarge)

Aluminum Black End Plate



(click to enlarge)

Aluminum Blue End Plate



(click to enlarge)

Black Plastic - Open Bezel

USE WITH (Enclosure Part Number)	Aluminum Clear End Plate (10 Pack)	Aluminum Black End Plate (10 Pack)	Aluminum Blue End Plate (10 Pack)	Black Plastic Open Bezel	
				(2 Pack)	(10 Pack)
1455D601	1455DAL-10	1455DALBK-10	1455DALBU-10	1455DBBK	1455DBBK-10
1455D801	1455DAL-10	1455DALBK-10	1455DALBU-10	1455DBBK	1455DBBK-10
1455C801	1455CAL-10	1455CALBK-10	1455CALBU-10	1455CBBK	1455CBBK-10
1455C1201	1455CAL-10	1455CALBK-10	1455CALBU-10	1455CBBK	1455CBBK-10
1455J1201	1455JAL-10	1455JALBK-10	1455JALBU-10	1455JBBK	1455JBBK-10
1455K1201	1455KAL-10	1455KALBK-10	1455KALBU-10	1455KBBK	1455KBBK-10
1455L1201	1455LAL-10	1455LALBK-10	1455LALBU-10	1455LBBK	1455LBBK-10
1455N1201	1455NAL-10	1455NALBK-10	1455NALBU-10	1455NBBK	1455NBBK-10
1455J1601	1455JAL-10	1455JALBK-10	1455JALBU-10	1455JBBK	1455JBBK-10
1455K1601	1455KAL-10	1455KALBK-10	1455KALBU-10	1455KBBK	1455KBBK-10
1455L1601	1455LAL-10	1455LALBK-10	1455LALBU-10	1455LBBK	1455LBBK-10
1455N1601	1455NAL-10	1455NALBK-10	1455NALBU-10	1455NBBK	1455NBBK-10
1455P1601	1455PAL-10	1455PALBK-10	1455PALBU-10	1455PBBK	1455PBBK-10
1455Q1601	1455QAL-10	1455QALBK-10	1455QALBU-10	1455QBBK	1455QBBK-10
1455R1601	1455RAL-10	1455RALBK-10	1455RALBU-10	1455RBBK	1455RBBK-10
1455T1601	1455TAL-10	1455TALBK-10	1455TALBU-10	1455TBBK	1455TBBK-10
1455L2201	1455LAL-10	1455LALBK-10	1455LALBU-10	1455LBBK	1455LBBK-10
1455N2201	1455NAL-10	1455NALBK-10	1455NALBU-10	1455NBBK	1455NBBK-10
1455P2201	1455PAL-10	1455PALBK-10	1455PALBU-10	1455PBBK	1455PBBK-10
1455Q2201	1455QAL-10	1455QALBK-10	1455QALBU-10	1455QBBK	1455QBBK-10

1455R2201	1455RAL-10	1455RALBK-10	1455RALBU-10	1455RBBK	1455RBBK-10
1455T2201	1455TAL-10	1455TALBK-10	1455TALBU-10	1455TBBK	1455TBBK-10



(click to enlarge)

Red ABS Plastic - Open Bezel



(click to enlarge)

Yellow ABS Plastic - Open Bezel

USE WITH (Enclosure Part Number)	Red		Yellow	
	(2 Pack)	(10 Pack)	(2 Pack)	(10 Pack)
1455C801	1455CBRED	1455CBRED-10	1455CBY	1455CBY-10
1455C1201	1455CBRED	1455CBRED-10	1455CBY	1455CBY-10
1455J1201	1455JBRED	1455JBRED-10	1455JBY	1455JBY-10
1455K1201	1455KBRED	1455KBRED-10	1455KBY	1455KBY-10
1455L1201	1455LBRED	1455LBRED-10	1455LBY	1455LBY-10
1455N1201	1455NBRED	1455NBRED-10	1455NBY	1455NBY-10
1455J1601	1455JBRED	1455JBRED-10	1455JBY	1455JBY-10
1455K1601	1455KBRED	1455KBRED-10	1455KBY	1455KBY-10
1455L1601	1455LBRED	1455LBRED-10	1455LBY	1455LBY-10
1455N1601	1455NBRED	1455NBRED-10	1455NBY	1455NBY-10
1455P1601	1455PBRED	1455PBRED-10	1455PBY	1455PBY-10
1455Q1601	1455QBRED	1455QBRED-10	1455QBY	1455QBY-10
1455R1601	1455RBRED	1455RBRED-10	1455RBY	1455RBY-10
1455T1601	1455TBRED	1455TBRED-10	1455TBY	1455TBY-10
1455L2201	1455LBRED	1455LBRED-10	1455LBY	1455LBY-10
1455N2201	1455NBRED	1455NBRED-10	1455NBY	1455NBY-10
1455P2201	1455PBRED	1455PBRED-10	1455PBY	1455PBY-10
1455Q2201	1455QBRED	1455QBRED-10	1455QBY	1455QBY-10
1455R2201	1455RBRED	1455RBRED-10	1455RBY	1455RBY-10
1455T2201	1455TBRED	1455TBRED-10	1455TBY	1455TBY-10



(click to enlarge)



(click to enlarge)



(click to enlarge)

**Translucent Blue
Polycarbonate - Open Bezel**



(click to enlarge)

**Translucent (IR) Red
Polycarbonate - Open Bezel**

USE WITH (Enclosure Part Number)	Translucent Blue		Translucent Red	
	(2 Pack)	(10 Pack)	(2 Pack)	(10 Pack)
1455C801	1455CBTBU	1455CBTBU-10	1455CBTRD	1455CBTRD-10
1455C1201	1455CBTBU	1455CBTBU-10	1455CBTRD	1455CBTRD-10
1455J1201	1455JBTBU	1455JBTBU-10	1455JBTRD	1455JBTRD-10
1455K1201	1455KBTBU	1455KBTBU-10	1455KBTRD	1455KBTRD-10
1455L1201	1455LBTBU	1455LBTBU-10	1455LBTRD	1455LBTRD-10
1455N1201	1455NBTBU	1455NBTBU-10	1455NBTRD	1455NBTRD-10
1455J1601	1455JBTBU	1455JBTBU-10	1455JBTRD	1455JBTRD-10
1455K1601	1455KBTBU	1455KBTBU-10	1455KBTRD	1455KBTRD-10
1455L1601	1455LBTBU	1455LBTBU-10	1455LBTRD	1455LBTRD-10
1455N1601	1455NBTBU	1455NBTBU-10	1455NBTRD	1455NBTRD-10
1455P1601	1455PBTBU	1455PBTBU-10	1455PBTRD	1455PBTRD-10
1455Q1601	1455QBTBU	1455QBTBU-10	1455QBTRD	1455QBTRD-10
1455R1601	1455RBTBU	1455RBTBU-10	1455RBTRD	1455RBTRD-10
1455T1601	1455TBTBU	1455TBTBU-10	1455TBTRD	1455TBTRD-10
1455L2201	1455LBTBU	1455LBTBU-10	1455LBTRD	1455LBTRD-10
1455N2201	1455NBTBU	1455NBTBU-10	1455NBTRD	1455NBTRD-10
1455P2201	1455PBTBU	1455PBTBU-10	1455PBTRD	1455PBTRD-10
1455Q2201	1455QBTBU	1455QBTBU-10	1455QBTRD	1455QBTRD-10
1455R2201	1455RBTBU	1455RBTBU-10	1455RBTRD	1455RBTRD-10
1455T2201	1455TBTBU	1455TBTBU-10	1455TBTRD	1455TBTRD-10



catalog pages on this series (193K) [9C-1455.pdf](#)

Exactly what you are looking for???

Link to our stocking distributors - most have "on-line" pricing, stock check and ordering!!!

Our Distributors

[Order from your favorite distributor](#)

[Home](#) | [Products](#) | [Distributors](#) | [Technical](#) | [Contact Us](#) | [Other Options](#)