

Material:

- Conductor: 24AWG 7*0.19±0.015mm
- Conductor Insulation color coding: (1) White/Orange, (1) Orange, (1) White/Green, (1) Green, (1) Blue, (1) White/Blue, (1) White/Brown, (1) Brown
- Cable jacket printing: DIGITUS Cat6 U-UTP PATCH CORD ISO/IEC 11801 & TIA/EIA 568-B.2-1 24AWGx4p CM(UL) C(UL)
- Wiring T568B Color
- P1 & P2 Contact plug: RJ45 8P8C 3µ" pc UL 94V-2
- Cable tie: White
- Cable jacket color: Black, White, Blue, or Grey
- Dielectric strength: 2.5KV dc-2seconds
- Working temperatures: -20°C ~ +60°C

PIN OUT

P1	WIRE COLOR	P2
1	ORANGE/WHITE	1
2	ORANGE	2
3	GREEN/WHITE	3
6	GREEN	6
4	BLUE	4
5	BLUE/WHITE	5
7	BROWN/WHITE	7
8	BROWN	8





Unit: mm



Order Code: DK-1611-**xxx/x**

Order lengths in feet: 1,3,5,7,10,15, 20,25,50,100

Cable Jacket colors: Black(BL), White(WH), Blue(B), Green(GR), or Grey(G)

RoHS Compliant

Scale	Free
TOLERANCE	
X.	±0.3
X.X	±X
X.XX	±X
DIM	TOL
X.°	±X°
X.X°	±X°
Angle	TOL

Id.	Modification	Date	Name
0	Drawn	25.04.13	Wilson

	Date	Name
Drawn	25.04.13	Wilson
Approved	28.04.13	Groll

ASSMANN WSW components

1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283
Toll Free: 1-877-277-6266 • Email: info@assmann.us

Title
Cat6 UTP Patch cable
Unshielded/Booted, 24AWG, 3µ"

ASSMANN WSW-No.
DK-1611-xxx/x

Drawing-No.

rev00

Replace

Sheet 1/1