PRODUCT FAMILIES

- Pin Headers and Sockets
- Clips and Insulators
- Banana Plugs and Jacks
  - Banana Plugs
  - Banana Jacks
  - Binding Posts
  - Safety Sockets
- Grabbers, Probes and Spade Terminals
- Test Leads and Patch Cords
- Coaxial Cable Assemblies
- DMM Kits

ISO 9001:2000

Banana Plugs

A pioneer and leader in the manufacture of alligator clips, test leads, and banana plugs.
While the founder of **Mueller Electric Company** invented alligator clips, the company has since expanded its product lines into electric test clips, test leads, test accessories, and board to board connectors, sold to qualifying manufacturers and through leading authorized distributors. Browse our selection of banana plug and banana jack configurations as well as check available inventory.

SEARCH TOOLS

MUELLER OR AUTOMATION STOCK SEARCH
PART #
SEARCH

COMPARE COMPETITOR PART #
Choose a Brand
PART #
SEARCH

MatedMate® DMM ACCESSORY SELECTOR
Select Meter Make
Select a Make First

BUILD A PCB HEADER OR SOCKET
OVER 12,000 IN STOCK!
GO

Banana Plug With 8-32 Thread

Model # BU-00226-*

- Material: Banana plug: nickel-plated brass body, nickel-plated phosphor bronze spring; Insulator: ABS
- Length: 1.66 in (42.13mm)
- *Std. Colors: -0 Black, -2 Red
- Rating: 1000 Volts, 15 Amps (hands free)

Cable mountable 4mm Shrouded Banana Plug

Model# BU-32603-*

- Material: Banana plug: nickel-plated brass; Insulator: nylon
- Length: 1.91 in (48.5mm)
- *Std. Colors: -0 Black, -2 Red
- Rating: 1000V, category III 1500V, category II 20 Amps, IEC 1010 Compliant

Insulated Banana Jack To Standard Banana Plug

Model# BU-32101-*

- Material: Banana plug: nickel-plated brass body, nickel-plated beryllium copper spring; Insulator: nylon
- Length: 2.61 in (66.3mm)
- *Std. Colors: -0 Black, -2 Red, -4 Yellow & -6 Blue
- Rating: 1000 V, 15 Amps (hands free), IEC 1010 Compliant

Insulated Stackable Banana Plug

Model# BU-31101-*

- Material: Banana plug: nickel-plated brass body, nickel-plated beryllium copper spring; Insulator: Nylon
- Length: 0.91 in (22.23mm)
- *Std. Colors: -0 Black, -2 Red
- Rating: 20 Amps

Solderless Banana Plug-Hex Design

Model# BU-00245-*

- Material: Banana plug: nickel-plated brass body, nickel-plated phosphor bronze spring; Insulator: ABS
- Length: 1.08 in (27mm)
- *Std. Colors: -0 Black, -2 Red
- Rating: 15 Amps

Solderless Banana Plug-Hex Design

Model# BU-00244-*

- Material: Banana plug: nickel-plated brass body, nickel-plated phosphor bronze spring; Insulator: ABS
- Length: 1.15 in (29mm)
- *Std. Colors: -0 Black, -2 Red
- Rating: 15 Amps

Insulated Phone Tip Jack

Model# BU-00243-*

- Material: Banana plug: nickel-plated brass body, nickel-plated phosphor bronze spring; Insulator: ABS
- Length: 1.1 in (28mm)
- *Std. Colors: -0 Black, -2 Red
- Rating: 15 Amps

Stackable Banana Plug

Model# BU-00249-*

- Material: Banana plug: nickel-plated brass body, nickel-plated phosphor bronze spring; Insulator: ABS
- Length: 1.68 in (43mm)
- *Std. Colors: -0 Black, -2 Red
- Rating: 15 Amps

Tapered Handle Banana Plug

Model# BU-00246-*

- Material: Banana plug: nickel-plated brass body, nickel-plated phosphor bronze spring; Insulator: ABS
- Length: 1.02 in (26mm)
- *Std. Colors: -0 Black, -2 Red
- Rating: 15 Amps

Insulated Phone Tip Jack

Model# BU-00241-*

- Material: Banana plug: nickel-plated brass body, nickel-plated phosphor bronze spring
- Length: 1.21 in (31mm)
- Rating: 15 Amps

Unshrouded Stackable Banana Plug

Model# BU-16-*

- Material: Banana plug: nickel-plated brass body, nickel-plated beryllium copper spring; Insulator: Nylon
- Length: 1.88 in (47.7mm)
- *Std. Colors: -0 Black, -2 Red
- Rating: 1000 Volts, 15 Amps (Hands free)