samtec



(2,54mm) .100"

CLH SERIES

THROUGH-HOLE LOW PROFILE SOCKET

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?CLH

Insulator Material:
Black Liquid Crystal Polymer
Contact Material:
Phosphor Bronze
Operating Temp Range:
-65°C to +125°C with Gold
-65°C to +105°C with Tin
Plating:
Au or Sn over 50µ" (1,27µm) Ni
Contact Resistance:
10 mΩ max
Insertion Depth:
(2,67mm) .105" to (3,43mm) .135" plug from top, (3,18mm) .125" min plus board thickness plug from bottom
Insertion Force:
4.0oz (1,11N) average
Normal Force:
50 grams (0,48N)
Withdrawal Force:
1.1oz (0,31N) average
Max Cycles:
100 with 10µ" (0,25µm) Au
RoHS Compliant:
Yes

FILE NO. E111594

Processing:

Lead–Free Solderable:
Yes

Note: Some lengths, styles and options are non-standard, non-returnable.

CLH – 1 – NO. PINS PER ROW – PLATING OPTION – D – ENTRY OPTION

Mates with:
TSW, MTSW, DW, EW, ZW, TLW, TSM, MTLW

–F
= Pre-plated Gold flash on contact, 75µ" (1,91µm) Matte Tin on tail

–L
= Pre-plated 10µ" (0,25µm) Gold on contact, 75µ" (1,91µm) Matte Tin on tail

Note: Other Gold plating options available. Contact Samtec.

–TE
= Top Entry



–DE
= Dual Entry (Top or Bottom Entry) Cannot be used with plated through-holes for bottom entry.



–PE
= Pass-Through (Top or Bottom Entry)



02 thru 50



TIGER CLAW CONTACT™

Due to technical progress, all designs, specifications and components are subject to change without notice.

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 **SAMTEC SILICON VALLEY** • Tel: 408-395-5900 **SAMTEC SOUTHERN CALIFORNIA** • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 **SAMTEC UNITED KINGDOM** • Tel: 44 01236 739292 **SAMTEC GERMANY** • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 **SAMTEC ITALY** • Tel: 39 039 6890337 **SAMTEC NORDIC/BALTIC** • Tel: +46-84477280 **SAMTEC BENELUX** • Tel: 44 01236 739292 **SAMTEC ISRAEL** • Tel: 972-3-7526600
SAMTEC INDIA • Tel: +91-80-3272 1612 **SAMTEC ASIA PACIFIC** • Tel: 65 6745-5955 **SAMTEC JAPAN** • Tel: 045-475-1385 **SAMTEC CHINA** • Tel: 86-21-61103766 **SAMTEC TAIWAN** • Tel: 886-2-2735-6109
SAMTEC HONG KONG • Tel: 852-26904858 **SAMTEC KOREA** • Tel: 82-31-717-5685 **SAMTEC ANZ** • Tel: 613 9512 7747 **SAMTEC SOUTH AFRICA** • Tel: 27 11 452 8112