

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300410013

Status:


Active

Overview:

Brad Mini-Change Connectors

Description:

Mini-Change A-Size Single-Ended Cordset, 4 Poles, Female (90°) to Pigtail, 18 AWG, PVC Cable, 2.0m (6.56') Length, Nickel (Ni) Plated Brass Coupler



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Cordsets
Series	130041
Connector End A	Mini-Change
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Mini-Change Connectors
Product Name	Mini-Change
Protocol	N/A
Region	America, Asia, Europe
Type	Single Ended
UPC	78172504925
Physical	
Cable Diameter	7.37mm (.290")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Orange
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	4
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	18
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	7.0A
Voltage - Maximum	300V
Material Info	
Engineering Number	104001D09M020
Reference - Drawing Numbers	
Sales Drawing	SD-130041-002

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130041 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION