Search Results

Evaluate
- FAQ's
Design a Solution
- Part Drawings
- PDFFiber Optic..
How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'F5LD2-2M9'**

Your search criteria matched only one product, shown below

F5LD2-2M9

- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- SC Duplex Patch Cords include SC Duplex Clips to maintain polarity
- Highest quality flame retardant fiber optic cable with tight -buffered coating on each optical fiber

Additional lengths and availability: Patch cords are available in 1 – 10 meter lengths in 1 meter increments, and 15, 20, 25 and 30 meter lengths. Pigtails are available in 1, 2, and 3 meter lengths. Ex: To order lengths other than 1 meter, replace the 1 after the M (FXE10-10M1Y) with the desired length (FXE10-10M2Y for 2 meter length). The above lengths are stock items. For other lengths, contact Customer Service for actual lead times.

Part Number	F5LD2-2M9
RoHS Compliancy Status	Compliant
Part Description	ST to ST multimode duplex patch cord, 3mm jacketed cable (two ST connectors on each end) - 50/125?m.
Product Type	ST Patch Cords
Length (m)	9
Fiber Compatibility	50/125?m
Fiber Cable Size	3mm
Fiber Cable Type	Jacketed
Fiber Type	Multimode
CE Compliant	No
Connector 1 Type	ST Connector
Connector 2 Type	ST Connector
End Configurations	ST to ST
Fiber Count	2
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy