Search Results

Evaluate
- Approvals
- PDF FDA Complian
- FAQ's
- Product Bulletins
- PDF Metal Detect..

Design a Solution
- Catalog Cut Sheet
- PDF PLT1M-C86 Pr
- Part Drawings
- PDF Pan-Ty Metal..

How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor



Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'PLT1M-C186'**

**Your search criteria matched only one product, shown below**

## PLT1M-C186

- Metal impregnated material allows identification by metal detectors or x -ray inspection to meet food, beverage and pharmaceutical safety standards by helping to reduce product contamination
- One-piece design with locking wedge provides low thread force and reliable installation to improve productivity and reduce operator fatigue
- Distinct blue color per common industry practices provides easy identification on conveyor belts and in finished products, reducing waste due to product contamination
- Excellent chemical resistance for food and pharmaceutical processing equipment manufacturing applications
- For use in processing and packaging areas where aggressive acid and alkaline chemicals are used to clean the equipment
- For indoor use

| | |
|---|---|
| Part Number | PLT1M-C186 |
| RoHS Compliancy Status | Compliant |
| Part Description | Cable Tie, 3.9"L (100mm), Metal Detectable Polypropylene, Miniature cross section, Dark Blue |
| Product Type | Cable Ties |
| Material | Metal Impregnated Polypropylene |
| Color | Dark Blue |
| CSA Certified | No |
| UL Listed (File #E56854) | No |
| UL Recognized (File #E56854) | No |
| Length (In.) | 3.9 |
| Length (mm) | 100 |
| Width (In.) | 0.098 |
| Width (mm) | 2.5 |
| CE Compliant | No |
| Cross Section | Miniature |
| Head Height (In.) | 0.186 |
| Head Height (mm) | 4.8 |
| Head Width (In.) | 0.188 |
| Head Width (mm) | 4.8 |
| Locking Style | Locking |
| Material Flammability Rating | HB |
| Max. Bundle Diameter (In.) | 0.87 |
| Max. Bundle Diameter (mm) | 22 |
| Max. Continuous Use Temperature | 239°F (115°C) |
| Min. Bundle Diameter (In.) | 0.13 |
| Min. Bundle Diameter (mm) | 3.3 |
| Min. Loop Tensile Strength (Lbs.) | 15 |
| Min. Loop Tensile Strength (N) | 67 |
| Plenum-Rated | No |
| Pricing Description | Cable Tie, 3.9"L (100mm), Miniature, Metal Detectable Polypropylene, Dark Blue |
| Thickness (In.) | 0.044 |
| Thickness (mm) | 1.1 |
| Tool | GTS, GTSL, GS2B, STS2 |
| Min. Order UOM | PC |
| Min. Order Qty. | 100 |
| BOM Qty. (# of Pkgs.) | 0 |
| Add to Favorite Product List | e |

**Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.**


Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy