


ALUMINUM BATTERY HOLDERS

A standard line of battery holders available for immediate shipment from stock. Low cost, lightweight and sturdily constructed of quality materials. Good electrical contact, low leakage current and snap-fit clips are the outstanding features.

MODIFICATIONS: We welcome the opportunity to quote on variations of standard items. Use our engineering service for your special custom-built holders. Holders with PC and Quick-Fit terminals available on special order.



- Brass Eyelets, Nickel Plate
- Brass Lugs, Nickel Plate
- Moisture Proof, Resin Impregnated, Fibre Insulating Washers
- Aluminum 2024-T3, Frame & Clip




FIG. 1




FIG. 2




FIG. 4




FIG. 5




FIG. 8




FIG. 12



FIG. 9




FIG. 10




FIG. 11






FIG. 14

POLARITY INDICATING LABEL

- No Gluing or Wetting Needed
- Economical
- Pressure Sensitive Adhesive Back
- Adheres To All Surfaces

Recommended where proper polarity of battery insertion or circuit polarity is to be shown. Labels are two color, (+) positive side red; arrow, (-) negative side blue.



CAT. NO. 58

**Ideal for Alkaline, Carbon, Zinc, NiMH
NiCd and Lithium Cells.**

DIMENSIONAL DRAWINGS ON THE FOLLOWING PAGE

BATTERY CROSS REFERENCE			
All Batteries listed within boxes are in the same size group			
CAT. NO.	HOLDS NO. OF CELLS	FIG. NO.	
EVEREADY			
DURACELL			
RAY-O-VAC			
NEDA			
"AAA" CELL HOLDER (BATTERY SIZE .375 .468 O.D. × 1.673 1.752 H)			
137	1	1	
138	2	2	E92, M24F, 824, 24A, 24F, 24P
169	3	3	912, CH12, MN2400
170	4	4	
"AA" CELL HOLDERS (BATTERY SIZE .531 .565 O.D. × 1.906 1.988 H)			
139	1	1	
140	2	2	E9, EV15, EN91, CH15, E91, E133, E133N, E177, 505, 523, 1015, 1215
171	3	3	ZM9, RM12R, NC15AA, M15F, M15AA, TR133R, TR177, M505, MN1500, PC 1500
182	4	4	5AA, 615, 815, 7AA
189	2	5	15, 15A, 15C, 15D, 15F, 15M, 15NC, 221, 1101M, 1113M, 1306AP, 1306M, 1314M, 1606M
192	4	7	
193	6	8	
"C" CELL HOLDERS (BATTERY SIZE .875 1.125 O.D. × 1.875 1.969 H)			
173	1	1	
174	2	2*	CH35, E93, 935, 1235, EV35, EN93
187	3	3	M14F, M14HD, NC14C, TR286, MN1400, PC1400
185	2	5	1C, 614, 814
196	4	7*	14A, 14C, 14D, 14F, 14NC, 1600M
197	6	8	
"D" CELL HOLDERS (BATTERY SIZE 1.187 1.375 O.D. × 2.312 2.412 H)			
175	1	1	
176	2	2*	CH50, E95, 950, 1250, EV50, EN95
190	3	3	M13F, NC13D, S42, M13HD, TR289, MN1300, PC1300
186	2	5	2D, 6D, 613, 813
200	4	7*	13A, 13C, 13D, 13F, 13NC, 1115M, 1810M
201	6	8	
205	6	12*	
"N" CELL HOLDERS (BATTERY SIZE .375 .468 O.D. × 1.110 1.189 H)			
154	1	1	E90, E340E, E401E, EP401E
155	2	2	MP401H
156	3	3	R401, RP401, 810
			910A, 910F, 910M, 1117M, 1118M, MN9100
"9 VOLT" BATTERY HOLDERS			
139B	1	1	206, M1611, 1611
173P	1	1	226, —, 1600
203P	1	10	CH22, EN22, E146X, 216, 522, 1222, E303396
1290	REF. PAGE 21		TR146X, M1604, M1604HD, MN1604, PC146X, PC1604
1291			A1604, D1604, 1604
			1604, 1604A, 1604C, 1604D, 1604M, 1604NC, 1619M
"15 VOLT" BATTERY HOLDERS			
163	1	9	—, —, —, 224
161	1	9	—, —, —, 208
166	1	11	411, —, —, 215
167	2	14	—, —, —, 220
225	1	1	504, —, —, —
226	2	2	—, —, —, —
"22 1/2 VOLT" BATTERY HOLDERS			
139	1	1	505, —, —, 221
168	1	9	420, —, —, 225
177	1	11	412, M215, —, 215
178	2	14	—, —, —, —
"30 VOLT" BATTERY HOLDERS			
183	1	11	413, —, —, 210
184	2	14	—, —, —, —

*"C" Cell Holders-Dual Cat. No. 97 clips used

"D" Cell Holders-Dual Cat. No. 98 clips used