Search Results

Evaluate
- FAQ's
Design a Solution
- Part Drawings
- PDF-Networked PO ..
How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'QZ1B2T3BN3631'**

Your search criteria matched only one product, shown below

QZ1B2T3BN3631

• Remote access to power consumption data via a web -based GUI provides global network access to real -time power information
• Integrates with Panduit ® PIM™ Software which aggregates power information through a single web based GUI interface
• Integrated power monitoring and management with on unit display provides true RMS input current load (in amps) for each power circuit or phase to properly load balance and maximize power circuits
• Provides user -defined alarm/messaging capabilities for specific events that exceeded thresholds
• Mounting buttons allow tool -less installation of power strips

Part Number	QZ1B2T3BN3631
RoHS Compliancy Status	Compliant
Part Description	Vertical power strip 35 A, 208V, Delta, 30 IEC G13 and 6 IEC C19 receptacles, RJ-45 Ethernet port with red LED current monitor, three 20 A double pole magnetic breaker on-off switch with integral switch guard, and 10' power cord with California Style 50 Amp, Twistlock Plug. UL and c-UL Listed. Dimensions: 66.3"H x 2.0"W x 2.0"D (1683mm x 51mm x 51mm)
Product Type	Vertical Power Outlet Unit
Color	Black
Depth (In.)	2.0
Depth (mm)	51
Height (In.)	66.3
Height (mm)	1683
Width (In.)	2.0
Width (mm)	51
Plug Type	California Style
Pricing Description	Vertical, Mixed (30) C-13 & (6) C-19 208V, 35A Networked Three-Phase Delta POU
Min. Order UOM	PC
Min. Order Qty.	1
Voltage	208V
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy