

Features

- complete probe set for measurements up to 100MHz
- attenuation: 1:1 or 1:10

Specifications

- position x1:
 - attenuation: 1:1
 - bandwidth: DC to 60MHz
 - rise time: 5.8ns
 - input resistance: 1Mohm (input resistance scope)
 - input capacitance: 90pF + cap. scope
 - working voltage: 600Vdc incl. peak AC derating with frequency
 - position REF: tip disconnected, scope input at ground
- position x10:
 - attenuation: 1:10
 - bandwidth: DC to 100MHz
 - rise time: 2.8ns
 - input resistance: 10Mohm (if scope input = 1Mohm)
 - input capacitance: 16pF approx.
 - working voltage: 600Vdc incl. peak AC derating with frequency
 - compensation range: 10 to 35pF
- cable length: 1.4m

