44AM1121-20-9/96-9CS2275 Product Details



44AM1121-20-9/96-9CS2275

TE Part Number: 731235-000
Active
Add to Part List

Spec 44, Spec 55 and Spec RCW Wire and Cable

Not EU RoHS or ELV Compliant

Product Highlights:
- Wire Source = United States
- Cable Type = Spec 44
- Cable Style = Jacketed, Round-Braid Shielded
- Wire Size (AWG/CM) = 20 AWG
- Voltage Rating = 600 VAC

View all Features | Find Similar Products

Quick Links
- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product
- Request Samples NEW!

Documentation & Additional Information

Product Drawings:
- TWO CONDUCTOR CABLE, RADIATION-CROSSLINKED, POLYALKE... (PDF, English)

Catalog Pages/Data Sheets:
- Wire and Cable,Harnessing and Protection Products (PDF, English)

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

List all Documents

Additional Information:
- Product Line Information

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Cable Style = Jacketed, Round-Braid Shielded
- Number of Conductors = Twisted Pair

Electrical Characteristics:
- Voltage Rating (VAC) = 600

Body Related Features:
- Wire Size (AWG/CM) = 20 AWG
- Cable Jacket Color = White
- Conductor Type = Tin-Plated Copper
- Wire Color = White, White w/ Blue Stripe
- Outside Diameter (mm [in]) = 3.76 [0.148]
- Wire Diameter (mm [in]) = 1.40 [0.055]
- Conductor O.D. (mm [in]) = 1.01 [0.040]

Configuration Related Features:
- Cable Type = Spec 44

Industry Standards:
- Government/Industry Qualification = No
- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not relevant for lead free process

Conditions for Usage:
- Temperature Range (°C) = -65 – +150

Operation/Application:
- Application = General Purpose - Lightweight

Packaging Related Features:
- Wire Source = United States
- Wire Size - Details = 20 AWG 0.62 mm², 0.00095 in², 19 x 32 AWG
- Shield (Screen) Diameter (mm [in]) = 3.35 [0.132]

Other:
- Brand = Raychem

© 2008 Tyco Electronics Corporation All Rights Reserved