

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

5SE40I-T

5SE40I-T

N

DRAWING
NUMBER**EN**

3

REPLACES

RELEASE NO. PR-2043

CHECK

CHECK 616

172765

Δη


71 | CHECK

NUR

25

18

4378-1A



NOTE -

- 1- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
 OF .087 MAX DIA ON .375 $\pm$.002 CENTERS
 2- ACTUATION IN LINE ARROW "A" IS RECOMMENDED
 3- CONTACT MATERIAL - 24K GOLD PLATED CONTACTS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE-----5-19 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE -----4 OZ MIN	30 VOLTS DC RATING	UNLESS OTHERWISE NOTED
RELEASE TRAVEL-----.004 MIN	INDUCTIVE -----SEA LEVEL----- 0.5 AMP	DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL -----.004 MAX	RESISTIVE -----SEA LEVEL----- 1.0 AMP	TOLERANCES ARE:
OVERTRAVEL-----.003 MIN		ONE PLACE (.0) ±.030
		TWO PLACE (.00) ±.015
		THREE PLACE (.000) ±.005
		ANGLES ±
		WEIGHT .26 OZ MAX