

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [39543-7104](#)  
**Status:** **Active**  
**Overview:** Eurostyle™ Terminal Blocks  
**Description:** 5.00mm Pitch Eurostyle™ Horizontal Fixed Mount PCB Terminal Block, with Reverse Imprinting, 4 Circuits

**Documents:**  
[3D Model](#)  
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                |                                            |
|----------------|--------------------------------------------|
| Product Family | Terminal Blocks                            |
| Series         | <a href="#">39543</a>                      |
| Application    | N/A                                        |
| Comments       | with Reverse Imprinting                    |
| Component Type | One Piece                                  |
| Overview       | <a href="#">Eurostyle™ Terminal Blocks</a> |
| Product Name   | ESE, Eurostyle™Fixed Mount                 |
| Type           | Euro Block                                 |
| UPC            | 822350546041                               |

**Physical**

|                               |                    |
|-------------------------------|--------------------|
| Circuits (Loaded)             | 4                  |
| Entry Angle                   | Vertical           |
| Lock to Mating Part           | None               |
| Number of Rows                | 1                  |
| Orientation                   | Horizontal         |
| PC Tail Length                | 3.50mm             |
| PCB Thickness - Recommended   | 2.50mm             |
| Panel Mount                   | No                 |
| Pitch - Mating Interface      | 5.00mm             |
| Pitch - Termination Interface | 5.00mm             |
| Polarized to Mating Part      | N/A                |
| Stackable                     | No                 |
| Temperature Range - Operating | -40°C to +105°C    |
| Wire Size AWG                 | 16, 18, 20, 22, 24 |
| Wire Size mm²                 | 0.20 - 1.31        |

**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 10A  |
| Voltage - Maximum             | 300V |

**Solder Process Data**

|                                                |                        |
|------------------------------------------------|------------------------|
| Duration at Max. Process Temperature (seconds) | 5                      |
| Lead-free Process Capability                   | Wave Capable (TH only) |
| Max. Cycles at Max. Process Temperature        | 135                    |
| Process Temperature max. C                     | 260                    |

**Material Info**

**Reference - Drawing Numbers**

|               |              |
|---------------|--------------|
| Sales Drawing | SD-39543-006 |
|---------------|--------------|




image - Reference only

**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

**Not Reviewed**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of  
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
non-product compliance questions.

**Search Parts in this Series**

[39543Series](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39543-7104](#)